

# EDGE MOUNT ADHESIVE BRACKETS

STREAMLINED, ERGONOMIC DESIGN TAKES UP LESS SPACE AND HELPS MAKE INSTALLATION EASIER

## Smaller Size, Higher Performance

TE Connectivity (TE) offers the latest addition to our popular Adhesive Bracket family: Edge Mount Adhesive Brackets. Ergonomically designed to help ensure ease of handling and efficient installation, these brackets take up less space and can accommodate various diameter cable bundles. Edge mount adhesive brackets offer another potent option as part of TE's cable management portfolio.

## Product Features

- Product footprint takes up less space
- Brackets are lightweight, but maintain their structural integrity by eliminating drilled holes and modifications
- Cable tie slot for large edge mount bracket can accommodate  $\leq 30$  mm diameter cable bundles
- Cable tie slot for small edge mount bracket can accommodate  $\leq 15$  mm diameter cable bundles
- Ergonomic design with smooth edges and corners
- V-groove in cable seating area for standard cable tie mount bracket

## Benefits

### Versatile

- Compatible with various industry standard cable tie sizes

### Ergonomic

- Curved surfaces over the edges and corners facilitate ease of handling

### Efficient


- Footprint consumes less space, leaving more room for other functional requirements

### Easy

- V-groove in cable seating area assists in properly mounting and placing cable bundle
- Adhesive solution versus bolt on for through hole routing

### Rugged





- Elimination of drilled holes and modifications helps maintain structural integrity



## Applications





- eVTOL Production
- Commercial Aircraft Cable Routing

## Small Edge Mount Bracket



Section A-A

## Large Edge Mount Bracket



Section A-A

Dimensions in mm.

**MECHANICAL**

<b>Tensile Strength</b>	PN 2406230-1: 3.1 N @ 80°C PN 2406490-1: 10.1 N @ 80°C
<b>Operating Temperature Range</b>	-55°C to +120°C
<b>Fungus Resistance per SAE AS23190</b>	3.3
<b>Flammability</b>	2.5 in per minute burn rate
<b>EU RoHS and EU ELV Compliant</b>	

**MATERIALS**

Nylon 66

**SPECIFICATIONS**

<b>Product Specification for Edge Mount Bracket</b>	108-161190
<b>Product Specification for Miniature Cable Tie Mount Bracket</b>	108-160612

**ORDERING INFORMATION**

<b>Description</b>	<b>Part Number</b>
Edge Mount Bracket — Small	2406230-1
Edge Mount Bracket — Large	2406490-1

## Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need. Visit [te.com/support](https://te.com/support) to chat with a Product Information Specialist.

## [te.com/edge-mount](https://te.com/edge-mount)

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2025 TE Connectivity. All Rights Reserved.

adm-eps-edgemount-ds-en-0125 01/25

TE Connectivity  
Aerospace, Defense & Marine  
2900 Fulling Mill Road  
Middletown, PA 17057