

Commercial Grade N Male to SMA Female Adapter



PE910061

Configuration

- N Male Connector 1
- SMA Female Connector 2
- 50 Ohms Impedance
- Commercial Grade Design
- Straight Body Geometry

Features

- Gold Plated Brass Contact

Applications

- Allows Connection Between Series
- General Purpose Test

Description

Pasternack's PE910061 type N male to SMA female adapter is part of our full line of RF components available for same-day shipping. Our type N to SMA adapter has a male to female gender configuration in a commercial grade design. PE910061 type N male to SMA female adapter operates to 6 GHz.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
Insertion Loss			0.15	dB
Operating Voltage (DC)			500	Vdc
Dielectric Withstanding Voltage (DC)			1,000	

Mechanical Specifications

Size

Length	1.17 in [29.72 mm]
Width	0.79 in [20.07 mm]
Height	0.79 in [20.07 mm]
Weight	0.07 lbs [31.75 g]

Description	Connector 1	Connector 2
Polarity	Standard	Standard

Commercial Grade N Male to SMA Female Adapter



PE910061

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	N Male		SMA Female	
Contact	Brass	Gold	Brass	Gold
Insulation	PTFE		PTFE	
Outer Conductor	Brass	Nickel		
Body	Brass	Nickel	Brass	Nickel
Gasket	Rubber			

Compliance Certifications (see [product page](#) for current document)


Commercial Grade N Male to SMA Female Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Commercial Grade N Male to SMA Female Adapter PE910061](#)

URL: <https://www.pasternack.com/commercial-grade-n-male-to-sma-female-adapter-pe910061.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE910061 CAD Drawing
Commercial Grade N Male to SMA Female Adapter



REVISION		DATE		CHANGED BY		APPROVED	
ZONE	REV	DESCRIPTION		INITIAL RELEASE		AGANWANI	
	A						

PE PASTERNAK an INFINITI® brand		Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE MILLIMETERS.		TOLERANCES: X = ±.2 [5] .XX = ±.02 [0.5] .XXX = ±.005 [0.13]		SCALE: NONE	
ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS OF INDIVIDUAL PARTS MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.		FRACTIONS: ± 1/32 ANGLES: ± 1°		SHEET: 1 OF 1	
CABLE LENGTH TOLERANCES: >12 [305] ≤ 60 [1524] = ±.12 [3] / -0 >60 [1524] ≤ 120 [3048] = ±.12 [3] / -0 >120 [3048] ≤ 300 [7620] = ±.12 [3] / -0		DESCRIPTION: COAXIAL ADAPTER, N-MALE / SMA FEMALE, COMMERCIAL GRADE			
ITEM NO. PE910061		DRAWN BY KGLEBOVA		REV A	
SIZE A		CAGE CODE 53919			