



## 70% ISOPROPYL ALCOHOL

70% IPA is recommended by CDC for disinfecting surfaces.\*



New from the critical cleaning experts at MicroCare™, Stereze Workspace Cleaners meet the highest safety and quality standards, keeping your people and space as safe as can be.

- Strong, tear resistant wipes designed to last
- Cleans desks, tables, counters, equipment, doors, door handles, light switches, keyboards, phones, computers, faucets, sinks, tools and more!
- Safe on stainless steel, metals, plastic and glass materials
- Presaturated wipe tub (STIA100W) has a unique “slam-shut” lid to keep wipes wet
- Made in the USA

### SAVE THE TUB!

Save money and reduce waste by re-using the packaging.

Refill packs contain the same quality wipes and fluid.

### AVAILABILITY:

Visit [MicroCare.com](http://MicroCare.com) for a distributor near you.

\* For more info, visit: [www.cdc.gov/coronavirus](http://www.cdc.gov/coronavirus)



**MicroCare, LLC**  
595 John Downey Drive  
New Britain, CT 06051 USA  
CAGE: OATV9  
Tel: +1 860 827 0626  
Toll Free: 1 800 638 0125  
Email: [TechSupport@MicroCare.com](mailto:TechSupport@MicroCare.com)

[MicroCare.com](http://MicroCare.com)

**MicroCare Europe BVBA**  
Vekestaat 29 B11  
Industriezone 't Sas  
1910 Kampenhout, Belgium  
Tel: +32 2 251 95 05  
Email: [EuroSales@MicroCare.com](mailto:EuroSales@MicroCare.com)

**MicroCare U.K. Ltd**  
Seven Hills Business Centre  
South Street, Morley  
Leeds, United Kingdom  
LS27 8AT  
Tel: +44 (0) 113 3609019  
Email: [mcceurope@microcare.com](mailto:mcceurope@microcare.com)

Follow Us!

**MicroCare Asia Pte Ltd**  
102E, Pasir Panjang Road  
Citilink, #05-06  
Singapore 118529  
Tel: +65 6271 0182  
Email: [TechSupport@MicroCare.sg](mailto:TechSupport@MicroCare.sg)

### Technical Details and Cleaning Data

Boiling Point	82 °C   180 °F
Chemical Family	Water & Alcohol
Evaporation Rate	Slow
Odor	Slight, Alcohol
Percent Volatile	100%
Specific Gravity	0.87 g/mL

### Health, Safety and Environmental Data

Flammable	Yes
Flashpoint	12 °C   54 °F
NFPA	Health: 1 Fire: 3 Instability: 1
RoHS & WEEE	Compliant
REACH	Compliant
US EPA SNAP	Approved
GHS / HCS Pictogram	

### Packaging

Spray Bottle (Refill: 1 Gallon, STIAJG)	32 oz   946 mL STIA32PS
Presaturated Wipes Tub, 100 Wipes Fluid content: 524 mL	5 in x 8 in 12 cm x 20 cm STIA100W
Presaturated Wipes Tub Refill, 100 Wipes Fluid content: 524 mL	5 in x 8 in 12 cm x 20 cm STIA100RW
Presaturated Wipes Bucket, 800 Wipes Fluid content: 3.0 L	8.5 in x 6 in 21.5 cm x 15.2 cm STIA800W
Presaturated Wipes Bucket Refill, 800 Wipes Fluid content: 3.0 L	8.5 in x 6 in 21.5 cm x 15.2 cm STIA800RW
Presaturated Wipe Individual Foil Wrap (50 Wipes/Box)	5 in x 6 in 12 cm x 15 cm STIA1W