





Press Release Quick Tips

Orion Fans Expands Fan Accessories Offering to Include Industry's Lowest-Cost Louvered Fan Guards

If you are already selling a fan, you should be selling one of these too
For fans and a complete line of fan accessories, all from one source, think Orion Fans

<p>Louvered Filter Fan Kits (industry's lowest cost)</p> <ul style="list-style-type: none">• Consists of a fan guard, filter, fan, metal guard, and hardware• Provides protection against dust, dirt and moisture from entering industrial, electrical and electronic cabinets• Can be rated to IP54, IP55 or IP56, and meet NEMA 12, depending on the fan used• Available from stock with 120mm, 172mm, 225mm, 254mm and 280mm AC fans• Kits requiring DC fans are also available upon request• Available with and without a finger guard	
<p>Louvered Fan Guards (industry's lowest cost)</p> <ul style="list-style-type: none">• Designed for harsh environments• Available for use with 80, 92, 120, 172, 225, 254 and 280mm fans	
<p>Air Flow Monitor Modules</p> <ul style="list-style-type: none">• Field retrofittable, economical solution for indicating fan or blower airflow• Operates an optical LED or audible alarm when airflow falls below 8.2 ft/s due to fan filter clogs or foreign materials coming in contact with the fan blade• Protects power supplies, PoE midspans and displays in sensitive equipment including servers, telecom switches, medical equipment and kiosks	
<p>Steel Wire & Wire Mesh Fan Guards</p> <ul style="list-style-type: none">• Can withstand 220 pounds of separation force• Meets UL/cUL standards• Wire fan guards are available for fan sizes ranging from 25mm to 280mm• Wire mesh fan guards are available from 60 to 172mm	

<p>Plastic Fan Guards</p> <ul style="list-style-type: none"> • Feature PBT, UL94V-0 thermoplastic • Available for fans in sizes ranging from 40 to 172mm 	
<p>Push-on Guards</p> <ul style="list-style-type: none"> • Cost-effective and simplifies assembly time • Requires no additional hardware • Available for 60, 80, 92, 120 and 172mm fans 	
<p>Traditional Filter Kits</p> <ul style="list-style-type: none"> • Each filter kit contains an ABS UL94V-0 thermoplastic fan guard, a retainer and media in 30ppi or 45ppi • Available for fans ranging in size from 40 to 172mm 	
<p>Cage Nuts</p> <ul style="list-style-type: none"> • Round and square hole snap-in cage nuts for mounting equipment into 19-inch racks • Heavy duty zinc plating and are available in M6, 10-32 and 12-24 thread sizes 	

Visit: <http://orionfans.com/products/accessories.html>