

Power Inductors

Model HM72L-0412 series




Features:

- Operating Temperature Range -55°C to $+125^{\circ}\text{C}$
- Ambient Temperature, Maximum $+85^{\circ}\text{C}$
- Temperature Rise, 40°C
- RoHS Compliant



All parts are Pb-free and comply with EU Directive 2011/65/EU (RoHS2)

Schematic



Specifications @ 25°C

Part Number	Inductance ($\mu\text{H} \pm 20\%$ @0A)	DCR ($\text{m}\Omega$) Typ	DCR ($\text{m}\Omega$) Max	Irms (A)	Isat (A)	Part Number	Inductance ($\mu\text{H} \pm 20\%$ @0A)	DCR ($\text{m}\Omega$) Typ.	DCR ($\text{m}\Omega$) Max	Irms (A)	Isat (A)
HM72L-0412R33LFTR	0.33	17.0	19.0	6.5	8.4	HM72L-04121R0LFTR	1.00	43.0	47.0	4.5	5.5
HM72L-0412R47LFTR	0.47	19.0	22.0	6.0	6.8	HM72L-04121R5LFTR	1.50	68.0	75.0	3.25	4.0
HM72L-0412R68LFTR	0.68	32.0	36.0	4.7	6.0	HM72L-04122R2LFTR	2.20	79.4	83.5	2.75	3.5

Notes: (1) Isat is the saturation current at which inductance rolls off approximately 30% from its initial (zero DC)

(2) Irms is the approximate current at which $\Delta T = 40^{\circ}\text{C}$

(3) Operating Temperature Range -55°C to $+125^{\circ}\text{C}$

General Note







TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Power Inductors

Model HM72L-0412 series



Electrical Specifications @ 25



General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT electronics plc

TT Electronics | BI Technologies
A-1445, Jalan Tanjung Api
25050 Kuantan Pahang Darul Makmur, Malaysia | Ph: +60 9 565 8888
www.ttelectronicsmagnetics.com/customer-service-enquiry

Issue A 10/2018 Page 2

Outline dimensions (mm)



CASE SIZE	A(mm)	B(mm)	C(mm)	D(mm)	E(mm)	F(mm)	G(mm)	H(mm)
0412 series	4.2 ± 0.25	4.4 ± 0.35	1.2	1.5 ± 0.3	0.8 ± 0.3	4.95	2.15	2.3

Packaging

Standard:	Embossed Tape and Reel	
	Reel:	Diameter: All case size = 13" (330mm)) Capacity: Case size 0412 = 3,000 units

Ordering information

HM72L – XXXX XXX LF TR

Case Size

Ind Value

Tape & Reel Packing

Lead frame (LF)

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.