

# Product Index

Displayport™ ..... 1211, 1213, 1215, 1219  
 Duxbox™ ..... 1440  
 DVI ..... 1090, 1102, 1104, 1213  
 EBBI™ ..... 1493  
 ECOIMATE® ..... 1309  
 Ethercon® ..... 1205  
 Ethernet ..... 1091, 1200, 1205, 1231-1238, 1240-1244, 1247  
 Factory Automation ..... 1313  
 Faston ..... 1532-1533  
 Ferrules ..... 1541-1542  
 FFC/FPC (Flexible Printed Circuit) ..... 1348, 1444-1445, 1454-1455, 1466, 1510-1513  
 Fiber Optic  
 Cable Assemblies ..... 1087, 1093-1094, 1205, 1216, 1237  
 Connectors ..... 1087, 1205, 1211, 1216, 1237  
 Filtered  
 Circular ..... 1332  
 D-Subs ..... 1266, 1276-1278, 1286-1287  
 Inlets ..... 1110-1111, 1113-1115, 1118-1120  
 Modular ..... 1195, 1200  
 Modules ..... 1110-1111, 1113-1115, 1118-1119, 1121  
 USB ..... 1217  
 FireWire (IEEE 1394) ..... 1101, 1104, 1202-1203, 1205, 1207, 1229, 1234, 1244, 1246-1247  
 Flat Flex Cable ..... 1073, 1511-1512, 1514-1515  
 Flat Ribbon Cable ..... 1072, 1284, 1392-1394, 1399-1400, 1436-1437, 1444, 1471, 1571  
 Futurebus ..... 1358, 1372  
 Gender Changers ..... 1267, 1438  
 GIG-Array ..... 1205  
 Han® ..... 1241, 1382-1387  
 Han® Max/Industrial Ethernet ..... 1205, 1231-1238, 1241-1244  
 HandyLink™ ..... 1212  
 Hard Metric ..... 1229, 1352, 1358-1359, 1361, 1366, 1372, 1377  
 HDMI  
 Cable Assemblies ..... 1090, 1102, 1104, 1202, 1205, 1213  
 Connectors ..... 1102, 1104, 1202-1203, 1205, 1213-1214  
 Headers  
 0.50mm ..... 1453-1454  
 1.00mm / .039" ..... 1368, 1488  
 1.25mm / .049" ..... 1401, 1459, 1489-1490, 1526  
 1.27mm / .050" ..... 1252, 1394, 1407, 1409, 1415, 1442, 1450, 1487, 1492  
 1.50mm / .059" ..... 1401, 1491  
 2.00mm / .079" ..... 1284, 1352, 1358, 1366, 1396-1397, 1400, 1402, 1409, 1442-1443, 1451, 1459, 1462-1464, 1490, 1494-1500  
 2.13mm / .084" ..... 1473  
 2.36mm / .093" ..... 1474  
 2.50mm / .098" ..... 1458, 1501, 1560-1561  
 2.54mm / .100" ..... 1352, 1391-1394, 1400, 1405-1407, 1409-1417, 1435-1437, 1440-1441, 1476-1479, 1481, 1519, 1527-1528  
 3.00mm / .118" ..... 1454, 1502-1504, 1547  
 3.96mm / .156" ..... 1378, 1420, 1482  
 4.14mm / .163" ..... 1422  
 4.20mm / .165" ..... 1431, 1506  
 5.00mm / .197" ..... 1366, 1427, 1547  
 5.08mm / .200" ..... 1424, 1508  
 6.35mm / .250" ..... 1425  
 7.50mm / .295" ..... 1388, 1508, 1569  
 10.00mm / .393" ..... 1507, 1569  
 Box ..... 1393, 1396  
 Breakaway ..... 1391, 1405, 1441, 1477, 1481, 1483  
 Carbus ..... 1364  
 DIN 41612 ..... 1239, 1356, 1368  
 DIP ..... 1471, 1519  
 Hard Metric ..... 1352, 1358, 1366, 1377  
 High-Temp ..... 1560  
 IDC ..... 1368, 1394, 1407, 1409, 1416-1417, 1420, 1436-1437, 1471, 1480, 1482-1483, 1487, 1560, 1562  
 Latch/Ejector ..... 1392, 1410, 1436-1437, 1442  
 Low Profile ..... 1393, 1409, 1414, 1436, 1440, 1459, 1476, 1487, 1560, 1562  
 Pin Strip ..... 1391, 1396-1397, 1405, 1441, 1477-1478, 1481, 1483, 1557-1558  
 Shrouded ..... 1394, 1411, 1413, 1417, 1436, 1440, 1442-1443, 1476, 1500-1501  
 Terminal Block ..... 1546-1548, 1557-1562, 1565-1569  
 Unshrouded ..... 1407, 1441-1443  
 Wire to Board ..... 1347, 1378, 1388, 1401, 1456-1459, 1489, 1494, 1496-1497  
 Hot Shoe ..... 1450  
 HPI ..... 1401  
 IDC  
 Cable ..... 1071-1072, 1074, 1394  
 D-Sub ..... 1250, 1255, 1260  
 Dust Covers / Strain Relief ..... 1260, 1395, 1407, 1416-1417, 1424, 1471  
 Headers ..... 1394, 1407, 1409, 1416-1417, 1420  
 Plugs ..... 1250, 1394, 1399, 1409, 1471, 1537  
 Receptacles ..... 1250, 1368, 1409, 1416, 1419, 1437, 1471, 1537  
 Scotchlok ..... 1530  
 Socket ..... 1250, 1395, 1419-1420, 1424  
 IEEE 1394 ..... 1101, 1104, 1202-1203, 1205, 1207, 1229, 1234, 1244, 1246-1247  
 iGrid™ ..... 1495  
 Industrial  
 Ethernet ..... 1205, 1231-1238, 1241-1244  
 FireWire (IEEE 1394) ..... 1205, 1234, 1244  
 USB ..... 1205, 1231, 1234-1235, 1238, 1243-1244  
 Infiniband ..... 1073, 1218-1219, 1226  
 Inlets ..... 1105, 1107, 1110-1115, 1117-1120

Interface Modules ..... 1547, 1571-1572  
 iPass ..... 1227  
 I-Tra ..... 1377  
 Jacks  
 Audio ..... 1084, 1128, 1130-1136, 1138-1145, 1147-1148, 1150, 1221, 2000  
 Banana ..... 1084, 1132-1134, 1985  
 DC Power ..... 1123-1125, 1127, 2000  
 DIN ..... 1130-1131, 1142, 1150  
 Modular ..... 1191-1192, 1194-1201, 1205, 1221, 1231-1234, 1244, 2000  
 Phone ..... 1135-1136, 1139-1142, 1147-1148, 1194, 1201  
 Phono (RCA) ..... 1084, 1128, 1130, 1138, 1142, 1147  
 Telephone ..... 1194, 1201  
 Test ..... 1134, 1985  
 Tip ..... 1134  
 XLR ..... 1128, 1131, 1142-1144, 1147, 1150  
 Jones Plugs and Sockets ..... 1381, 1389  
 Jumpers  
 Cable ..... 1471, 1511-1512  
 FFC / FPC ..... 1511-1512  
 Shunts ..... 1390, 1435, 1443, 1471, 1477, 1518  
 Shorting ..... 1471  
 Terminal ..... 1549-1550  
 Test Leads ..... 1987-1988  
 Keying Plugs ..... 1291, 1294, 1403, 1414, 1418, 1421  
 Kits  
 D-Sub ..... 1250, 1252, 1258-1259, 1284, 1286  
 Modular ..... 1193, 1284, 1988, 1990, 2000  
 Pin and Socket ..... 1472, 1474  
 Pin Adapters ..... 1154, 1175, 1197, 1190  
 Terminal ..... 1530, 1537-1542  
 KK® Series ..... 1480-1483  
 LFH™ ..... 1493  
 Lighting Connectors ..... 83, 1347-1351  
 M8 ..... 1295, 1338-1339, 1840  
 M12 ..... 1241, 1295, 1313, 1338-1339, 1840  
 M23 ..... 1312, 1337  
 M40 ..... 1312  
 Mate-N-Lok ..... 1421-1426, 1438  
 Memory  
 Compactflash® ..... 1209, 1352, 1354, 1361, 1373, 1375  
 DDR ..... 1374  
 DDR2 ..... 1364, 1374  
 DDR3 ..... 1364, 1374  
 DIMM ..... 1373-1374  
 Hybrid ..... 1360  
 Keys ..... 1235  
 Memory Stick ..... 1354  
 microDIMM ..... 1375  
 microSD™ ..... 1209, 1352-1354, 1361, 1373, 1375  
 miniDIMM ..... 1375  
 miniSD™ ..... 1209, 1353-1354, 1373  
 MMC ..... 1353-1354  
 PC Card ..... 1364  
 SD™ ..... 1209, 1352-1354, 1361, 1375  
 SIM Card ..... 1209, 1353, 1361, 1373, 1375  
 Smart Card ..... 1353-1354, 1360, 1373  
 Metrimat ..... 1427  
 Metral ..... 1365  
 Mezzanine ..... 1222, 1229, 1368, 1430, 1438-1439  
 Mi II ..... 1496  
 MicroBlade™ ..... 1494  
 MicroClasp™ ..... 1497  
 Micro-fit 3.0™ ..... 1502-1504  
 Micro-MaTch ..... 1408  
 MicroTCA™ (JTCA™)  
 Card Edge ..... 1229, 1367, 1376  
 D-Sub Power ..... 1097, 1268  
 Micro-USB ..... 1202-1203, 1206, 1215  
 Milli-Grid ..... 1499-1500  
 Mini-Clamp ..... 1399-1400  
 Mini-D Ribbon ..... 1249-1250  
 Mini-DIN ..... 1293, 1332  
 Mini-Fit ..... 1505-1507  
 Mini SAS ..... 1219-1220, 1224, 1227  
 Minitek™ ..... 1442-1443  
 Mini-USB ..... 1101, 1202-1203, 1206, 2008, 1215, 1243  
 Modular  
 Cable Assemblies ..... 1192, 1205, 1236, 1238, 1243-1244  
 Couplers ..... 1193  
 Jacks ..... 1191-1192, 1194-1201, 1205, 1231-1234, 1244, 2000  
 Plugs ..... 1193, 1196-1198, 1232-1234, 1236, 1238, 1244, 1988, 1990  
 Power Over Ethernet (POE) ..... 1199  
 RJ11 ..... 1194, 1232  
 RJ45 ..... 1192, 1194, 1200-1201, 1205, 1232, 1236, 1238, 1244, 1464-1466  
 Stacked ..... 1192  
 Motiongrade™ ..... 1312  
 MT Series ..... 1414  
 MTA Series ..... 1416-1420, 1990  
 MTE Series ..... 1411, 1413  
 MX150™ ..... 1509  
 NEMA Terminal Blocks ..... 1543  
 OpticalCon® ..... 1205  
 Outlets ..... 1105, 1107, 1111-1114, 1117-1120, 1274  
 Patch Cord Assemblies ..... (See Wire and Cable)  
 PCI-Express ..... 1227, 1355, 1368, 1373  
 PC Pins / Receptacles ..... 1150, 1253-1254, 1257, 1403, 1413, 1416, 1419, 1440, 1480, 1482, 1522, 1525  
 PE Series ..... 1431  
 PicoBlade™ ..... 1489  
 Pico-Clasp™ ..... 1488  
 PicoFlex® ..... 1487  
 Pico-Spox™ ..... 1491

Pin and Socket  
 1.00mm / .039" ..... 1488  
 1.57mm / .062" ..... 1429, 1472  
 2.00mm / .079" ..... 1451, 1505-1506  
 2.13mm / .084" ..... 1473  
 2.36mm / .093" ..... 1429, 1474  
 2.54mm / .100" ..... 1418  
 3.00mm / .118" ..... 1426, 1502-1504  
 3.96mm / .156" ..... 1418-1420  
 4.14mm / .163" ..... 1421-1422  
 4.20mm / .165" ..... 1431, 1505-1506  
 5.00mm / .197" ..... 1427  
 5.08mm / .200" ..... 1423-1424  
 6.35mm / .250" ..... 1425  
 PC 104 and PC 104-Plus ..... 1357, 1451  
 Plugs  
 AC ..... 1107, 1128  
 Banana ..... 1132-1134, 1985  
 DC Power ..... 1128, 1130, 1138, 1142, 1147  
 DIN ..... 1130-1131, 1142, 1150, 1332, 1574, 1577  
 Iris ..... 1136  
 Jones ..... 1381, 1389  
 Modular ..... 1193, 1196-1198, 1232-1234, 1236, 1238, 1244, 1988  
 Phone ..... 1137, 1141-1142, 1147, 1149  
 Phono (RCA) ..... 1128, 1130, 1138, 1142, 1147  
 Tip ..... 1134  
 Water Resistant / Waterproof ..... 1236, 1293, 1301-1302, 1305-1306, 1325, 1328, 1330, 1335-1336, 1340, 1342, 1509  
 XLR ..... 1128, 1131, 1142-1144, 1147, 1150  
 Pneumatic Modules ..... 1385  
 Power  
 AC ..... 1105, 1107-1115, 1117-1121, 1128  
 Circular ..... 1248, 1289-1290, 1337, 1343  
 DC Power ..... 1114, 1122-1127, 1248, 2000  
 Disk Drive ..... 1508  
 Entry Modules ..... 1108-1115, 1117-1119  
 Heavy Duty ..... 1382-1387  
 IEC ..... 1105, 1107, 1109-1115, 1117-1120  
 JONES ..... 1381, 1389  
 Rectangular ..... 1378-1389, 1431, 1449, 1505-1506, 1508, 2000  
 Power Clamp ..... 1381, 1389  
 Powercon® ..... 1145  
 Quickie™ ..... 1436-1437  
 Radsok® ..... 1307  
 Rack and Panel ..... 1363  
 Rectangular Power ..... 1378-1389, 2000  
 RF  
 Adapters ..... 1146, 1152, 1154, 1156, 1158, 1161, 1166, 1168-1172, 1174-1175, 1177-1178, 1181-1182, 1186-1187, 1189-1190  
 AMC ..... 1172  
 BNC ..... 1084, 1096, 1129, 1146, 1151-1152, 1158, 1162, 1165-1168, 1170, 1175-1177, 1188, 1190, 1984  
 Compression ..... 1084, 1129, 1177  
 F Series ..... 1129, 1146, 1159, 1176, 1178  
 H.F.L ..... 1182  
 High Frequency Edge Mount ..... 1184  
 MATV/CATV ..... 1175, 1178  
 MCX/MMCX ..... 1099-1100, 1170, 1175, 1180, 1187-1189  
 MHV ..... 1170  
 Mini BNC ..... 1084, 1170  
 M-UHV ..... 1159  
 N Series ..... 1100, 1156, 1162  
 QMA ..... 1172  
 QSL ..... 1157  
 RCA ..... 1084, 1129, 1177  
 Reverse Polarity ..... 1162, 1169  
 SHV ..... 1155  
 SMA ..... 1092, 1096, 1099-1100, 1154, 1156, 1159, 1162-1163, 1171, 1176, 1179, 1182-1185, 1188-1190, 1984  
 SMB ..... 1100, 1154, 1165, 1173, 1186, 1188-1189, 1318  
 SMK ..... 1185  
 SMP ..... 1172, 1183  
 Stainless Steel ..... 1096, 1171, 1184  
 Terminators ..... 1152, 1190  
 TNC ..... 1155, 1159, 1162, 1164, 1169, 1177  
 Twin-Axial ..... 1173  
 UHF ..... 1159, 1169, 1173, 1178  
 U.F.L ..... 1181  
 W.F.L ..... 1182  
 ZDC ..... 1158-1159  
 Rib-Cage™ ..... 1439  
 Sabre ..... 1508  
 Scotchlok ..... 1530  
 SCSI ..... 1103, 1220-1221, 1227, 1230  
 Searay ..... 1492  
 Serial ATA (SATA) ..... 1103, 1214, 1219-1220, 1227-1228  
 SFP / SFP+ ..... 1218, 1223, 1225  
 Sherlock™ ..... 1498  
 Shrunk D Ribbon (SDR) ..... 1207  
 Shunts ..... (See Connectors/Jumpers)  
 SL™ ..... 1204, 1475-1476  
 SlimStack™ ..... 1484-1486  
 Smart Card ..... 1353-1354, 1360, 1373  
 Sockets  
 Ball Grid Array (BGA) ..... 1438  
 Board Mount ..... 1249-1250, 1390, 1393, 1395, 1397-1398, 1400, 1424, 1426  
 Burn-In ..... 1517  
 Compact PCI ..... 1358-1359, 1382  
 DDR2 ..... 1374  
 DIMM ..... 1373-1374  
 DIP ..... 1471, 1516-1520, 1523-1524  
 Display ..... 1518, 1524  
 Fine Pitch ..... 1451-1452  
 IC ..... 1518-1520, 1523-1524, 1526-1528, 1785

IDC ..... 1419-1420, 1471  
 In-line ..... 1343, 1427, 1517, 1524, 1526-1528  
 PCB ..... 1132, 1158-1159, 1293, 1390, 1421-1423, 1425, 1438, 1506-1507, 1515-1516, 1522, 1525, 1990-1991  
 Jones ..... 1381, 1389  
 Oscillator ..... 1519  
 PLCC ..... 1516, 1519-1521  
 SIMM ..... 1520  
 SIP ..... 1520, 1526-1528  
 SOIC ..... 1517-1518  
 SOJ ..... 1518  
 SSOP ..... 1518  
 Surface Mount ..... 1202-1204, 1250, 1352, 1373, 1488, 1516, 1521, 1524  
 Test ..... 1517, 1519  
 Transistor ..... 1520, 1524  
 Wiremount ..... 1394-1395, 1397, 1399-1400  
 ZIF ..... 1519  
 Solar ..... 1248  
 Solderless ..... 1133-1134, 1530-1533, 1535-1537, 1539-1540  
 Speakon® ..... 1145  
 SPEEDCON ..... 1339  
 SPOX™ ..... 1501  
 Terminal Blocks  
 2.50mm / .098" ..... 1560-1561  
 2.54mm / .100" ..... 1554, 1556  
 3.5mm / .137" ..... 1545, 1547, 1551, 1554, 1558-1562, 1564  
 3.81mm / .150" ..... 1545, 1547, 1554, 1556, 1560, 1565, 1570  
 4.00mm / .157" ..... 1545-1547, 1551-1552, 1554, 1556, 1564, 1566, 1569  
 5.00mm / .197" ..... 1545-1547, 1551-1552, 1554, 1556, 1564, 1566, 1569  
 6.35mm / .250" ..... 1544  
 7.50mm / .295" ..... 1545, 1569  
 7.62mm / .300" ..... 1545, 1568-1569  
 9.52mm / .375" ..... 1543-1544, 1549  
 10.00mm / .393" ..... 1545, 1556, 1569  
 10.16mm / .400" ..... 1545, 1569  
 12.00mm / .500" ..... 1553  
 15.00mm / .590" ..... 1569  
 Accessories ..... 1543, 1547, 1549-1550, 1556, 1570, 1572-1574, 1577-1581  
 Barrier ..... 1544, 1549-1550, 1553  
 CLIPLINE ..... 1573-1577  
 DIN Rail ..... 1572-1581  
 Eurostyle ..... 1545-1546, 1551-1554, 1556-1570, 1573-1581  
 Ferrules ..... 1541  
 Fixed ..... 1551, 1553, 1558-1560, 1563-1564  
 Fuse Blocks ..... 1578, 1581  
 Interface Modules ..... 1547, 1571-1572  
 Panel Mount ..... 1554, 1570, 1572  
 Pluggable ..... 1545, 1547-1548, 1552-1554, 1557-1570, 1574  
 Terminal Strips ..... 1544, 1549, 1553, 1557-1558, 1581  
 Terminals and Splices  
 Butt Splices ..... 1531-1533, 1535-1536, 1539-1540  
 Closed End Splices ..... 1530, 1535  
 Compression ..... 1540  
 Couplers ..... 1536  
 Crimp ..... 1475, 1478, 1480, 1482, 1489-1491, 1494, 1499, 1501, 1508, 1530-1531, 1533, 1540-1541  
 Disconnects ..... 1530-1531, 1536, 1539-1540  
 Faston ..... 1532-1533  
 Ferrules ..... 1541-1542  
 Fork ..... 1531, 1539-1540  
 Heat Shrink ..... 1531, 1536  
 PCB ..... 1480, 1482, 1489, 1507, 1522, 1550-1551, 1558-1559, 1562, 1564-1569, 1726  
 Ring ..... 1531-1533, 1535-1537, 1539  
 Snap Plugs ..... 1535, 1537  
 Solder Lugs ..... 1133  
 Spade ..... 1531-1533, 1535-1536  
 Wire Connectors ..... 1475, 1530-1531, 1537, 1540-1541, 1546-1547, 1557, 1561, 1565-1569  
 Tools ..... (See "T" Section)  
 Triad™ ..... 1226  
 Trim Trio™ ..... 1340-1344  
 Trio Tek ..... 1446  
 USB  
 Cable Assemblies ..... 1090-1091, 1097, 1101, 1104, 1192, 1202, 1205-1206, 1208, 1215, 1235, 1238, 1243-1244  
 Connectors ..... 1091, 1097, 1101, 1104, 1192, 1202-1206, 1208-1209, 1211, 1214-1215, 1217-1218, 1231, 1234-1235, 1238, 1243-1245  
 UHM ..... 1352  
 Val-U-Lok ..... 1431  
 Vesa ..... 1278  
 VHDCI ..... 1103, 1212, 1219  
 Video RCA Broadcast ..... 1129  
 Wire Nuts ..... 1531, 1537  
 X2 ..... 1224, 1986  
 Xepak ..... 1224, 1226  
 XFP ..... 1224, 1226  
 XLR ..... 1128, 1131, 1142-1144, 1147, 1150  
 X-Pak ..... 1224  
 Z-Pack ..... 1358-1359  
**Connectors** ..... 1750, 1752, 1786  
**Controllers**  
 LCD ..... 49, 51-53, 55, 183, 203, 207, 266, 293  
 Programmable ..... 177, 1788  
 Temperature ..... 35, 303-304, 1752, 1789  
**Converters** ..... (See Semiconductors)  
**Core Modules** ..... (See Semiconductors)  
**Counters** ..... 249-251, 1785, 1790-1791