

Product Index

Flow 1849, 1852
 Fluid 157
 Hall Effect 157, 300, 360, 1835, 1837, 1839, 1853
 Image 264
 Infrared 157, 165-166, 292, 1836
 Linear 159, 300, 1834-1835, 1837-1839, 1852
 Linear Motion 1834-1835, 1837-1838
 Load Cells 1863-1864
 Magnetic 1834, 1836-1837, 1839
 Photoelectric 1843-1847
 Photomicrosensors 1844-1845
 Position 1834-1839
 Pressure 1854-1864
 Proximity 273, 1839-1843
 Reflective 157, 166, 1845
 Speed 292, 1839
 Reed 1848
 RFID Products 16, 34, 294
 Rotary 1834-1835, 1838
 Temperature 16, 28, 34-35, 287-288, 292, 294, 303-304, 561-562, 1838, 1850-1851
 Tilt 1849, 1864
 Vane 1839
 Vibration 1849, 1864

Sensor/Actuator Boxes 1338

Servers 22-23, 33, 42

Shunts 315-316, 357, 360, 376, 391, 619, 1390, 1406, 1435, 1443, 1471, 1477, 1518, 1977

Single Board Computers 43-46, 48

Sirens 1806, 1811

Slewing 1029-1061

Smart Card Readers 293-294, 314, 1353-1354, 1360, 1364, 1373

Sockets (See Connectors)

Socket Relays 1515, 1763, 1776

Software 173, 179, 190, 192, 198, 245

Sonalerts 1804-1806

Speakers 1086, 1803, 1805, 1810-1811

Splices 1068, 1343, 1530-1533, 1535-1540

Static Control Products 1877-1880, 1882, 1993-1996

Stick Controllers 1611

Surge Suppressors 432, 516, 525-528, 530, 532-536, 538, 540-544, 546-547, 555-556, 558-559, 571

Switches

Anti-Vandal 1620-1622, 1633-1634, 1651, 1653-1654

Basic 1583-1587, 1589-1597

Boot Seals 1618-1619, 1658-1659, 1661, 1668, 1705

Coaxial 1710

Coded Rotary 1612, 1695-1701

Detection 1608-1610

DIP/SIP 1688-1691, 1699-1701

Directional 1611

Door 1610, 1686

Door Contact 1610, 1686

Emergency Stop 1620-1621, 1647, 1649

Encoders 294, 1611-1617

Foot 1636

Hook 1587

Illuminated

Pushbutton 1620-1623, 1626, 1629-1634, 1636-1637, 1640-1645, 1647, 1649, 1655

Rocker 1637, 1670-1674, 1677-1678

Selector 1620-1621, 1679

Slide 1685

Tactile 1603-1604, 1607, 1666

Toggle 372, 659

Indicator 1621

Key Pushbutton 273, 389, 1637

Leaf 1587

Lever & Push Operation 1244, 1611-1612, 1680

Limit 372, 1591, 1702-1704

Line Interrupt 1587

Line Voltage 1683

Magnetic 1617, 1686, 1798, 1800

Multi-Directional 1598, 1611

Navigation 1602, 1611

Optical (Photomicrosensors) 157

Piezo 1653-1654

Push 1244, 1611-1612

Pushbutton

16mm 1622, 1646-1647

22mm 1635, 1645, 1648-1650

Anti-Vandal 1620-1622, 1633-1634, 1651, 1653-1654

Boot Seals 1618-1619, 1705

Emergency Stop 1620-1621, 1647, 1649

Environmentally Sealed 1620-1621, 1639

Foot 1636

Hermetically Sealed 1618

Illuminated 1620-1623, 1626, 1629-1634, 1636-1637, 1640-1645, 1647, 1649, 1655

Key 1621

Non-Illuminated 1622, 1626, 1632, 1640, 1646, 1648, 1650

Power 1629

Security 1620

Snap Action 1618, 1620-1621, 1624-1625, 1636, 1638, 1655

Surface Mount 1624, 1626, 1687

Rocker

Appliance Style 1673

Boot Seals 1705

Dual Color 1673

Double Pole 1669

Illuminated 1637, 1670-1674, 1677-1678

Miniature 1671-1673, 1675, 1677

Power 1671-1672, 1675, 1677, 1800

Sealed 1675, 1677-1678

Single Pole 1669, 1671

Snap-In 1669-1671, 1677

Tippette 1670

Rotary

Adjustable 1695-1696, 1698

Decimal Coded 1699-1701

DIP 1699-1701

Enclosed 1692, 1694-1696, 1698

Hexadecimal Coded 1699, 1701

Non-Shorting 1695-1698, 1700

Open Frame 1692-1693, 1696-1697

Shorting 1698

Surface Mount 1614, 1700-1701

TO-5 1698

Seals 1618-1619, 1645, 1658-1659, 1661, 1668, 1691, 1705

Security 1620

Seesaw and Push 1244, 1611-1612

Selector 1620-1621, 1679

Slide

Illuminated 1685

Instrumentation Grade 1680

Line Voltage 1683

Miniature 659, 1680, 1682-1685

PCB Mount 1681-1685

Power 1681, 1683

Sealed 1682

Snap-In 1682

Surface Mount 1681

Snap Action 1583-1597, 1618, 1620-1621, 1638, 1655, 1702, 1704

Stick Controllers 1611

Tactile

Caps 1600, 1603-1604, 1606

Double Action 1598

Illuminated 1603-1604, 1607

Surface Mount 1598-1599, 1601-1603, 1605-1607

Through-Hole 1599-1607

Tilt 1665, 1849

Toggle

Boot Seals 1658-1659, 1661, 1668, 1705

Environmentally Sealed 1667

Illuminated 1666

LED Tipped 1666

Miniature 1658-1661, 1663, 1665-1667

Panel Mount 1661, 1663-1665

PC Mount 1665

Power 1662, 1668

Surface Mount 1660

T

Tachometers 1790

Tape

Anti-Static 1993, 1995

Circuit Plating 1992-1993

Color Coding 1992

Double Coated Film 1992

Duct 1992

Foam 1996

Glass Cloth 1992

Labeling 1047

Low Static 1993, 1995

Mastic 1992

Plating 1992-1993

Shielding 1993, 1996

Silicone Rubber Electrical 1992

Splicing 1992

VHB 49, 1993

Vinyl Electrical 1531, 1992

Terminal Blocks (See Connectors)

Terminals (See Connectors)

Test Equipment

Accessories

Alligator Clips and Leads 1984, 1988

Banana Plugs and Jacks 1985

BNC 1984

Grabbers 1984-1987

Patch Cords 1980, 1985-1986

Telecom Products 1984, 1986

Test Clips 1980, 1984-1988

Test Lead Holder 1986

Test Leads 1984-1988

Analyzers and Testers 555, 1981-1982

Kits and Sets 1190, 1981-1982, 1986-1988

Meters 1976-1979

Probes 1980, 1982-1984, 1987-1988

Thermal Protection 538, 560-564, 566, 1797-1802

Thermistors 560-564, 566, 1838

Thermostats 1838, 1850, 1901

Thyristors 412, 454, 517-523, 571, 1754

Timers 256-257, 272, 295, 307, 318, 1791-1793

Tools

Cable Stripper 1084, 1155

Cable Tie 1049-1050, 1057

Clamps 1057

Coax Cable Stripper 1084, 1155

Contact Extraction

7.50mm 1508

CPC 1288-1289, 1990

D-Sub 1256, 1258, 1271

DIN 1371

KK® Series 1480, 1482

MATE-N-LOK 1425, 1502, 1507, 1990

MICRO-FIT 3.0™ 1502

MINI-FIT JR.™/SR.™ 1507

MTE Series 1413

Pin and Socket 1340, 1344-1345, 1423, 1425, 1472, 1474, 1502, 1507, 1990

SL™ 1475

Contact Insertion

CPC 1289, 1990

D-Sub 1256, 1258, 1271

DIN 1371

KK® Series 1480

MATE-N-LOK 1425, 1990

SL™ 1475

Crimpers

7.50mm 1508

Coaxial 1154, 1177, 1185, 1340, 1344, 1370

CPC 1288-1290, 1990

D-Sub 1256, 1258, 1275

DIN 1370-1371

Ferrule 1541-1542

IDC 1480, 1530

KK® Series 1480, 1482

MATE-N-LOK 1422-1423, 1425, 1502, 1505, 1507, 1990

MICRO-FIT 1502

Mini and Maxi PV 1165

MINI-FIT JR./SR. 1505, 1507

Modular 1193, 1198, 1465, 1990

MTA Series 1990

MTE Series 1413

Pin and Socket 1340, 1344-1345, 1422-1423, 1425, 1429, 1472-1474, 1502, 1505, 1507, 1990-1991

Pliers 1542

RF 1154-1155, 1165, 1173, 1177, 1185

SL™ 1475

Solderless Terminal 1530, 1532-1533, 1538, 1540

Hooks 1155, 1173, 1193, 1275, 1990

IC Extraction 1520

Keying 1403, 1414, 1418

Knives/Blades 1350

Pliers 1542

Probes 190, 1983, 1988

Semi-Rigid Assembly 1185

Solder/Desolder Accessories/Aids 1540

Staking 1999

Strain Relief 1418, 1828

Termination 1216

Trim Trio™ 1340, 1344

Trimmer Adjustment 693, 695

Wire Strippers 1084, 1542

Transducers

Electromagnetic 1805

Electromechanical 1807

Piezo 1805, 1807

Speaker 1803, 1805, 1811

Surface Mount 1862

Transformers

Audio 1900

Cold Cathode 986

Converter 1899-1900

Current Sense 1045, 1899-1900

Encapsulated 1899-1900

Fluorescent 986

Isolation 993, 1045, 1899-1900

PC Mount 1899-1900, 1902

Power 969, 986, 991, 1899-1902, 1978

Pulse 1899-1900

Signal 1044-1045

Surface Mount 969, 991, 993, 1044-1045, 1899-1900

Toroidal 1899-1900

Transistors (See Semiconductors)

Tubing (See Wire and Cable)

TVS (See Semiconductors)

U

USB

Connectors (See Connectors)

Devices 16, 23, 30-31, 42, 183, 185, 203-204, 207, 251, 303, 379, 528

Host Controllers 30

Interface 16, 23, 28, 30-31, 203-204, 207-208, 249, 251, 270, 303, 306, 330, 379, 528, 1104, 1211

V

Variators 546-549, 552-554, 557

Vibration Sensors 1849, 1864

Video Amplifiers 266, 337, 1145

Voltage

Detectors 343, 378

Reference (See Semiconductors)

Regulators (See Semiconductors)

Suppressors 330, 432, 441, 516, 525-528, 530, 532-536, 538, 540-544, 546-547, 555-556, 558-559, 842

W

Web Server 33

Wi-Fi 11, 23, 38, 41-42

Wire and Cable

Analog 1085

Audio 1075, 1084, 1086

Braided Slewing 1059-1060

Broadcast 1129, 1146

Bus Bar 1079, 1082

Cable Assemblies

Audio 1091, 1146-1147

BNC 1091, 1096, 1146, 1984

Cat 5e 1091, 1192, 1235-1236, 1240-1241, 1243-1244

Cat 6 1091, 1205, 1232

Computer 1089, 1095

Z

ZigBee™ 5, 11, 16-19, 21, 38, 339-340, 928

DC Power 1248

D-Sub 1088, 1095, 1097-1098, 1212-1213, 1252

DMS-59™ 1102

Fiber Optic 1087, 1093-1094, 1205, 1216

Flat Ribbon 1089, 1098, 1511-1512

HDMI 1090, 1102, 1104, 1202, 1205, 1213

High Speed 1088, 1097, 1223, 1227, 1469

IEEE 1394 1101, 1104, 1202, 1205, 1244, 1246

M1 1102

M8 1295, 1338

M12 1241, 1295, 1313, 1338

Mini-D Ribbon 1088

Mini-USB 1101, 1202, 1206, 1208, 1215, 1243

Modular 1192, 1205, 1232, 1236, 1238, 1243-1244

Molded 1089, 1091, 1095, 1984

Patch Cord 1087, 1091, 1147, 1192, 1235, 1240-1241, 1244, 1980, 1985-1986

PCI Express 1227

Phone 1147

RF 1092, 1096, 1099-1100, 1146, 1157, 172, 1181-1182, 1185, 1984

SCSI 1095, 1103, 1220, 1227

Serial ATA (SATA) 1103, 1220, 1227-1228

Shrunk D Ribbon (SDR) 1088

USB 31, 41, 1090-1091, 1097, 1101, 1104, 1192, 1202, 1206, 1208, 1215, 1235, 1238, 1243-1244, 1103, 1212

VHDCI 1103, 1212

XL® 1147

Cable Clamps/Clips 110, 1049, 1051-1054, 1057-1058, 1096, 1248, 1259, 1299-1300, 1342, 1381, 1825, 1829, 1999

Cable Glands 1387, 1870

Cable Mounting 1048-1054, 1057-1059, 1131, 1138, 1230, 1236, 1246, 1250, 1294-1295, 1315, 1317-1318, 1320, 1323, 343, 1368, 1370, 1436, 1980, 1999

Cable Testers 1996

Cable Tie Tools 1049-1050, 1057

Cable Ties 1047-1051, 1054-1057

Camera 1084, 1088

Coaxial 1075, 1083-1085

Communication & Control 49, 110, 1076, 1086, 1626, 1996

Computer 1083, 1089, 1095, 1230

Data 12, 1072, 1088

Fiber Optics 87, 1087, 1093-1094, 1205, 1216, 1237

Flat IDC Ribbon Cable 939, 1070-1074, 1082, 1089, 1098, 1368, 1394, 1437, 1471, 1511-1512, 1514-1515, 1825

Heat Shrink End Caps 1062, 1066

Heat Shrink Tubing 1060-1069

Heat Shrink Woven Fabric 1060, 1068

Hook and Loop Fasteners 1047, 1057

Hook-Up Wire 1077-1081

Hook-Up Wire Kits 1079, 1081

Instrumentation 1086

Lacing Cord and Tape 1074

Local Area Network 1075, 1091

Magnet 1082

Microphone 1075

Modular Telephone 1072

Multi-Conductor 1072, 1075-1076

Multi-Pair 1072-1073, 1076, 1086, 1192

Power Cord 51, 79, 110, 1091, 1244

Shielding & Bonding 1064, 1082, 1208, 1996

Sleeves 1062, 1068

Slewing 1059-1061

Speaker 1086, 1626, 1996

Splices 1068, 1343

SVHS 1085

Telephone 1072, 1074, 1202

Test Lead 1074, 1986

Test Prod. 1081

Tubing

Braid Tubing 1059-1061

Corrugated Loom 1059

CPC/FLEXA 1237, 1293

Fiberglass 1061, 1078

Grommet 1054, 1059

Heat Shrink 1060-1069

Spiral Wrap 1054, 1059, 1061

Video 1075, 1084-1086

Wire Markers 1047, 1049-1050, 1057, 1062

Wire Pulling Lubricant 1047

Wireless

Radio Modules 7, 12-13, 21, 23-24, 176

RF Devices 4-8, 10, 12-13, 16-19, 21, 24-25, 35, 168

Eval Boards 5-7, 13, 18-21, 23-24, 26, 28, 32, 35, 38, 42

Workbench 190