

TE .156" Series IDC Connectors



Specifications:

- Voltage rating: 250VAC
- Current rating: 5A max.
- Low-level resistance: 3mΩ max. initial
- Operating temperature: -55°C to +105°C
- Dielectric withstanding Voltage: 1250VAC/1Min.
- Insulation resistance: 5000MΩ min. initial


Material and Finish:

- Housing: UL94V-2 rated, type 6/6 and 6/12 nylon
- Contacts: Phosphor bronze, post tin plated

Features:

- End to end stackable
- Contacts are lubricated to prevent fretting corrosion
- 156 Centers
- Pre-loaded with contacts

This product is RoHS compliant.



File No. LR7189



File No. E28476



RoHS Compliant

CLOSED END

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	No. of Pos.	Wire Size (AWG)	Color	Price Each		
					1	10	100
With Locking Ramp and Without Tabs							
571-3-640426-2	3-640426-2	2	18	Orange	.32	.27	.261
571-3-640426-3	3-640426-3	3	18	Orange	.33	.271	.215
571-3-640426-4	3-640426-4	4	18	Orange	.47	.425	.301
571-3-640426-5	3-640426-5	5	18	Orange	.61	.554	.472
571-3-640426-6	3-640426-6	6	18	Orange	.62	.562	.398
571-3-640426-7	3-640426-7	7	18	Orange	.67	.593	.425
571-3-640426-8	3-640426-8	8	18	Orange	.93	.89	.769
571-3-640426-9	3-640426-9	9	18	Orange	1.02	.84	.75
571-4-640426-0	4-640426-0	10	18	Orange	.98	.821	.655
571-3-640427-2	3-640427-2	2	20	Yellow	.13	.13	.128
571-3-640427-3	3-640427-3	3	20	Yellow	.40	.38	.23
571-3-640427-4	3-640427-4	4	20	Yellow	.48	.432	.368
571-3-640427-5	3-640427-5	5	20	Yellow	.73	.664	.565
571-3-640427-6	3-640427-6	6	20	Yellow	.80	.70	.60
571-3-640427-7	3-640427-7	7	20	Yellow	.79	.707	.508
571-3-640427-8	3-640427-8	8	20	Yellow	.90	.801	.575
571-3-640428-2	3-640428-2	2	22	Red	.34	.29	.243
571-3-640428-3	3-640428-3	3	22	Red	.40	.34	.28
571-3-640428-4	3-640428-4	4	22	Red	.42	.384	.33
571-3-640428-5	3-640428-5	5	22	Red	.55	.494	.421
571-3-640428-6	3-640428-6	6	22	Red	.70	.66	.50
571-3-640428-7	3-640428-7	7	22	Red	.79	.655	.504
571-3-640428-8	3-640428-8	8	22	Red	1.04	.913	.787
571-4-640428-0	4-640428-0	10	22	Red	1.21	1.11	.85
571-3-640429-2	3-640429-2	2	24	Natural	.40	.39	.27
571-3-640429-3	3-640429-3	3	24	Natural	.41	.301	.215
571-3-640429-4	3-640429-4	4	24	Natural	.43	.385	.272
571-3-640429-5	3-640429-5	5	24	Natural	.48	.427	.307
571-3-640429-6	3-640429-6	6	24	Natural	.67	.626	.479
571-3-640429-8	3-640429-8	8	24	Natural	.69	.603	.44
571-3-640429-9	3-640429-9	9	24	Natural	.80	.73	.521
With Locking Ramp and Tabs							
571-3-643817-2	3-643817-2	2	18	Orange	.29	.25	.241
571-3-643817-3	3-643817-3	3	18	Orange	.39	.359	.306
571-3-643817-4	3-643817-4	4	18	Orange	.45	.366	.351
571-3-643817-5	3-643817-5	5	18	Orange	.56	.51	.38
571-3-643817-6	3-643817-6	6	18	Orange	.68	.57	.49
571-3-643817-7	3-643817-7	7	18	Orange	.61	.541	.385
571-3-643817-8	3-643817-8	8	18	Orange	.80	.70	.55
571-3-643817-9	3-643817-9	9	18	Orange	.82	.731	.529
571-4-643817-0	4-643817-0	10	18	Orange	.83	.696	.552
571-3-643818-2	3-643818-2	2	20	Yellow	.36	.34	.24
571-3-643818-3	3-643818-3	3	20	Yellow	.38	.302	.201
571-3-643818-4	3-643818-4	4	20	Yellow	.49	.45	.35
571-3-643818-5	3-643818-5	5	20	Yellow	.48	.427	.302
571-3-643818-6	3-643818-6	6	20	Yellow	.52	.478	.343
571-3-643818-7	3-643818-7	7	20	Yellow	.64	.567	.408
571-3-643818-8	3-643818-8	8	20	Yellow	.69	.633	.447
571-3-643819-2	3-643819-2	2	22	Red	.36	.34	.24
571-3-643819-3	3-643819-3	3	22	Red	.35	.33	.28
571-3-643819-4	3-643819-4	4	22	Red	.48	.45	.34
571-3-643819-5	3-643819-5	5	22	Red	.47	.427	.305
571-3-643819-6	3-643819-6	6	22	Red	.68	.57	.49
571-3-643819-7	3-643819-7	7	22	Red	.61	.541	.388
571-3-643819-8	3-643819-8	8	22	Red	.69	.613	.446
571-3-643820-2	3-643820-2	2	24	Natural	.22	.198	.159
571-3-643820-3	3-643820-3	3	24	Natural	.43	.39	.30
571-3-643820-4	3-643820-4	4	24	Natural	.34	.322	.229
571-3-643820-5	3-643820-5	5	24	Natural	.47	.426	.301
571-3-643820-6	3-643820-6	6	24	Natural	.51	.492	.355
Without Locking Ramp and Without Tabs							
571-3-640431-2	3-640431-2	2	18	Orange	.34	.259	.183
571-3-640431-3	3-640431-3	3	18	Orange	.42	.302	.216
571-3-640431-4	3-640431-4	4	18	Orange	.51	.48	.368
571-3-640431-5	3-640431-5	5	18	Orange	.48	.427	.302
571-3-640431-6	3-640431-6	6	18	Orange	.52	.478	.343
571-3-640431-7	3-640431-7	7	18	Orange	.61	.567	.405
571-3-640431-8	3-640431-8	8	18	Orange	.73	.611	.468
571-3-640431-9	3-640431-9	9	18	Orange	.76	.632	.521
571-3-640433-2	3-640433-2	2	22	Red	.32	.24	.194
571-3-640433-3	3-640433-3	3	22	Red	.44	.317	.226
571-3-640433-4	3-640433-4	4	22	Red	.41	.381	.267
571-3-640433-5	3-640433-5	5	22	Red	.49	.447	.316
571-3-640433-6	3-640433-6	6	22	Red	.53	.467	.334
571-3-640433-7	3-640433-7	7	22	Red	.64	.567	.408
571-3-640433-8	3-640433-8	8	22	Red	.72	.61	.466
571-3-640433-9	3-640433-9	9	22	Red	.82	.731	.527
571-4-640433-0	4-640433-0	10	22	Red	.86	.696	.555

FEED-THRU

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	No. of Pos.	Wire Size (AWG)	Color	Price Each		
					1	10	100
With Locking Ramp and Without Tabs (Cont.)							
571-3-640599-2	3-640599-2	2	18	Orange	.42	.366	.299
571-3-640599-3	3-640599-3	3	18	Orange	.38	.34	.28
571-3-640599-4	3-640599-4	4	18	Orange	.66	.619	.474
571-3-640599-5	3-640599-5	5	18	Orange	.52	.468	.326
571-3-640599-6	3-640599-6	6	18	Orange	.53	.491	.354
571-3-640599-7	3-640599-7	7	18	Orange	.63	.567	.403
571-3-640599-8	3-640599-8	8	18	Orange	.70	.624	.448
571-3-640599-9	3-640599-9	9	18	Orange	.79	.697	.502
571-4-640599-0	4-640599-0	10	18	Orange	.84	.697	.553
571-3-640600-2	3-640600-2	2	20	Yellow	.33	.25	.209
571-3-640600-3	3-640600-3	3	20	Yellow	.34	.312	.219
571-3-640600-4	3-640600-4	4	20	Yellow	.43	.406	.281
571-3-640600-5	3-640600-5	5	20	Yellow	.47	.436	.308
571-3-640600-6	3-640600-6	6	20	Yellow	.76	.71	.54
571-3-640600-7	3-640600-7	7	20	Yellow	.64	.567	.408
571-3-640600-8	3-640600-8	8	20	Yellow	.70	.634	.448
571-3-640600-9	3-640600-9	9	20	Yellow	.79	.73	.522
571-3-640601-2	3-640601-2	2	22	Red	.30	.28	.20
571-3-640601-3	3-640601-3	3	22	Red	.37	.323	.233
571-3-640601-4	3-640601-4	4	22	Red	.39	.333	.26
571-3-640601-5	3-640601-5	5	22	Red	.48	.425	.32
571-3-640601-6	3-640601-6	6	22	Red	.64	.63	.44
571-3-640601-7	3-640601-7	7	22	Red	.62	.541	.39
571-3-640601-8	3-640601-8	8	22	Red	.69	.633	.447
571-3-640601-9	3-640601-9	9	22	Red	.82	.731	.527
571-4-640601-0	4-640601-0	10	22	Red	.86	.738	.546
571-3-640602-2	3-640602-2	2	24	Natural	.31	.229	.159
571-3-640602-3	3-640602-3	3	24	Natural	.32	.29	.22
571-3-640602-4	3-640602-4	4	24	Natural	.41	.364	.256
571-3-640602-5	3-640602-5	5	24	Natural	.49	.43	.30
571-3-640602-6	3-640602-6	6	24	Natural	.51	.468	.338
571-3-640602-7	3-640602-7	7	24	Natural	.64	.567	.408
571-3-640602-8	3-640602-8	8	24	Natural	.80	.70	.605
571-3-640602-9	3-640602-9	9	24	Natural	.76	.685	.496
571-4-640602-0	4-640602-0	10	24	Natural	.87	.664	.579
With Locking Ramp and Tabs							
571-3-644465-2	3-644465-2	2	18	Orange	.31	.219	.149
571-3-644465-3	3-644465-3	3	18	Orange	.34	.323	.236
571-3-644465-4	3-644465-4	4	18	Orange	.39	.343	.247
571-3-644465-5	3-644465-5	5	18	Orange	.47	.426	.306
571-3-644465-6	3-644465-6	6	18	Orange	.54	.488	.344
571-3-644465-7	3-644465-7	7	18	Orange	.65	.578	.409
571-3-644465-8	3-644465-8	8	18	Orange	.72	.654	.467
571-3-644465-9	3-644465-9	9	18	Orange	.80		