

KEYSTONE PTFE Insulated Terminals, Pins & Test Points



This product is RoHS compliant.

Features:

- Outstanding Electrical, Mechanical, Thermal and Chemical properties.
- Provides greater pull-out strength and high torque resistance
- Ideal for high quality terminal and connector applications
- Custom PTFE jacks manufactured to your specifications
- Other platings and bushing colors available upon request
- Space saving design for high density packaging

SPLIT-TYPE FORK TURRETS

Bushing: White PTFE RoHS
Terminal: Brass, Tin Plate



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Fig.	Dimensions: in. (mm)						Price Each			
			A	B	C	E	R	Mtg. Hole Dia.	1	100	500	1000
534-11100	11100	A	.172 (4.4)	.148 (3.8)	.125 (3.2)	.250 (6.4)	.125 (3.2)	.136 (3.5)	.94	.909	.863	.828
534-11111	11111	A	.187 (4.8)	.171 (4.3)	.150 (3.8)	.390 (9.9)	.148 (3.8)	.158 (4.0)	1.25	1.18	1.11	1.08
534-11112	11112	A	.187 (4.8)	.171 (4.3)	.150 (3.8)	.453 (11.5)	.148 (3.8)	.158 (4.0)	1.31	1.24	1.19	1.13
534-11113	11113	A	.187 (4.8)	.171 (4.3)	.150 (3.8)	.328 (8.3)	.148 (3.8)	.158 (4.0)	1.25	1.18	1.11	1.08
534-11114	11114	A	.187 (4.8)	.171 (4.3)	.150 (3.8)	.390 (9.9)	.148 (3.8)	.158 (4.0)	2.32	1.47	1.02	.887
534-11115	11115	A	.187 (4.8)	.171 (4.3)	.150 (3.8)	.453 (11.5)	.148 (3.8)	.158 (4.0)	1.39	1.33	1.27	1.20
534-11116	11116	B	.187 (4.8)	.171 (4.3)	.212 (5.4)	.390 (9.9)	.148 (3.8)	.158 (4.0)	1.33	1.27	1.21	1.15

THREADED TURRET TERMINALS

Bushing: White PTFE RoHS
Terminal: Brass, Tin Plate



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Fig.	Thread	Dimensions: in. (mm)					Price Each			
				Hex	C	E	L	R	1	100	500	1000
534-11350	11350	C	2-56	.156 (3.9)	.206 (5.2)	.360 (9.1)	.125 (3.2)	.062 (1.6)	1.78	1.67	1.59	1.52
534-11351	11351	C	4-40	.270 (6.9)	.270 (6.9)	.510 (12.9)	.250 (6.4)	.094 (2.4)	3.08	2.32	2.10	1.98
534-11352	11352	C	6-32	.250 (6.4)	.270 (6.9)	.510 (12.9)	.375 (9.5)	.094 (2.4)	2.07	1.95	1.87	1.77

THREADED FEED-THRU TERMINALS

Bushing: White PTFE
Terminal: Brass, Tin Plate
Body: Brass, Nickel Plate
 * Nut and washer supplied unassembled



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Fig.	Thread	Dimensions: in. (mm)					Price Each			
				Hex	C	E	L	R	1	100	500	1000
534-11360	11360	D	4-40	.156 (4.0)	.235 (6.0)	.355 (9.0)	.200 (5.1)	.032 (0.8)	3.21	3.03	2.91	2.75
534-11361	11361	D	4-40	.156 (4.0)	.235 (6.0)	.405 (10.3)	.250 (6.4)	.032 (0.8)	3.53	3.35	3.19	3.03
534-11362	11362	D	12-28	.250 (6.4)	.287 (7.3)	.287 (7.3)	.403 (10.2)	.082 (2.1)	3.31	2.86	2.72	2.59
534-11363	11363	E	10-32	.312 (7.9)	.250 (6.4)	.425 (10.8)	.565 (14.3)	.062 (1.6)	3.57	3.27	2.87	2.03
534-11364	11364	E	6-32	.188 (4.8)	.250 (6.4)	.368 (9.3)	.510 (12.9)	.040 (1.0)	4.30	3.71	3.53	3.35


TEST POINT JACKS

Bushing: White PTFE (RoHS Compliant), Red or Black (Non-RoHS Compliant)
Terminal Jack: Beryllium Copper (QQ-C-533)
Plating: Gold per Mil-G-45204, Type II



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Fig.	RoHS White	NON-RoHS		Dimensions: in. (mm)										Price Each			
				Red	Black	A	B	C	D	E	R	Probe Dia. ±.001 (.03)	Probe Length	1	100	500	1000		
534-11001	11001	F	yes	--	--	.142 (3.6)	.120 (3.0)	.244 (6.2)	.046 (1.2)	.120 (3.0)	.060 (1.5)	.040 (1.0)	.205 (5.2)	1.81	1.71	1.62	1.55		
534-11002	11002	F	yes	--	--	.142 (3.6)	.120 (3.0)	.283 (7.2)	.046 (1.2)	.120 (3.0)	.060 (1.5)	.040 (1.0)	.245 (6.2)	2.20	2.08	2.00	1.89		
534-11003	11003	F	yes	--	--	.172 (4.4)	.140 (3.6)	.142 (3.6)	.050 (1.3)	.060 (1.5)	.080 (2.0)	.040 (1.0)	.125 (3.2)	2.06	1.95	1.87	1.77		
534-11004	11004	F	yes	--	--	.172 (4.4)	.148 (3.8)	.179 (4.5)	.046 (1.2)	.120 (3.0)	.060 (1.5)	.040 (1.0)	.140 (3.6)	2.07	1.97	1.86	1.77		
534-11005	11005	F	yes	--	--	.218 (5.5)	.185 (4.7)	.301 (7.6)	.050 (1.3)	.105 (2.7)	.125 (3.2)	.080 (2.0)	.315 (8.0)	2.13	2.01	1.91	1.81		
534-11006	11006	F	yes	--	--	.218 (5.5)	.185 (4.7)	.271 (6.9)	.046 (1.2)	.120 (3.0)	.074 (1.9)	.080 (2.0)	.195 (4.9)	2.47	2.34	2.07	1.95		
534-11007	11007	F	yes	--	--	.218 (5.5)	.185 (4.7)	.271 (6.9)	.046 (1.2)	.120 (3.0)	.074 (1.9)	.090 (2.3)	.195 (4.9)	2.53	2.42	2.28	2.17		
534-11008	11008	F	yes	--	--	.218 (5.5)	.185 (4.7)	.301 (7.6)	.046 (1.2)	.120 (3.0)	.074 (1.9)	.080 (2.0)	.225 (5.7)	2.20	2.11	1.99	1.88		
534-11009	11009	F	yes	--	--	.218 (5.5)	.185 (4.7)	.400 (10.2)	.050 (1.3)	.187 (4.8)	.074 (1.9)	.080 (2.0)	.280 (7.1)	1.97	1.88	1.78	1.69		
534-11010	11010	F	yes	--	--	.218 (5.5)	.185 (4.7)	.271 (6.9)	.046 (1.2)	.136 (3.5)	.074 (1.9)	.080 (2.0)	.340 (8.6)	2.20	2.10	1.99	1.89		
534-11011	11011	G	yes	--	--	.218 (5.5)	--	.430 (10.9)	--	.150 (3.8)	.050 (1.3)	.080 (2.0)	.200 (5.1)	2.59	2.45	2.17	2.04		
534-11011-B	11011-B	G	--	yes	--	.218 (5.5)	--	.430 (10.9)	--	.150 (3.8)	.050 (1.3)	.080 (2.0)	.200 (5.1)	4.14	3.93	3.73	3.53		
534-11012	11012	G	yes	--	--	.218 (5.5)	--	.500 (12.7)	--	.150 (3.8)	.050 (1.3)	.080 (2.0)	.280 (7.1)	2.37	2.25	2.14	2.02		
534-11012-B	11012-B	G	--	yes	--	.218 (5.5)	--	.500 (12.7)	--	.150 (3.8)	.050 (1.3)	.080 (2.0)	.280 (7.1)	2.47	2.34	2.07	1.95		
534-11012-R	11012-R	G	--	yes	--	.218 (5.5)	--	.500 (12.7)	--	.150 (3.8)	.050 (1.3)	.080 (2.0)	.280 (7.1)	2.78	2.63	2.31	2.19		
534-11013	11013	H	yes	--	--	.218 (5.5)	.187 (4.8)	.689 (17.5)	.500 (12.7)	.125 (3.2)	.050 (1.3)	.080 (2.0)	.500 (12.7)	3.95	3.75	3.56	3.37		
534-11014	11014	H	yes	--	--	.218 (5.5)	.187 (4.8)	.378 (9.6)	.400 (10.2)	.125 (3.2)	.050 (1.3)	.080 (2.0)	.250 (6.4)	3.12	2.97	2.82	2.67		
534-11015	11015	H	yes	--	--	.218 (5.5)	.187 (4.8)	.378 (9.6)	.400 (10.2)	.187 (4.7)	.035 (.89)	.080 (2.0)	.250 (6.4)	3.47	3.30	3.13	2.98		
534-11016	11016	H	yes	--	--	.218 (5.5)	.187 (4.8)	.378 (9.6)	.500 (12.7)	.125 (3.2)	.050 (1.3)	.080 (2.0)	.250 (6.4)	3.30	3.15	2.98	2.83		



Terminals
Keystone