


TE Mini-Universal MATE-N-LOK® Headers



RoHS Compliant This product is RoHS compliant.



TE Mini-Universal MATE-N-LOK® connectors provide a highly reliable and economic means of grouping multiple-lead connections in today's computer, computer/peripheral equipment, business machines, entertainment centers, appliances, and other sophisticated commercial equipment. The electrical connector is an integral component in these applications. They also offer worldwide application approval because of their reliability and economy. Electrical functions have increased in complexity and new designs continually call for the maximum use of space. The Mini-Universal MATE-N-LOK® family of connectors offers the design and features to answer these modern industry requirements.

- Features:**
- Nylon white housing
 - PCB thru mount
 - UL94V-0 flammability rated material
 - Fully polarized
- Specifications:**
- Voltage rating: 600V AC or DC
 - Current: 9.5A

VERTICAL HEADERS WITH DRAIN HOLES



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Contacts	Description	Finish	Price Each		
						1	25	100
571-1-770166-0	1-770166-0	A	2	In-Line	Tin	.85	.80	.73
571-1-770166-1	1-770166-1	A	2	In-Line	Gold	1.30	1.22	1.11
571-1-770170-0	1-770170-0	A	3	In-Line	Tin	1.05	.876	.795
571-1-770170-1	1-770170-1	A	3	In-Line	Gold	2.19	1.86	1.70
571-1-770174-0	1-770174-0	A	4	Dual Row	Tin	1.19	1.12	1.02
571-1-770174-1	1-770174-1	A	4	Dual Row	Gold	1.97	1.67	1.52
571-1-770178-0	1-770178-0	A	6	Dual Row	Tin	1.38	1.14	1.05
571-1-770178-1	1-770178-1	A	6	Dual Row	Gold	2.58	2.27	2.07
571-1-794065-0	1-794065-0	A	8	Dual Row	Tin	2.07	1.76	1.60
571-1-794065-1	1-794065-1	A	8	Dual Row	Gold	2.67	2.54	2.45
571-1-770182-0	1-770182-0	A	9	Matrix	Tin	1.98	1.68	1.54
571-1-770182-1	1-770182-1	A	9	Matrix	Gold	5.12	4.50	4.09
571-1-770743-0	1-770743-0	A	10	Dual Row	Tin	2.32	1.97	1.80
571-1-770743-1	1-770743-1	A	10	Dual Row	Gold	3.68	3.23	2.94
571-1-770186-0	1-770186-0	A	12	Matrix	Tin	1.95	1.61	1.47
571-1-770186-1	1-770186-1	A	12	Matrix	Gold	6.07	5.03	4.30
571-1-794066-0	1-794066-0	A	12	Dual Row	Tin	2.22	1.88	1.72
571-1-794066-1	1-794066-1	A	12	Dual Row	Gold	3.39	3.21	3.02
571-1-794067-0	1-794067-0	A	14	Dual Row	Tin	2.34	1.48	1.38
571-1-794067-1	1-794067-1	A	14	Dual Row	Gold	4.99	4.48	4.23
571-1-770190-0	1-770190-0	A	15	Matrix	Tin	2.67	2.21	1.92
571-1-794068-0	1-794068-0	A	16	Dual Row	Tin	2.82	2.47	2.25
571-1-794068-1	1-794068-1	A	16	Dual Row	Gold	4.80	4.32	4.06
571-1-794069-0	1-794069-0	A	18	Dual Row	Tin	2.84	2.26	2.02
571-1-794069-1	1-794069-1	A	18	Dual Row	Gold	5.62	5.28	4.75
571-1-794070-0	1-794070-0	A	20	Dual Row	Tin	3.38	2.85	2.48
571-1-794070-1	1-794070-1	A	20	Dual Row	Gold	9.30	8.15	6.80
571-1-794071-1	1-794071-1	A	22	Dual Row	Gold	11.18	9.94	8.30
571-1-794072-0	1-794072-0	A	24	Dual Row	Tin	3.97	2.51	2.50
571-1-794072-1	1-794072-1	A	24	Dual Row	Gold	13.52	12.16	10.81

VERTICAL HEADERS WITHOUT DRAIN HOLES (CONT.)

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Contacts	Description	Finish	Price Each		
						1	25	100
571-1-794075-0	1-794075-0	A	16	Dual Row	Tin	2.98	2.68	2.13
571-1-794075-1	1-794075-1	A	16	Dual Row	Gold	9.55	8.62	7.10
571-1-794076-0	1-794076-0	A	18	Dual Row	Tin	3.41	3.08	2.69
571-1-794077-0	1-794077-0	A	20	Dual Row	Tin	3.41	3.06	2.51
571-1-794077-1	1-794077-1	A	20	Dual Row	Gold	8.30	7.46	6.75
571-1-794078-0	1-794078-0	A	22	Dual Row	Tin	3.39	3.03	2.73
571-1-794078-1	1-794078-1	A	22	Dual Row	Gold	8.39	7.54	6.91
571-1-794079-0	1-794079-0	A	24	Dual Row	Tin	3.86	3.46	3.03
571-1-794079-1	1-794079-1	A	24	Dual Row	Gold	9.72	8.75	7.93

RIGHT ANGLE HEADERS WITH BOARD LOCK



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Contacts	Description	Finish	Price Each		
						1	25	100
571-1-770966-0	1-770966-0	B	2	In-Line	Tin	.77	.69	.669
571-1-770966-1	1-770966-1	B	2	In-Line	Gold	2.32	1.97	1.80
571-1-770967-0	1-770967-0	B	3	In-Line	Tin	1.25	1.16	1.06
571-1-770967-1	1-770967-1	B	3	In-Line	Gold	3.55	3.12	2.84
571-1-770968-0	1-770968-0	B	4	Dual Row	Tin	1.37	1.13	1.03
571-1-770968-1	1-770968-1	B	4	Dual Row	Gold	3.62	3.19	2.89
571-1-770969-0	1-770969-0	B	6	Dual Row	Tin	1.63	1.38	1.26
571-1-770969-1	1-770969-1	B	6	Dual Row	Gold	4.43	3.89	3.54
571-1-770970-0	1-770970-0	B	8	Dual Row	Tin	1.92	1.60	1.26
571-1-770970-1	1-770970-1	B	8	Dual Row	Gold	5.83	5.13	4.66
571-1-770971-0	1-770971-0	B	10	Dual Row	Tin	2.87	2.52	2.29
571-1-770971-1	1-770971-1	B	10	Dual Row	Gold	8.02	7.02	6.35
571-1-770972-0	1-770972-0	B	12	Dual Row	Tin	2.56	2.29	1.68
571-1-770972-1	1-770972-1	B	12	Dual Row	Gold	7.45	6.63	5.83
571-1-770973-0	1-770973-0	B	14	Dual Row	Tin	5.53	4.41	3.49
571-1-770973-1	1-770973-1	B	14	Dual Row	Gold	9.92	8.69	7.13
571-1-770974-0	1-770974-0	B	16	Dual Row	Tin	2.34	2.30	1.95
571-1-794105-0	1-794105-0	B	18	Dual Row	Tin	6.55	5.13	4.14
571-1-794106-0	1-794106-0	B	20	Dual Row	Tin	4.49	3.93	3.19
571-1-794106-1	1-794106-1	B	20	Dual Row	Gold	12.89	11.58	10.14
571-1-794107-0	1-794107-0	B	22	Dual Row	Tin	5.44	4.89	3.89
571-1-794108-0	1-794108-0	B	24	Dual Row	Tin	5.23	4.52	3.76
571-1-794108-1	1-794108-1	B	24	Dual Row	Gold	20.21	17.70	15.10

VERTICAL HEADERS WITHOUT DRAIN HOLES



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	No. of Contacts	Description	Finish	Price Each		
						1	25	100
571-1-770872-0	1-770872-0	A	2	In-Line	Tin	.85	.70	.64
571-1-770872-1	1-770872-1	A	2	In-Line	Gold	1.60	1.36	1.24
571-1-770873-0	1-770873-0	A	3	In-Line	Tin	1.05	.86	.79
571-1-770873-1	1-770873-1	A	3	In-Line	Gold	1.76	1.57	1.42
571-1-770874-0	1-770874-0	A	4	Dual Row	Tin	1.29	1.07	.98
571-1-770874-1	1-770874-1	A	4	Dual Row	Gold	2.43	2.29	2.08
571-1-770875-0	1-770875-0	A	6	Dual Row	Tin	1.51	1.36	1.13
571-1-770875-1	1-770875-1	A	6	Dual Row	Gold	3.55	3.12	2.84
571-1-794073-0	1-794073-0	A	8	Dual Row	Tin	1.67	1.50	1.21
571-1-794073-1	1-794073-1	A	8	Dual Row	Gold	4.08	3.65	3.41
571-1-770876-0	1-770876-0	A	9	Matrix	Tin	2.36	2.11	1.99
571-1-770858-1	1-770858-1	A	10	Dual Row	Gold	5.78	4.62	4.14
571-1-794040-0	1-794040-0	A	12	Matrix	Tin	1.72	1.56	1.35
571-1-770621-0	1-770621-0	A	12	Dual Row	Tin	1.49	1.36	1.18
571-1-770621-1	1-770621-1	A	12	Dual Row	Gold	4.41	3.98	3.59
571-1-794074-0	1-794074-0	A	14	Dual Row	Tin	2.70	2.43	1.93
571-1-794074-1	1-794074-1	A	14	Dual Row	Gold	8.91	7.17	6.50

TOOLS

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Description	Price Each
571-1897271	189727-1	C	Contact Extraction Tool	26.06
571-4558301	455830-1	D	Contact Insertion Tool	20.77
571-908701	90870-1	E	Pro-Crimper III with Die, 30-24 AWG	267.45
571-90758-1	90758-1	E	Pro-Crimper III with Die, 26-22 AWG	217.30
571-90759-1	90759-1	E	Pro-Crimper III with Die, 22-18 AWG	217.30