

# PHOENIX CONTACT Cipline DIN Rail Terminal Blocks



RoHS Compliant This product is RoHS compliant.

## PUSH-IN CONNECTION TECHNOLOGY TERMINAL BLOCKS

Push-in connection technology are modular terminal blocks that require 50% lower insertion force and create user friendly wiring. As part of the CLIPLINE Complete family, these terminal blocks use standard system accessories, including bridging and marking.

### Features:


- Push-in technology makes wiring easy and reduces fatigue
- Compatible with Cipline Complete accessories
- Front connection for space-saving convenient wiring
- Three standard marker grooves
- No special tooling required
- Actuation button
- Touch-proof design



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Fig.	Phoenix Type	Color	AWG	Voltage Rating	Current Rating	Dimensions (mm)			Price Each			
							W	L	H	1	10	50	100
<b>2-Conductor Terminal Blocks</b>													
651-3209510	A	PT 2.5	Gray	26-14	800	30A	5.2	48.5	36.5	1.35	1.20	1.08	1.01
651-3209523	A	PT 2.5 BU	Blue	26-14	800	30A	5.2	48.5	36.5	1.34	1.18	1.08	.993
651-3209536	A	PT 2.5-PE	Grn/Yel	26-14	-	-	5.2	48.5	36.5	4.51	4.01	3.64	3.39
<b>3-Conductor Terminal Blocks</b>													
651-3209549	A	PT 2.5-TWIN	Gray	26-14	800	30A	5.2	60.5	36.5	1.51	1.35	1.22	1.14
651-3209552	A	PT 2.5-TWIN BU	Blue	26-14	800	30A	5.2	60.5	36.5	1.63	1.46	1.32	1.23
651-3209565	A	PT 2.5-TWIN-PE	Grn/Yel	26-14	-	-	5.2	60.5	36.5	5.32	4.73	4.30	3.99
<b>4-Conductor Terminal Blocks</b>													
651-3209578	A	PT 2.5-QUATT RO	Gray	26-14	800	30A	5.2	72	36.5	2.18	1.94	1.77	1.65
651-3209581	A	PT 2.5-QUATT RO BU	Blue	26-14	800	30A	5.2	72	36.5	2.18	1.94	1.77	1.65
651-3209594	A	PT 2.5-QUATT RO-PE	Grn/Yel	26-14	-	-	5.2	72	36.5	6.88	6.11	5.56	5.17
<b>Double-level Terminal Blocks</b>													
651-3210567	B	PTTB 2.5	Gray	26-14	500	26A	5.2	68	47.5	3.10	2.76	2.50	2.33
651-3210570	B	PTTB 2.5 BU	Blue	26-14	500	26A	5.2	68	47.5	3.21	2.86	2.59	2.42
651-3210583	B	PTTB 2.5-PV	Gray	26-14	500	26A	5.2	68	47.5	6.62	5.88	5.35	4.97
651-3210596	B	PTTB 2.5-PE	Grn/Yel	26-14	-	-	5.2	68	47.5	9.43	8.40	7.63	7.09
651-3210978	B	PTTB 2.5-PE/L	Grn/Yel	26-14	-	-	5.2	68	47.5	5.90	5.25	4.76	4.43
651-3210981	B	PTTB 2.5-PE/N	Grn/Yel	26-14	-	-	5.2	68	47.5	6.61	5.88	5.34	4.96
651-3210994	B	PTTB 2.5-L/N	Gray	26-14	500	26A	5.2	68	47.5	3.82	3.40	3.09	2.88
<b>Double-level Terminal Blocks - Angled Design</b>													
651-3209604	B	PTTBS 2.5	Gray	26-14	500	26A	5.2	78	55	3.10	2.76	2.50	2.33
651-3209617	B	PTTBS 2.5 BU	Blue	26-14	500	26A	5.2	78	55	3.43	3.04	2.76	2.57
651-3210211	B	PTTBS 2.5-PV	Gray	26-14	500	26A	5.2	78	55	6.96	6.19	5.63	5.23
651-3209620	B	PTTBS 2.5-PE	Grn/Yel	26-14	-	-	5.2	78	55	9.61	8.55	7.77	7.22
<b>Three-level Terminal Blocks</b>													
651-3210499	C	PT 2.5-3L	Gray	26-14	500	26A	5.2	102	58	5.24	4.67	4.24	3.94
651-3210509	C	PT 2.5-3L BU	Blue	26-14	500	26A	5.2	102	58	5.24	4.67	4.24	3.94
651-3210512	C	PT 2.5-3PV	Gray	26-14	500	26A	5.2	102	58	8.71	7.74	7.04	6.54
651-3210525	C	PT 2.5-3PE	Grn/Yel	26-14	-	-	5.2	102	58	11.46	10.87	10.33	9.82
651-3210538	C	PT 2.5-PE/L/N	Grn/Yel	26-14	-	-	5.2	102	58	8.62	7.67	6.96	6.47
651-3210541	C	PT 2.5-PE/L/L	Grn/Yel	26-14	-	-	5.2	102	58	8.00	7.12	6.47	6.02
<b>Knife / Disconnect Terminal Blocks</b>													
651-3210156	D	PT 2.5-MT	Gray	26-14	400	20A	5.2	60.5	36.5	4.14	3.68	3.34	3.11
651-3210169	D	PT 2.5-TWIN-MT	Gray	26-14	400	20A	5.2	74	55	4.64	4.12	3.76	3.49
651-3211663	D	PT 2.5-TWIN-MT BU	Blue	26-14	400	20A	5.2	74	55	4.64	4.12	3.76	3.49
651-3210172	D	PT 2.5-QUATT RO-MT	Gray	26-14	400	20A	5.2	78	55	5.28	4.69	4.27	3.96
651-3211676	D	PT2.5-QUATTROMT BU	Blue	26-14	400	20A	5.2	78	55	5.28	4.69	4.27	3.96
<b>Disconnect Terminal Blocks</b>													
651-3210185	E	PT 2.5-TG	Gray	26-14	400	20A	5.2	60.5	36.5	2.64	2.35	2.14	1.98
651-3210198	E	PT 2.5-TWIN-TG	Gray	26-14	400	20A	5.2	74	36.5	3.14	2.80	2.54	2.36
651-3210208	E	PT 2.5-QUATT RO-TG	Gray	26-14	400	20A	5.2	84	36.5	3.76	3.34	3.03	2.82
<b>COMBI Double-level Terminal Blocks</b>													
651-3210871	F	PTTB 2.5/2P	Gray	26-14	500	22A	5.2	71.5	47.5	3.20	2.85	2.58	2.41
651-3210884	F	PTTB 2.5/2P BU	Blue	26-14	500	22A	5.2	71.5	47.5	3.20	2.85	2.58	2.41
651-3210907	F	PTTB 2.5/2P-PV	Gray	26-14	500	22A	5.2	71.5	47.5	6.63	5.91	5.36	4.98
651-3210897	F	PTTB 2.5/2P-PE	Grn/Yel	26-14	-	-	5.2	71.5	47.5	8.81	7.84	7.12	6.62
<b>Diode Terminal Blocks</b>													
651-3210224	G	PT 2.5-DIO/L-R	Gray	26-14	800	0.5A	5.2	48.5	36.5	5.61	4.99	4.53	4.21
651-3210237	G	PT 2.5-DIO/R-L	Gray	26-14	800	0.5A	5.2	48.5	36.5	7.58	7.20	6.83	6.50
651-3210240	G	PT2.5-TWIN-DIO/L-R	Gray	26-14	800	0.5A	5.2	48.5	36.5	5.92	5.28	4.79	4.46
651-3210253	G	PT2.5-TWIN-DIO/R-L	Gray	26-14	800	0.5A	5.2	48.5	36.5	5.92	5.28	4.79	4.46
651-3210266	G	PT2.5QUATTRODIOL-R	Gray	26-14	800	0.5A	5.2	48.5	36.5	6.00	5.34	4.84	4.51
651-3210279	G	PT2.5QUATTRODIOR-L	Gray	26-14	800	0.5A	5.2	48.5	36.5	6.00	5.34	4.84	4.51
<b>Diode Terminal Blocks - Double Level</b>													
651-3210923	G	PTTB 2.5-DIO/O-U	Gray	26-14	800	0.5A	5.2	68	47.5	7.24	6.44	5.86	5.44
651-3210936	G	PTTB 2.5-DIO/U-O	Gray	26-14	800	0.5A	5.2	68	47.5	7.24	6.44	5.86	5.44
651-3211427	G	PTTB2.5-DIO/UL-UR	Gray	26-14	800	0.5A	5.2	68	47.5	7.43	6.60	6.01	5.58
651-3211430	G	PTTB2.52DIOOULURUL	Gray	26-14	800	0.5A	5.2	68	47.5	10.20	9.35	8.64	8.03
651-3211443	G	PTTB2.52DIOOULOUR	Gray	26-14	800	0.5A	5.2	68	47.5	10.19	9.34	8.63	8.02
651-3210282	G	PTTBS 2.5-DIO/O-U	Gray	26-14	800	0.5A	5.2	68	47.5	7.43	6.60	6.01	5.58
651-321295	G	PTTBS 2.5-DIO/U-O	Gray	26-14	800	0.5A	5.2	68	47.5	7.24	6.44	5.86	5.44
<b>Double-level Light Indicator Terminal Blocks</b>													
651-3211456	H	PTTB 2.5-LA 24 RD	Gray	26-14	24	26A	5.2	68	47.5	10.19	9.34	8.63	8.02
651-3211469	H	PTTB 2.5-LA 60 RD	Gray	26-14	24	26A	5.2	68	47.5	10.19	9.34	8.63	8.02
651-3211472	H	PTTB 2.5-LA 230	Gray	26-14	24	26A	5.2	68	47.5	10.08	9.24	8.54	7.94



Phoenix Contact Terminal Blocks