

# KEYSTONE LED Holders and Spacer Mounts



LED Indication

Keystone

## "SNAP-IN" T-1 AND T-1 3/4 LED HOLDERS

Material: Nylon 6/6, Black

MOUSER STOCK NO. Mfr.   Mfr. Part No.	Fig.	LED Size	Color	Mounting Hole Size	Min. Mounting Center	Panel Thickness	Price Each			
							1	100	500	1000
534-8309	A	T-1	0.114	0.232	0.188	0.171	.21	.18	.176	.135
534-8310	B	T-1 3/4	0.20	0.315	0.274	0.25	.45	.37	.24	.16

For quantities greater than listed, call for quote.

## "UNIVERSAL" SPACER MOUNTS FOR TRI-LEAD T-1 (3MM) AND T-1 3/4 (5MM)

- Unique design separate leads and retains Tri-Lead (and/or Bi-Lead) components
- Provides height control, lead retention and stability
- Designed for PC board mounting of Tri-Lead (and/or Bi-Lead) T-1 and T-1 3/4 LEDs
- Also suitable for mounting lamps, resistors, transistors, diodes, capacitors, etc.
- Material: Black PVC, UL Rated 94V-0

MOUSER STOCK NO. Mfr.   Mfr. Part No.	Fig.	Length "L"	Price Each			MOUSER STOCK NO. Mfr.   Mfr. Part No.	Length "L"	Price Each		
			1	100	500			1	100	500
534-8900	C	0.120	.23	.126	.105	534-8916	0.40	.20	.112	.107
534-8901	C	0.140	.22	.14	.125	534-8917	0.42	.23	.149	.121
534-8902	C	0.160	.23	.128	.106	534-8918	0.44	.18	.125	.108
534-8903	C	0.180	.24	.134	.116	534-8919	0.45	.22	.12	.114
534-8904	C	0.200	.23	.125	.109	534-8920	0.46	.22	.12	.114
534-8905	C	0.220	.21	.13	.114	534-8921	0.48	.23	.128	.121
534-8906	C	0.240	.23	.149	.133	534-8922	0.50	.26	.147	.136
534-8907	C	0.250	.09	.084	.075	534-8923	0.55	.22	.14	.124
534-8908	C	0.260	.22	.12	.10	534-8924	0.60	.22	.14	.124
534-8909	C	0.280	.22	.14	.114	534-8925	0.65	.22	.14	.12
534-8910	C	0.300	.22	.12	.104	534-8926	0.70	.22	.14	.124
534-8911	C	0.320	.23	.146	.13	534-8927	0.75	.22	.14	.124
534-8912	C	0.340	.25	.145	.126	534-8928	0.80	.22	.16	.124
534-8913	C	0.350	.23	.13	.114	534-8929	0.85	.25	.179	.138
534-8914	C	0.360	.24	.136	.119	534-8930	0.90	.25	.179	.138
534-8915	C	0.380	.23	.146	.13	534-8931	0.95	.24	.171	.132

## "SELF-ALIGNING" SPACER MOUNTS FOR BI-LEAD T-1 (3MM) AND T-1 3/4 (5MM)

- The spacer features an internally tapered barrier which guides the leads and eliminates the possibility of crimping and shorting. The internal configuration also assures positive self-alignment on .100 centers.
- No special tools required
- Material: Natural Nylon
- Cost and labor saving
- UL Rated 94V-2

MOUSER STOCK NO. Mfr.   Mfr. Part No.	Fig.	Length "L"	"A" Ref	Price Each		
				1	100	500
<b>T-1 3/4</b>						
534-8311	D	0.120	0.045	.18	.10	.093
534-8312	D	0.140	0.065	.18	.10	.09
534-8313	D	0.160	0.085	.19	.107	.099
534-8314	D	0.180	0.105	.19	.107	.099
534-8315	D	0.200	0.125	.18	.10	.09
534-8316	D	0.220	0.145	.18	.10	.093
534-8317	D	0.240	0.045	.18	.104	.097
534-8318	D	0.250	0.060	.18	.09	.08
534-8319	D	0.260	0.065	.19	.107	.099
534-8320	D	0.280	0.090	.18	.09	.083
534-8321	D	0.300	0.110	.19	.106	.099
534-8322	D	0.320	0.120	.19	.099	.077
534-8323	D	0.340	0.140	.19	.096	.088
534-8324	D	0.350	0.150	.18	.10	.093
534-8325	D	0.360	0.160	.18	.10	.09
534-8326	D	0.380	0.060	.18	.10	.093
534-8327	D	0.40	0.08	.18	.10	.093
534-8328	D	0.42	0.10	.19	.106	.096
534-8329	D	0.44	0.12	.19	.106	.099
534-8330	D	0.45	0.12	.18	.10	.093
534-8331	D	0.46	0.14	.19	.106	.099
534-8332	D	0.48	0.15	.18	.10	.093
534-8333	D	0.50	0.06	.18	.10	.093
534-8334	D	0.55	0.10	.18	.10	.093
534-8335	D	0.60	0.15	.18	.10	.093
534-8336	D	0.65	0.08	.18	.10	.093
534-8337	D	0.70	0.12	.19	.107	.099
534-8338	D	0.75	0.06	.19	.107	.096
534-8339	D	0.80	0.11	.18	.10	.093
534-8340	D	0.85	0.16	.18	.12	.104
534-8341	D	0.90	0.20	.18	.104	.097
534-8342	D	0.93	0.23	.18	.11	.093
<b>T-1</b>						
534-7351	E	0.120	0.045	.22	.171	.107
534-7352	E	0.140	0.065	.18	.09	.083
534-7353	E	0.160	0.085	.18	.14	.125
534-7354	E	0.180	0.105	.18	.104	.087
534-7355	E	0.200	0.125	.18	.14	.125
534-7356	E	0.220	0.145	.18	.11	.09
534-7357	E	0.240	0.045	.19	.149	.133
534-7358	E	0.250	0.060	.22	.15	.10
534-7359	E	0.260	0.065	.18	.14	.125
534-7360	E	0.280	0.090	.19	.106	.099
534-7361	E	0.300	0.110	.18	.11	.09
534-7362	E	0.320	0.120	.19	.106	.099
534-7363	E	0.340	0.140	.18	.10	.093
534-7364	E	0.350	0.150	.18	.104	.097
534-7365	E	0.360	0.160	.19	.117	.099
534-7366	E	0.380	0.060	.18	.104	.097
534-7367	E	0.40	0.08	.18	.10	.09
534-7368	E	0.42	0.10	.19	.111	.103
534-7369	E	0.44	0.12	.19	.106	.099
534-7370	E	0.45	0.12	.22	.14	.124
534-7371	E	0.46	0.14	.22	.10	.09
534-7372	E	0.48	0.15	.19	.106	.099
534-7373	E	0.50	0.06	.26	.17	.11
534-7374	E	0.55	0.10	.18	.10	.093
534-7375	E	0.60	0.15	.19	.111	.103
534-7376	E	0.65	0.08	.18	.10	.093
534-7377	E	0.70	0.12	.18	.104	.097
534-7378	E	0.75	0.06	.18	.10	.093
534-7379	E	0.80	0.11	.29	.18	.11
534-7380	E	0.85	0.16	.18	.10	.093
534-7381	E	0.90	0.20	.18	.10	.093
534-7382	E	0.93	0.23	.18	.10	.093

