

OMRON Low Signal Relays

OMRON G5V-1 & G5V-13 SERIES: 1A SPDT SMALL LOW SIGNAL RELAYS

Specifications:

- Contact resistance: 100mΩ max.
- Contact material: Ag (Au clad)
- Power consumption: 150mW

Features:


- Ultra-miniature, highly sensitive relay for signal circuits
- High-sensitivity: 150mW nominal power consumption
- Wide switching power of 1mA to 1A
- Conforms to FCC part 68 requirements for coil to contacts
- Fully-sealed construction
- Ideal for use in telecommunications, security, and computer/peripheral equipment



* 2% pickup voltage

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Omron Part No.	Fig.	Rated Current (mA)	Coil Resistance (Ω)	Coil Voltage (VDC)	Price Each			
						1	25	50	100
Single Contact - Minimum Permissible Load DC5V, 1mA									
653-G5V-1-DC3	G5V-1-DC3	A1	50.0	60.0	3	1.57	1.45	1.35	1.27
653-G5V-1-DC5	G5V-1-DC5	A1	30.0	166.7	5	1.57	1.53	1.41	1.29
653-G5V-1-DC6	G5V-1-DC6	A1	25.0	240.0	6	1.64	1.54	1.46	1.38
653-G5V-1-DC9	G5V-1-DC9	A1	16.7	540.0	9	1.64	1.54	1.38	1.30
653-G5V-1-DC12	G5V-1-DC12	A1	12.5	960.0	12	1.64	1.54	1.38	1.30
653-G5V-1-DC24	G5V-1-DC24	A1	6.3	3840.0	24	1.95	1.83	1.67	1.56
* 653-G5V-1-2DC5	G5V-1-2 DC5	A1	30.0	166.7	5	1.62	1.49	1.45	1.40
* 653-G5V-1-2DC9	G5V-1-2 DC9	A1	16.7	540.0	9	1.79	1.65	1.53	1.42
* 653-G5V-1-2DC12	G5V-1-2 DC12	A1	12.5	960.0	12	2.39	2.22	1.98	1.78
Double Contact - Minimum Permissible Load DC100mV, 100µA									
653-G5V-13DC3	G5V-13DC3	A1	50.0	60.0	3	1.77	1.62	1.49	1.38
653-G5V-13DC5	G5V-13DC5	A1	30.0	167.0	5	2.30	1.94	1.89	1.59
653-G5V-13-DC12	G5V-13-DC12	A1	12.5	960.0	12	3.19	2.84	2.59	2.28
653-G5V-13-DC24	G5V-13-DC24	A1	3.25	3840.0	24	3.19	2.84	2.59	2.28



OMRON G5V-2 SERIES: 2A DPDT GENERAL USAGE LOW SIGNAL RELAYS

Specifications:

- Contact resistance: 50mΩ max.
- Power consumption: Standard type 500mW, High-sensitivity type 360mW, Ultra-sensitive type 150mW

Features:

- Miniature relay for signal circuits
- Suitable for handling low signals in computer peripherals, telecommunications and security equipment
- Capable of switching loads 10µA to 2A
- Conforms to FCC part 68: 1500V surge withstand
- Reliable Ag + Au-clad, bifurcated crossbar contacts
- Fully-sealed construction



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Omron Part No.	Fig.	Rated Current (mA)	Coil Resistance (Ω)	Coil Voltage (VDC)	Price Each			
						1	25	50	100
Standard Type									
653-G5V-2-DC3	G5V-2-DC3	B2	166.70	18.0	3	2.27	2.15	1.90	1.72
653-G5V-2-DC5	G5V-2-DC5	B2	100.00	50.0	5	2.13	2.00	1.89	1.79
653-G5V-2-DC6	G5V-2-DC6	B2	83.30	72.0	6	2.63	2.53	2.24	2.02
653-G5V-2-DC9	G5V-2-DC9	B2	55.60	162.0	9	1.82	1.67	1.55	1.50
653-G5V-2-DC12	G5V-2-DC12	B2	41.70	288.0	12	2.02	1.90	1.80	1.71
653-G5V-2-DC24	G5V-2-DC24	B2	20.80	1152.0	24	2.02	1.90	1.80	1.71
653-G5V-2-DC48	G5V-2-DC48	B2	12.00	4000.0	48	2.81	2.71	2.50	2.30
High-Sensitivity Type									
653-G5V-2-H-DC5	G5V-2-H-DC5	B2	72.00	70.0	5	2.21	2.07	1.95	1.85
653-G5V-2-H-DC9	G5V-2-H-DC9	B2	40.00	225.0	9	2.47	2.30	2.18	2.05
653-G5V-2-H-DC12	G5V-2-H-DC12	B2	30.00	400.0	12	2.17	2.05	1.93	1.83
653-G5V-2-H-DC24	G5V-2-H-DC24	B2	15.00	1600.0	24	2.61	2.45	2.31	2.19
Ultra-Sensitive Type									
653-G5V-2-H1-DC5	G5V-2-H1-DC5	B2	30.00	166.7	5	2.64	2.08	1.96	1.87
653-G5V-2-H1-DC9	G5V-2-H1-DC9	B2	16.70	540.0	9	3.03	2.45	2.33	2.08
653-G5V-2-H1-DC12	G5V-2-H1-DC12	B2	12.50	960.0	12	3.05	2.94	2.55	2.30
653-G5V-2-H1-DC24	G5V-2-H1-DC24	B2	8.30	2880.0	24	2.76	2.45	2.33	2.08
653-G5V-2-H1-DC48	G5V-2-H1-DC48	B2	6.25	7680.0	48	3.95	3.86	3.55	3.26

OMRON G6L SERIES: 1A SPST-NO LOW PROFILE LOW SIGNAL RELAYS

Specifications:

- Contact resistance: 100mΩ max.
- Max. switching current: 1A
- Power consumption: 180mW

Features:

- Extremely thin and flat relay, one of the thinnest relays in the world
- Uses 20% less mounting area and 67% less volume in comparison with the G5V-1 relay
- High dielectric strength: 1000VAC between coil and contacts and 750VAC between contacts of the same polarity
- Conforms to FCC part 68



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Omron Part No.	Fig.	Rated Current (mA)	Coil Resistance (Ω)	Coil Voltage (VDC)	Price Each			
						1	25	50	100
Standard Type									
653-G6L-1F-DC3	G6L-1F-DC3	C3	60.0	50.0	3	2.76	2.48	2.20	1.98
653-G6L-1F-DC4.5	G6L-1F-DC4.5	C3	40.0	112.5	4.5	2.76	2.48	2.20	1.98
653-G6L-1F-DC5	G6L-1F-DC5	C3	36.0	139.0	5	2.76	2.48	2.20	1.98
653-G6L-1F-DC12	G6L-1F-DC12	C3	15.0	800.0	12	2.66	2.41	2.15	1.93
653-G6L-1F-DC24	G6L-1F-DC24	C3	9.6	2504.0	24	3.03	2.72	2.42	2.18
High-Sensitivity Type									
653-G6L-1P-DC3	G6L-1P-DC3	D3	60.0	50.0	3	2.74	2.46	2.19	1.97
653-G6L-1P-DC4.5	G6L-1P-DC4.5	D3	40.0	112.5	4.5	1.90	1.81	1.77	1.68
653-G6L-1P-DC5	G6L-1P-DC5	D3	36.0	139.0	5	2.76	2.48	2.20	1.98
653-G6L-1P-DC12	G6L-1P-DC12	D3	15.0	800.0	12	2.66	2.41	2.15	1.93
653-G6L-1P-DC24	G6L-1P-DC24	D3	9.6	2504.0	24	2.46	2.37	2.11	1.98

