

KEYSTONE Test Points and Hardware



THRU-HOLE MOUNT TEST POINTS - COLOR KEYED

Specifications:

- Color-Keyed for visibility and quick identification
- Economical choice for PC Test point terminations
- Snap-fit mounting provides positive retention for wave soldering
- Space saving, ultra low and low profile designs
- Ideal for reliable production testing and field service troubleshooting

- Wire form loop for safe, non-slip testing
- Practical replacement for wire-wrap posts and turrets
- Secure grip for J hooks, EZ hooks, grabbers, alligator clips, tips or probes
- Plastic base strengthens terminal for positive holding power



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Fig.	Mounting Hole (in.)	Mounting Center	Board Thickness (in.)	Color	Price Each			
							1	100	500	1000
Miniature Terminal: .010 x .020" Phosphor Bronze Wire, Tin Plate; Base: Glass Filled Nylon UL 94V-0										
534-5000	5000	A	0.040	.100 x .100	.062 & .093	Red	.42	.231	.199	.136
534-5001	5001	A	0.040	.100 x .100	.062 & .093	Black	.42	.199	.178	.136
534-5002	5002	A	0.040	.100 x .100	.062 & .093	White	.42	.21	.189	.135
534-5003	5003	A	0.040	.100 x .100	.062 & .093	Orange	.38	.19	.17	.13
534-5004	5004	A	0.040	.100 x .100	.062 & .093	Yellow	.40	.21	.18	.129
Compact Terminal: .015 x .032" Phosphor Bronze Wire, Tin Plate; Base: Valox, UL 94V-0										
534-5005	5005	B	0.063	.125 x .125	.062 & .093	Red	.38	.19	.17	.129
534-5006	5006	B	0.063	.125 x .125	.062 & .093	Black	.39	.199	.178	.135
534-5007	5007	B	0.063	.125 x .125	.062 & .093	White	.38	.19	.17	.13
534-5008	5008	B	0.063	.125 x .125	.062 & .093	Orange	.42	.21	.19	.129
534-5009	5009	B	0.063	.125 x .125	.062 & .093	Yellow	.39	.21	.178	.126
Multipurpose Terminal: .015 x .032" Phosphor Bronze Wire, Tin Plate; Base: Valox, UL 94V-0										
534-5010	5010	C	0.063	.125 x .125	.062 & .093	Red	.40	.31	.20	.13
534-5011	5011	C	0.063	.125 x .125	.062 & .093	Black	.40	.21	.18	.129
534-5012	5012	C	0.063	.125 x .125	.062 & .093	White	.41	.31	.20	.15
534-5013	5013	C	0.063	.125 x .125	.062 & .093	Orange	.43	.336	.217	.141
534-5014	5014	C	0.063	.125 x .125	.062 & .093	Yellow	.38	.31	.20	.13

SMT TEST POINTS - TAPE AND REEL

5015 Specifications:

- Contact material: .010 Phosphor Bronze
- Contact Finish: Silver Plated
- Tape Material: 8mm wide, 4mm pitch conductive polycarbonate
- Reel size available = 1,000 pieces

5016 Specifications:

- Contact material: .015 Phosphor Bronze
- Contact Finish: Silver Plated
- Tape Material: 12mm wide, 4mm pitch conductive polycarbonate
- Reel size available = 1,000 pieces



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Fig.	Description	Price Each			
				1	100	500	1000
534-5015	5015	D	Miniature Ultra low profile	.66	.32	.27	.17
534-5016	5016	E	Compact unique design	.42	.22	.17	.15

STAINLESS STEEL CAPTIVE PANEL SCREWS

Specifications:

- Stainless Steel per ASTM-A581/A-582



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Fig.	Thread Size	Dimensions: in.			Price Each		
				S.D. ±0.005	S.L. ±0.010	S.D. -0.005, -0.00	1	100	500
534-8700	8700	F	4-40	0.078	0.375	0.036	2.52	2.27	2.15
534-8703	8703	F	6-32	0.095	0.375	0.045	3.48	3.20	2.30
534-8704	8704	F	6-32	0.095	0.500	0.045	3.74	2.85	2.47
534-8705	8705	F	6-32	0.095	0.625	0.045	2.82	2.61	2.25


For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Fig.	Thread Size	Dimensions: in.				Price Each			
				T.L. -0.015	S.D. 0.005	S.L. ±0.010	P.D. -0.010	P.L. ±0.015	1	100	500
534-8706	8706	G	4-40	0.125	0.078	0.171	0.078	0.078	2.03	1.87	1.71
534-8707	8707	G	4-40	0.125	0.078	0.296	0.078	0.078	2.05	1.89	1.74
534-8708	8708	G	4-40	0.125	0.078	0.421	0.078	0.078	2.70	2.46	2.15
534-8709	8709	G	6-32	0.218	0.095	0.187	0.095	0.093	3.56	3.28	2.35
534-8710	8710	G	6-32	0.218	0.095	0.312	0.095	0.093	2.47	2.22	1.98
534-8711	8711	G	6-32	0.218	0.095	0.437	0.095	0.093	3.62	2.76	2.36

PANEL BEARINGS

Specifications:

- Material: Brass, Nickel Plated (QQ-N-290)
- Supplied Unassembled



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Description.	Dimensions: in.				Price Each		
			A	B	C	D	1	100	500
534-1705	1705	3/8 - 32 Standard	.253	.437	.500	.437	1.06	.96	.83
534-1706	1706	1/4 - 32 Miniature	.128	.343	.437	.375	1.55	1.30	1.01

THUMB SCREWS


Specifications:

- For quick removal of panel from chassis.
- Material: Brass, Nickel Plated (QQ-N-290)



RoHS Compliant

DIMENSIONS: in.



VOLUME CONTROL EXTENDERS


Specifications:

- For 1/4" volume control shafts having 3/8-32 threaded bushings.
- Material: Brass, Nickel Plated (QQ-N-290)



RoHS Compliant

DIMENSIONS: in.



For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Keystone Part No.	Thread Size	Price Each		
			1	100	500
534-1708	1708	6-32	1.45	1.24	1.08
534-1709	1709	8-32	1.89	1.73	1.13
534-1710	1710	10-32	1.89	1.73	1.13

MOUSER STOCK NO.	Keystone Part No.	A	B	Price Each		
				1	100	500
534-1464	1464	0.625	0.250	1.95	1.75	1.56
534-1465	1465	0.625	0.675	1.86	1.67	1.49
534-1466	1466	0.687	0.500	2.07	1.86	1.66
534-1467	1467	0.750	0.250	1.99	1.86	1.68