

# QUALTEK Fan Accessories

## FAN SILENCERS

For fast and screwless fan fastening without vibration to the housing. With the patented rubber elastic sleeves you fasten axial fans without screws, quickly and safe with four mushroom formed pegs on a mounting plate or a housing wall.

### Features:

- Eliminates transmission of vibration from the fan to the housing and reduces noise up to 9dB
- Fast, simple, and safe screwless mounting and remounting from fans
- Labor saving device with less mounting costs through shorter mounting times
- Protects the fan against vibrations and thus increases the life



RoHS Compliant

### Specifications:

- Material: TPE (Thermoplastic Elastomer)
- Color: Black
- Hardness: ca. 70° Shore A
- Fire Resistance: UL94-V-0

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Fits Fan Size	Price Each			
				1	25	50	100
562-QLM-40	QLM-40-20-10	A	40mm	2.50	2.35	2.26	2.14
562-QLM-60	QLM-60-30-10	A	60mm	2.99	2.84	2.70	2.56
562-QLM-80	QLM-80-40-10	A	80mm	3.35	3.14	3.03	2.86
562-QLM-90	QLM-92-40-10	A	90mm	3.78	3.55	3.41	3.23
562-QLM-120	QLM-119-50-10	A	120mm	4.68	4.45	4.23	4.15

## Accessories

For quantities greater than listed, call for quote.

Finger Guards				1	25	50	100
562-QSG-40-01	QSG-40-01	B	40mm, width = 42.0mm	1.64	1.45	1.32	1.23
562-QSG-60-01	QSG-60-01	B	60mm, width = 62.0mm	2.03	1.80	1.66	1.55
562-QSG-80-01	QSG-80-01	B	80mm, width = 82.0mm	2.22	2.02	1.84	1.71
562-QSG-92-01	QSG-92-01	B	90mm, width = 94.0mm	1.36	1.21	1.11	1.03
562-QSG-119-01	QSG-119-01	B	120mm, width = 121.0mm	1.82	1.62	1.49	1.38
562-QSG-119-02	QSG-119-02	B	120mm, width = 128.0mm	2.70	2.51	2.37	2.26

## Finger Guard Pins

562-QN-36-110	QN-36-110	C	-	.36	.33	.30	.27
---------------	-----------	---	---	-----	-----	-----	-----

## Filter Media

562-QF-40	QF-40-01	D	40mm	.82	.71	.62	.55
562-QF-60	QF-60-01	D	60mm	.97	.83	.766	.671
562-QF-80	QF-80-01	D	80mm	.98	.79	.71	.65
562-QF-92	QF-92-01	D	90mm	1.03	.848	.745	.687
562-QF-119	QF-119-01	D	120mm	.78	.74	.70	.66

## EMI Filter Shields

562-QSB-40	QSB-40-01	E	40mm	3.39	2.81	2.55	2.29
562-QSB-60	QSB-60-01	E	60mm	5.18	4.26	3.90	3.51
562-QSB-80	QSB-80-01	E	80mm	7.74	7.18	6.43	6.07
562-QSB-92	QSB-92-01	E	90mm	9.45	7.58	6.80	6.42
562-QSB-119	QSB-119-01	E	120mm	9.75	8.20	7.62	7.44

## WIRE FORM FAN GUARDS - 08 SERIES

For use with tubeaxial fans. 1/4" maximum ring spacing design was developed to assist our customers in complying with domestic and international safety agency requirements.

### Specifications:

- Over wire dia. at butt joints: .010 max.
- Depth of serrations: .015 max.
- Thickness of nickel chrome plating: .005 min.
- Tolerance: ±.03"

### Features:

- C1010 basic wire
- Weld joints withstand 220lbs. minimum separation force
- † Black



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Fits Fan Size	Dimensions (mm)			Price Each			
				A	B	C	1	25	50	100
562-08149	08149	F	40mm	29.1	32.0	4.80	.65	.56	.49	.43
562-08248	08248	G	50mm	41.6	40.0	4.80	.90	.87	.86	.84
562-08147	08147	H	60mm	53.1	50.0	4.95	.68	.65	.57	.53
562-08147-02	08147-02	H	60mm	53.1	50.0	4.95	.92	.87	.82	.77
562-08132	08132	I	80mm	76.2	71.5	4.95	.68	.66	.64	.61
562-08153	08153	J	80mm	76.9	71.37	3.89	.86	.76	.66	.59
562-08172	08172	H	80mm	76.2	71.4	4.95	.85	.76	.66	.59
562-08134	08134	J	92mm	89.4	82.5	4.95	.84	.796	.757	.717
562-08174	08174	J	92mm	89.4	82.4	4.95	.89	.80	.69	.64
562-08128	08128	K	120mm	115.6	104.9	7.11	1.85	1.74	1.51	1.40
562-08129	08129	L	120mm	115.6	104.9	3.75	1.25	1.09	1.00	.92
562-08130	08130	L	120mm	115.6	104.9	5.66	.95	.79	.71	.62
562-08170	08170	L	120mm	115.6	104.8	5.66	.78	.75	.66	.59
562-08141	08141	M	120mm	117.3	104.8	5.21	1.70	1.52	1.31	1.19
562-08146	08146	N	120mm	109.5	104.8	4.83	1.07	.95	.83	.77
562-08125	08125	O	150mm	154.4	161.9	6.45	2.36	2.17	2.00	1.85
562-08126	08126	P	150mm	154.4	161.9	6.45	2.25	2.07	1.90	1.78
562-08127	08127	Q	254mm	222.3	174.00	6.35	3.75	3.65	3.60	3.57
562-08154	08154	R	254mm	209.6	174.00	8.35	2.72	2.50	2.39	2.18

## PLASTIC FAN GUARDS - 09 SERIES

The 09 Series low cost plastic fan guards, produced with UL 94-V0 material are designed for tubeaxial fans with design considerations given to maximize airflow with reduced noise levels.

### Features:

- Decreased noise level due to design
- Withstands high impact



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Fits Fan Size	Mounting	Dimensions (mm)			Price Each			
					A	B	C	1	25	50	100
62-09150G	09150-G	S	40mm	1.26	39.87	32.0	4.75	.66	.62	.58	.56
562-09250G	09250-G	S	60mm	1.97	59.94	50.0	6.35	.49	.41	.37	.33
562-09252-G	09252-G	T	60mm	1.96	60.00	50.00	7.00	.72	.67	.64	.62
562-09325G	09325-G	U	80mm	2.81	80.0	71.37	6.60	.65	.49	.45	.39
562-09080-G	09080-G	V	80mm	2.81	79.96	71.4	3.04	.62	.57	.51	.49
562-09081-G	09081-G	W	80mm	2.81	80.00	71.50	7.00	1.06	.98	.95	.92
562-09362G	09362-G	X	92mm	3.25	91.95	82.55	6.35	.79	.66	.60	.54
562-09363G	09363-G	Y	92mm	3.245	92.0	82.5	7.0	1.71	1.55	1.48	1.42
562-09120-G	09120-G	Z	120mm	4.13	115.1	104.8	6.60	.90	.84	.76	.73
562-09121-G	09121-G	AA	120mm	4.13	115.1	104.8	6.60	1.00	.931	.87	.83
562-09122	09122-G	BB	120mm	4.12	115.1	104.8	6.60	.94	.86	.79	.75
562-09123-G	09123-G	CC	120mm	4.13	120.0	105.0	7.0	1.27	1.17	1.12	1.08
562-09450G	09450-G	DD	120mm	4.13	118.11	104.92	7.11	.95	.79	.72	.64
562-09650G	09650-G	EE	150mm	6.38	176.5	161.8	9.91	1.42	1.39	1.36	1.34
562-09651G	09651-G	FF	150mm	6.37	176.5	161.8	7.5	1.84	1.67	1.58	1.53

