

KEYSTONE Swage Standoffs, Terminals, Tools & Hole Plugs

ELECTRONICS CORP.

SWAGE THREADED STANDOFFS



Specifications:

• Brass: per ASTM-B16 • Nickel Plate: QQ-N-290 • For .062" thick boards RoHS Compliant For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	"H" Height above Panel	"L" Shank Length	Panel Thickness	"LD" Shank Diameter	Price Each			
Mfr.	Mfr. Part No.						1	100	500	1000
Round 2-56 Thread x .156 O.D. (5/32")										
534	1589-2	A	0.125	0.109	1/16	0.125	.60	.36	.28	.22
534	1590-2	A	0.187	0.109	1/16	0.125	.48	.30	.25	.21
534	1591-2	A	0.250	0.109	1/16	0.125	.55	.346	.293	.262
Hex 2-56 Thread x .156 O.D. (5/32")										
534	1731-2	B	0.125	0.109	1/16	0.125	.47	.315	.273	.25
534	1740-2	B	0.250	0.109	1/16	0.125	.60	.48	.44	.42
Round 4-40 Thread x .187 O.D. (3/16")										
534	2260-2	A	0.125	0.109	1/16	0.139	.62	.49	.33	.21
534	2262-2	A	0.250	0.109	1/16	0.139	.62	.47	.32	.23
534	2263-2	A	0.375	0.109	1/16	0.139	.58	.357	.294	.251
534	2264-2	A	0.500	0.109	1/16	0.139	.66	.374	.299	.255
Hex 4-40 Thread x .187 O.D. (3/16")										
534	2270-2	B	0.125	0.109	1/16	0.139	.52	.353	.288	.255
534	2272-2	B	0.250	0.109	1/16	0.139	.58	.35	.291	.239
534	2274-2	B	0.500	0.109	1/16	0.139	.72	.577	.535	.502
Round 4-40 Thread x .250 O.D. (1/4")										
534	1560A	A	0.125	0.109	1/16	0.187	.33	.21	.18	.16
534	1790-2	A	0.187	0.109	1/16	0.187	.62	.31	.259	.187
534	1650-2	A	0.250	0.109	1/16	0.187	.49	.313	.267	.244
534	1623-2	A	0.500	0.109	1/16	0.187	.88	.514	.457	.392
534	1625-2	A	0.750	0.109	1/16	0.187	1.06	.639	.571	.395
534	1652-2	A	1.000	0.109	1/16	0.187	1.27	.763	.664	.512
Hex 4-40 Thread x .250 O.D. (1/4")										
534	1653-2	B	0.125	0.109	1/16	0.187	.71	.357	.275	.22
534	1746-2	B	0.187	0.109	1/16	0.187	.49	.399	.357	.336
534	1627-2	B	0.250	0.109	1/16	0.187	.51	.29	.249	.207
534	1629-2	B	0.500	0.109	1/16	0.187	.88	.492	.455	.433
534	1655-2	B	0.750	0.109	1/16	0.187	.87	.595	.524	.467
Round 6-32 Thread x .250 O.D. (1/4")										
534	1560B	A	0.125	0.109	1/16	0.187	.34	.30	.27	.25
534	1546	A	0.250	0.109	1/16	0.187	.38	.28	.25	.21
534	1561B	A	0.375	0.109	1/16	0.187	.75	.50	.33	.30
534	1604-2	A	0.500	0.109	1/16	0.187	.91	.796	.526	.335
534	1608-2	A	0.750	0.109	1/16	0.187	.96	.57	.488	.374
Hex 6-32 Thread x .250 O.D. (1/4")										
534	1620-2	B	0.125	0.109	1/16	0.187	.54	.31	.277	.21
534	1621-2	B	0.250	0.109	1/16	0.187	.80	.66	.44	.291
534	1758-2	B	0.500	0.109	1/16	0.187	.66	.33	.29	.25
534	1761-2	B	0.750	0.109	1/16	0.187	1.01	.684	.622	.544

STANDARDIZED TERMINALS

Features:

- Swage and thread mounting types available
- Bright tin plated for extended shelf life and excellent solderability
- Wide variety of sizes to suit space and wire size requirements

Specifications:

- Material: Free Cutting Brass- ASTM-B16
- Plating: Bright Electro-Tin per MIL-T-10727 Type 1



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Description	Uses Staking Tool #	Board Thickness	"L" Shank Length	Price Each			
Mfr.	Mfr. Part No.						1	100	500	1000
Single & Double Turret Series										
534	1528-1	C	Single	Special Order	0.032	0.051	.17	.12	.08	.06
534	1528-2	C	Single	Special Order	0.062	0.082	.32	.24	.15	.07
534	1528-4	C	Single	Special Order	0.125	0.145	.43	.268	.167	.094
534	1502-1	D	Double	534-TL-2	0.032	0.078	.26	.203	.148	.125
534	1502-2	D	Double	534-TL-2	0.062	0.109	.20	.16	.13	.10
534	1502-3	D	Double	534-TL-2	0.093	0.141	.19	.17	.15	.10
534	1502-4	D	Double	534-TL-2	0.125	0.172	.38	.283	.189	.134
Tubular (Hollow) Turret Series										
534	1540-2	E	Tubular	534-TL-5	0.062	0.109	.34	.25	.20	.17
534	1540-4	E	Tubular	534-TL-5	0.125	0.172	.30	.20	.18	.16
534	1509-2	F	Tubular	534-TL-8	0.062	0.109	.79	.55	.37	.278
534	1509-4	F	Tubular	534-TL-8	0.125	0.172	.65	.59	.40	.25

STAKING TOOLS

Specifications:

- Manufactured from steel with zinc plate
- May be used with an arbor press or hand tapped
- Punch and anvil are precision machined and hardened to ensure long life

For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Description	Price Each	
Mfr.	Mfr. Part No.			1	5
534	TL-2	G	Top staking punch and anvil for standardized terminals	18.84	17.88
534	TL-5	G	Top staking punch and anvil for standardized terminals	17.94	17.03
534	TL-8	G	Top staking punch and anvil for standardized terminals	17.94	17.03
534	TL19	G	For swage standoffs, .187" OD, 2-56 thread	18.03	16.77
534	TL-20	G	For swage standoffs, .25" OD, 4-40 thread	17.94	17.03
534	TL-21	G	For swage standoffs, .25" OD, 6-32 thread	18.84	17.88

METAL HOLE PLUGS

Plug chassis holes, wiring outlets, access holes, or unused openings.

Made of nickel-plated steel.


- Excellent spring retention



RoHS Compliant

For quantities greater than listed, call for quote.

MOUSER STOCK NO.		Fig.	Hole Size (in.)	D (in.)	No. of Prongs	Price Each			
Mfr.	Mfr. Part No.					1	100	500	1000
534	7600	H	1/4	13/32	6	.38	.335	.305	.25
534	7601	H	5/16	7/16	6	.37	.32	.291	.239
534	7602	H	3/8	1/2	6	.37	.32	.291	.239
534	7603	H	1/2	21/32	8	.40	.36	.29	.23
534	7604	H	5/8	13/16	8	.76	.42	.384	.291
534	7606	H	7/8	1 1/16	12	.89	.766	.503	.346
534	7607	H	1	1 9/64	12	.50	.44	.395	.322



Keystone

Hardware