




# TAMURA Power Transformers



## TAMURA LAMINATED POWER TRANSFORMERS

- Class B 130°C Insulation
- 2500Vrms Hi-Pot
- North American Application



Single Primary 115V

Dual Primary 115/230VAC

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Tamura Part No.	Price Each		MOUSER STOCK NO.	Tamura Part No.	Price Each		Power (VA)	Secondary Ratings		Dimensions: in.						
		1	10			1	10		Series (VCT @ A)	Parallel (VAC @ A)	L	W	H	MC	A	B	C
<a href="#">838-3FS-210</a>	3FS-210	3.68	2.92	<a href="#">838-3FD-210</a>	3FD-210	3.78	2.99	1.1	10.0 @ 0.110	5.0 @ 0.220	1.44	1.23	1.00	-	0.25	0.25	1.20
<a href="#">838-3FS-212</a>	3FS-212	3.84	3.05	<a href="#">838-3FD-212</a>	3FD-212	3.78	2.99	1.1	12.6 @ 0.090	6.3 @ 0.180	1.44	1.23	1.00	-	0.25	0.25	1.20
<a href="#">838-3FS-216</a>	3FS-216	3.93	3.12	<a href="#">838-3FD-216</a>	3FD-216	3.78	2.99	1.1	16.0 @ 0.070	8.0 @ 0.140	1.44	1.23	1.00	-	0.25	0.25	1.20
<a href="#">838-3FS-220</a>	3FS-220	3.84	3.05	<a href="#">838-3FD-220</a>	3FD-220	3.78	2.99	1.1	20.0 @ 0.055	10.0 @ 0.110	1.44	1.23	1.00	-	0.25	0.25	1.20
<a href="#">838-3FS-224</a>	3FS-224	3.84	3.05	<a href="#">838-3FD-224</a>	3FD-224	3.78	2.99	1.1	24.0 @ 0.045	12.0 @ 0.090	1.44	1.23	1.00	-	0.25	0.25	1.20
<a href="#">838-3FS-248</a>	3FS-248	3.84	3.05	---	---	-	-	1.1	48.0 @ 0.023	24.0 @ 0.046	1.44	1.23	1.00	-	0.25	0.25	1.20
---	---	-	-	<a href="#">838-3FD-310</a>	3FD-310	4.30	3.41	2.4	10.0 @ 0.250	5.0 @ 0.500	1.44	1.23	1.26	-	0.25	0.25	1.20
<a href="#">838-3FS-312</a>	3FS-312	4.07	3.22	<a href="#">838-3FD-312</a>	3FD-312	4.30	3.41	2.4	12.6 @ 0.200	6.3 @ 0.400	1.44	1.23	1.26	-	0.25	0.25	1.20
<a href="#">838-3FS-316</a>	3FS-316	4.39	3.47	<a href="#">838-3FD-316</a>	3FD-316	4.30	3.41	2.4	16.0 @ 0.150	8.0 @ 0.300	1.44	1.23	1.26	-	0.25	0.25	1.20
<a href="#">838-3FS-320</a>	3FS-320	4.07	3.22	<a href="#">838-3FD-320</a>	3FD-320	4.30	3.41	2.4	20.0 @ 0.120	10.0 @ 0.240	1.44	1.23	1.26	-	0.25	0.25	1.20
<a href="#">838-3FS-324</a>	3FS-324	4.39	3.47	<a href="#">838-3FD-324</a>	3FD-324	4.62	3.66	2.4	24.0 @ 0.100	12.0 @ 0.200	1.44	1.23	1.26	-	0.25	0.25	1.20
<a href="#">838-3FS-328</a>	3FS-328	4.07	3.22	<a href="#">838-3FD-328</a>	3FD-328	4.30	3.41	2.4	28.0 @ 0.085	14.0 @ 0.170	1.44	1.23	1.26	-	0.25	0.25	1.20
---	---	-	-	<a href="#">838-3FD-336</a>	3FD-336	4.30	3.41	2.4	36.0 @ 0.065	18.0 @ 0.130	1.44	1.23	1.26	-	0.25	0.25	1.20
<a href="#">838-3FS-412</a>	3FS-412	7.55	5.97	<a href="#">838-3FD-412</a>	3FD-412	8.19	6.48	6.0	12.6 @ 0.500	6.3 @ 1.000	1.69	1.39	1.36	1.0625	0.25	0.35	1.28
<a href="#">838-3FS-416</a>	3FS-416	7.80	6.17	<a href="#">838-3FD-416</a>	3FD-416	7.63	6.04	6.0	16.0 @ 0.400	8.0 @ 0.800	1.69	1.39	1.36	1.0625	0.25	0.35	1.28
---	---	-	-	<a href="#">838-3FD-420</a>	3FD-420	7.91	6.26	6.0	20.0 @ 0.300	10.0 @ 0.600	1.69	1.39	1.36	1.0625	0.25	0.35	1.28
<a href="#">838-3FS-424</a>	3FS-424	7.55	5.97	<a href="#">838-3FD-424</a>	3FD-424	8.19	6.48	6.0	24.0 @ 0.250	12.0 @ 0.500	1.69	1.39	1.36	1.0625	0.25	0.35	1.28
<a href="#">838-3FS-428</a>	3FS-428	7.77	6.14	<a href="#">838-3FD-428</a>	3FD-428	7.63	6.04	6.0	28.0 @ 0.200	14.0 @ 0.400	1.69	1.39	1.36	1.0625	0.25	0.35	1.28
<a href="#">838-3FS-436</a>	3FS-436	7.23	5.72	<a href="#">838-3FD-436</a>	3FD-436	8.49	6.72	6.0	36.0 @ 0.170	18.0 @ 0.340	1.69	1.39	1.36	1.0625	0.25	0.35	1.28
<a href="#">838-3FS-516</a>	3FS-516	10.26	8.04	<a href="#">838-3FD-516</a>	3FD-516	10.74	8.50	12.0	16.0 @ 0.800	8.0 @ 1.600	1.97	1.63	1.50	1.25	0.30	0.40	1.41
<a href="#">838-3FS-524</a>	3FS-524	10.26	8.04	<a href="#">838-3FD-524</a>	3FD-524	11.13	8.81	12.0	24.0 @ 0.500	12.0 @ 1.000	1.97	1.63	1.50	1.25	0.30	0.40	1.41
<a href="#">838-3FS-528</a>	3FS-528	10.26	8.04	<a href="#">838-3FD-528</a>	3FD-528	10.74	8.50	12.0	28.0 @ 0.420	14.0 @ 0.840	1.97	1.63	1.50	1.25	0.30	0.40	1.41
<a href="#">838-3FS-536</a>	3FS-536	9.55	7.48	<a href="#">838-3FD-536</a>	3FD-536	10.36	8.20	12.0	36.0 @ 0.350	18.0 @ 0.700	1.97	1.63	1.50	1.25	0.30	0.40	1.41
---	---	-	-	<a href="#">838-3FD-548</a>	3FD-548	11.13	8.81	12.0	48.0 @ 0.250	24.0 @ 0.500	1.97	1.63	1.50	1.25	0.30	0.40	1.41