


3M™ Cleaners and Protection Supplies

NOVEC™ AEROSOL CLEANERS

- Non-ozone depleting
- Non-Corrosive
- Contains no nPB, HFCs, or HAPS
- Non-Flammable
- HCFC-141b alternative


For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Description	Price Each	
		1	5
517-32917	Flux Remover 12 oz.	23.69	21.63
517-32925	Electronic Degreaser 12 oz.	24.40	22.28
517-32933	Contact Cleaner 11 oz.	24.65	23.81



WORKSTATION MONITOR

- Continuously monitors the resistance of the work surface, operator, and wiring connections
- Monitors a visitor to the workstation as well as the primary operator
- Uses 2300 Series wrist straps



724 Workstation Monitor with 732 Remote Jack

MOUSER STOCK NO.	3M Part No.	Description	Price Each	
			1	5
517-724	724	Workstation monitor with 732 remote input jack and mounting hardware	172.81	162.01


WRIST STRAP MONITOR

- Small and compact
- Continuously monitors one worker
- Clip on belt
- Battery operated
- Uses 2300 Series wrist straps

MOUSER STOCK NO.	3M Part No.	Description	Price Each	
			1	5
517-725	725	725 Portable wrist strap monitor	95.87	89.89

2300 SERIES DUAL CONDUCTOR CORDS

3M™ Dual Conductor Ground Cord is part of a personnel ground monitoring system. The 3M™ Workstation Monitors Models 724, 725, and 790 use a dual conductor type wrist strap system consisting of a dual conductor wristband and ground cord. The dual system allows for a monitored loop resistance measurement, which includes the wristband contact to the wearer and a redundant grounding path. If one conductor of the system fails, the other can still function maintaining the grounding of the person. As a result, this prevents static from being generated by the person, eliminating possible exposure to static-sensitive electronic components. The 2300 series are compatible with all existing 3M dual conductor fabric, metal, and thermoplastic wristbands.



MOUSER STOCK NO.	3M Part No.	Description	Price Each	
			1	5
Straight Connection				
517-4720	4720	Dual Conductor wrist band, blue	7.55	7.32
517-23600	23600	Coiled, 5 ft. working length	25.36	23.54
517-23700	23700	Coiled, 10 ft. working length	30.52	28.99
517-2371	2371	Coiled, 20 ft. working length	36.42	33.63
517-23680	23680	Dual conductor adj. wrist band	12.90	11.90
Right Angle Connection				
517-2360R	2360R	Coiled, R/A connection, 5 ft. length	28.70	27.28
517-2370R	2370R	Coiled, R/A connection, 10 ft. length	33.26	31.61
517-2371R	2371R	Coiled, R/A connection, 20 ft. length	40.23	38.23
Right Angle Connection with larger Mono Plug O.D.				
517-2391	2391	Coiled, R/A connection, 5 ft. length	27.58	24.85


STATIC-DISSIPATIVE FIELD SERVICE KITS

Static-safe workstations in a portable format for the field service technician.

8501 Portable Field Service Kit

- Adjustable fabric wrist band
- Heavy-duty static-dissipative work surface (.021" x 22" x 24") with two 8" x 11" pockets and 5 ft. coiled ground cord
- Common-point ground cord system with 10' section for wrist band and 5' section for mat

MOUSER STOCK NO.	Price Each	
	1	5
517-8501	70.78	68.10



ADJUSTABLE FABRIC WRIST STRAPS

The front line of defense in all static control processes. One size adjusts to any size wrist to provide reliable, 360 degree protection.




74P7

- Includes alligator clip
- Single Conductor


For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Description	Price Each	
		1	5
517-2214	Adjustable band, 5 foot coiled cord	18.95	17.98
517-2204	Adjustable band only	7.97	7.00
517-2210C	5 foot coiled cord only	20.26	18.95
517-22240	Adjustable band, 10 ft coiled cord	32.12	27.53
517-2271	Economy adjustable strap	4.28	4.07
517-2272	Econo. adj. strap w/ 5' coiled cord	9.86	8.83



4600 SERIES COST EFFECTIVE WRIST BANDS & CORDS

These wrist bands consist of a molded insulative thermoplastic colored exterior with an integrally molded conductive interior insert and 4mm metal male snap.



- Includes alligator clip

MOUSER STOCK NO.	Fig.	Description	Price Each	
			1	5
517-4610	A	5 foot lightweight coiled cord, 4mm snap end	10.59	9.84
517-4611	A	10 foot lightweight coiled cord, 4mm snap end	12.97	11.86
517-4620	B	Blue wrist band with 4mm stud	4.54	4.37

3M™ SCC GROUND CORDS AND GROUND BLOCK

- Table mat ground cord LPCGC151M connect a mat and two wrist straps.
- Floor mat ground cord FGC151M has domed profile to help avoid tripping.
- Ground block WSGR2 mounts to bench and connects two wrist straps to ground. Two parking studs reduce damage to cords left at the bench. No resistor.



* Includes one megohm resistor and #10 ring terminal

MOUSER STOCK NO.	3M Part No.	Description	Price Each	
			1	10
* 517-FGC151M	FGC151M	Floor Ground Cord, 15' cord, 3/8" stud	18.83	14.20
* 517-LPCGC151M	LPCGC151M	Low Profile Ground Cord, 3/8" stud	11.92	11.56
517-WSGR2	WSGR2	Bench Ground Block, 10' cord	13.37	12.66

3M™ SCC INSTRUMENTATION

Combination wrist strap/tester allows associates to test their own wrist straps, heel grounders or shoes. Wrist strap monitors measures the resistance of the wrist strap and person to ensure proper operation of the wrist strap and connection of the grounding product to a person.

Features:

- Compatible with standard single wire wrist straps
- Easy to use
- Audible and visual alarm



WSMONITOR2

MOUSER STOCK NO.	3M Part No.	Description	Price Each	
			1	5
517-COMBOTESTER	COMBOTESTER	Heel grounder/Wriststrap Tester with stand	399.91	364.01
517-WSMONITOR1	WSMONITOR1	Wrist strap monitor - 1 Wrist strap	65.07	60.52
517-WSMONITOR2	WSMONITOR2	Wrist strap monitor - 1 Wrist strap and 1 Mat	115.60	107.50

3M

ELECTRONICS VACUUM

A powerful unit for high efficiency clean up of most business equipment.




Features:

- 1 HP motor
- Comes complete with wand, crevice tool, crevice brush, dusting brush, needle nozzle, and Type 2 filter
- 3 year warranty
- Attachments and power cord store inside door of high impact plastic case
- Stretch hose extends from 2" to 10'
- Portable, quick set up and efficient safe operation

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Description	Price Each	
		1	5
517-497AJM	115V electronics vacuum, 5.0 Amps	282.51	
Replacement Filters			
517-SF1	Small Particle: traps extremely fine particles in the range of .3-.5 microns from highly sensitive equipment.	30.47	
517-MF2	Medium Particle: traps toner and dust from copiers, laser printers, and other office equipment.	13.98	



Replacement Filter

