

TEXAS INSTRUMENTS Logic

Products may be RoHS compliant.
Check mouser.com for RoHS status.



For quantities greater than listed, call for quote.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Package	Description	Price Each		MOUSER STOCK NO.	Package	Description	Price Each	
			1	25				1	25
595-SN74LVC114AD	SOIC-14	Hex Inverter	.44	.335	595-SN74LVC244ADWR	SOIC-20	Octal Buff/Driver	.47	.331
595-SN74LVC14APWR	TSSOP-14	Hex Inverter	.39	.255	595-SN74LVC244APW	TSSOP-20	Octal Buff/Driver	.43	.36
595-SN74LVC14MWBVREP	SOT-23-5	Single Schmitt Trig	.79	.61	595-SN74LVC244APWR	TSSOP-20	Octal Buff/Driver	.45	.321
595-SN74LVC157APWR	TSSOP-16	Quad Data Selector/Multiplex	.65	.40	595-SN74LVC244ARGYR	QFN-20	Octal Buff/Driver	.61	.42
595-74LVC16244ADGGRG	TSSOP-48	16-Bit Buffer/Driver	1.19	.95	595-SN74LVC245ADBR	SSOP-20	Octal Bus Transc	.47	.331
595-SN74LVC16245ADL	SSOP-48	16-Bit Bus Transc	1.44	1.37	595-SN74LVC245ADW	SOIC-20	Octal Bus Transc	.50	.40
595-SN74LVC16245BVR	SOT-23-5	Single Positive-NAND Gate	.39	.22	595-SN74LVC245ADWR	SOIC-20	Octal Bus Transc	.55	.38
595-SN74LVC1G00DCKR	SC70	Single Positive-NAND Gate	.36	.202	595-SN74LVC245APW	TSSOP-20	Octal Bus Transc	.47	.40
595-SN74LVC1G00DRYR	SON-6	Single 2-Input Pos NAND Gate	.39	.258	595-SN74LVC245APWR	TSSOP-20	Octal Bus Transc	.47	.331
595-SN74LVC1G02DCKR	SOP-5	Single 2-Input Positive NOR Gate	.36	.202	595-SN74LVC2G00DCTR	SSOP-8	Dual 2-Input Positive NAND Gate	.57	.352
595-SN74LVC1G02DRYR	SON-6	Single 2-Input Pos NOR Gate	.39	.258	595-SN74LVC2G02DCTR	SSOP-8	Dual 2-Input Positive NOR Gate	.57	.352
595-SN74LVC1G02DSFR	SON-6	Single 2-Input Pos NOR Gate	.52	.31	595-SN74LVC2G02DCUR	VSSOP-8	Dual 2-Input Positive NOR Gate	.47	.331
595-SN74LVC1G04DBVR	SOP-5	Single Inverter	.36	.202	595-SN74LVC2G04DBVR	SOT-23-6	Dual Inverter	.47	.308
595-SN74LVC1G04DCKR	SOP-5	Single Inverter	.36	.202	595-SN74LVC2G04DCKR	SC-70-6	Dual Inverter	.43	.246
595-SN74LVC1G04DCKTE	SC-70	Single Inverter	.71	.56	595-SN74LVC2G06DBVR	SOT-23-6	Dual Inverter Buff/Driver	.39	.255
595-SN74LVC1G04DSF2	SON-6	Single Inverter	.38	.314	595-SN74LVC2G06DCKR	SC-70-6	Dual Inverter Buff/Driver	.39	.255
595-SN74LVC1G04DSFR	SON-6	Single Inverter	.52	.31	595-SN74LVC2G07DBVR	SOT-23-6	Dual Buff	.47	.308
595-SN74LVC1G06DBVR	SOT-23-5	Single Inverter Buff/Driver	.45	.255	595-SN74LVC2G07DCKR	SC-70-6	Dual Buff	.51	.334
595-SN74LVC1G06DCKR	SC70-5	Single Inverter Buff/Driver	.45	.255	595-SN74LVC2G07DRYR	SON-6	Dual Buffer/Driver	.46	.42
595-SN74LVC1G06DRLR	SOP-5	Single Inverter Buff/Driver	.44	.29	595-SN74LVC2G07DSFR	SON-6	Dual Buffer/Driver w/Open Drain	.45	.41
595-SN74LVC1G06DRYR	SON-6	Single Inverter Buffer/Driver	.39	.258	595-SN74LVC2G08DCTR	SSOP-8	Dual Positive-AND Gate	.57	.352
595-SN74LVC1G06DSFR	SON-6	Single Inverter Buffer/Driver	.39	.258	595-SN74LVC2G08DCUR	VSSOP-8	Dual Positive-AND Gate	.47	.331
595-SN74LVC1G06DSFR	SON-6	Single Inverter Buffer/Driver	.52	.31	595-SN74LVC2G125DCTR	SSOP-8	Dual Bus Buff Gate	.65	.40
595-SN74LVC1G07DBVR	SOT-23-5	Single Buff	.49	.276	595-SN74LVC2G14DBVR	SOT-23-6	Dual Inverter	.39	.255
595-SN74LVC1G07DCKR	SC70-5	Single Buff	.45	.255	595-SN74LVC2G14DCKR	SC70-6	Dual Inverter	.39	.255
595-SN74LVC1G07DSFR	SON-6	Single Buffer/Driver	.52	.31	595-SN74LVC2G157DCTR	SSOP-8	Single Data Selector/Multiplex	.57	.352
595-SN74LVC1G08DBVR	SOP-5	Single Positive-AND Gate	.36	.202	595-SN74LVC2G157DCUR	VSSOP-8	Single Data Selector/Multiplex	.52	.352
595-SN74LVC1G08DCKR	SC70-5	Single Positive-AND Gate	.36	.202	595-SN74LVC2G17DBVR	SOT-23-6	Dual Buff	.55	.36
595-SN74LVC1G08DCKT	SC 70-5	Single Positive-AND Gate	.70	.536	595-SN74LVC2G17DCKR	SOT-23-6	Dual Buff	.47	.308
595-SN74LVC1G08DSFR	SON-6	Single 2-Input Pos NAND Gate	.52	.31	595-SN74LVC2G21DCUR	SSOP-8	Dual Buff/Driver	.62	.431
595-SN74LVC1G10DRYR	SON-6	Single 3-Input Positive-NAND Gate	.47	.342	595-SN74LVC2G21DCUR	VSSOP-8	Dual Buff/Driver	.57	.40
595-SN74LVC1G10DSFR	SON-6	Single 3-Input Positive-NAND Gate	.44	.318	595-SN74LVC2G24DBVR	SOT-23-6	Dual Buff Gate	.43	.281
595-SN74LVC1G11DRYR	SON-6	Single 3-Input Positive-AND Gate	.47	.342	595-SN74LVC2G24DCKR	SC-70-6	Dual Buff Gate	.47	.308
595-SN74LVC1G11DSFR	SON-6	Single 3-Input Positive-AND Gate	.44	.318	595-SN74LVC2G34DCKR	SSOP-8	SPDT Analog Switch	.57	.352
595-SN74LVC1G27DRYR	SON-6	Single 3-Input Positive-NOR Gate	.47	.342	595-SN74LVC2G34DCTR	SSOP-8	SPDT Analog Switch	.57	.352
595-SN74LVC1G27DSFR	SON-6	Single 3-Input Positive-NOR Gate	.44	.318	595-SN74LVC2G34DCUR	VSSOP-8	Dual Analog Switch	.65	.40
595-SN74LVC1G32DSF2	SON-6	Single Positive-OR Gate	.39	.27	595-SN74LVC2G74DCTR	SSOP-8	Single D-Type Flip-Flop	.57	.352
595-SN74LVC1G332DRYR	SON-6	Single 3-Input Positive-OR Gate	.47	.342	595-SN74LVC2G74DCUR	VSSOP-8	Single D-Type Flip-Flop	.48	.334
595-SN74LVC1G332DSFR	SON-6	Single 3-Input Positive-OR Gate	.44	.318	595-SN74LVC2G86DCKR	VSSOP-8	Dual 2-Input Exclusive OR Gate	.57	.352
595-SN74LVC1G57DRYR	SON-6	Config. Multiple-Function Gate	.44	.318	595-SN74LVC2G004DBVR	SOT-23-6	Dual Inverter	.43	.281
595-SN74LVC1G57DSFR	SON-6	Config. Multiple-Function Gate	.44	.318	595-SN74LVC2G004DCKR	SC-70-6	Dual Inverter	.43	.281
595-SN74LVC1G58DRYR	SON-6	Config. Multiple-Function Gate	.47	.342	595-SN74LVC2T45DCTR	SSOP-8	Dual-Bit Dual Supply Transc	.69	.536
595-SN74LVC1G58DSFR	SON-6	Config. Multiple-Function Gate	.44	.318	595-SN74LVC2T45DCUR	US-8	Dual-Bit Dual Supply Transc	.69	.536
595-SN74LVC1G66DRYR	SON-6	Single Analog Switch	.47	.396	595-SN74LVC32AD	SOIC-14	Quad Positive-OR Gate	.44	.335
595-SN74LVC1G66DSFR	SON-6	Single Analog Switch	.44	.369	595-SN74LVC32APW	TSSOP-14	Quad Positive-OR Gate	.44	.33
595-SN74LVC1G97DRYR	SON-6	Config. Multiple-Function Gate	.44	.318	595-SN74LVC374ADWR	SOIC-20	Edge-Trigger D-Type Flip-Flop	.48	.334
595-SN74LVC1G97DSFR	SON-6	Config. Multiple-Function Gate	.44	.318	595-SN74LVC374APWR	TSSOP-20	Edge-Trigger D-Type Flip-Flop	.54	.377
595-SN74LVC1G98DRYR	SON-6	Config. Multiple-Function Gate	.44	.318	595-SN74LVC3G04DCTR	SSOP-8	Triple Inverter Gate	.72	.50
595-SN74LVC1G98DSFR	SON-6	Config. Multiple-Function Gate	.44	.318	595-SN74LVC3G07DCTR	SSOP-8	Triple Buff/Driver	.71	.49
595-SN74LVC1G125DBVR	SOP-5	Single Bus Buff Gate	.36	.202	595-SN74LVC3G07DCUR	VSSOP-8	Triple Buff/Driver	.71	.49
595-SN74LVC1G125DCKR	SOP-5	Single Bus Buff Gate	.42	.23	595-SN74LVC3G07QDCQ1	VSSOP-8	Dual 1 of 4 FET Mltplx/Demltplx	.66	.51
595-SN74LVC1G125DRLR	SOP-5	Single Bus Buff Gate	.57	.38	595-SN74LVC3G14DCTR	SSOP-8	Triple Schmitt-Trigger Inverter	.63	.44
595-SN74LVC1G126DCKR	SOP-5	Single Bus Buff Gate	.36	.202	595-SN74LVC3G14DCUR	VSSOP-8	Triple Schmitt-Trigger Inverter	.68	.536
595-SN74LVC1G139DCTR	SSOP-8	2-Ln-to-4-Ln Decoder	.59	.413	595-SN74LVC3G34DCTR	SSOP-8	Triple Buff Gate	.71	.49
595-SN74LVC1G14DBVR	SOP-5	Single Inverter	.52	.272	595-SN74LVC3G34DCUR	VSSOP-8	Triple Buff Gate	.57	.40
595-SN74LVC1G14DCKR	SOP-5	Single Inverter	.52	.272	595-SN74LVC4245ADBR	SSOP-24	Octal Bus Transc	.87	.721
595-SN74LVC1G14DRLR	SOP-5	Single Inverter	.44	.29	595-SN74LVC4245ADW	SOP-24	Octal Bus Transc	.78	.708
595-SN74LVC1G14DSFR	SON-6	Single Schmitt-Trigger Inverter	.52	.31	595-SN74LVC4245APWREP	TSSOP-24	Octal Bus Xcvr	2.32	1.78
595-SN74LVC1G17DBVR	SOT-23-5	Single Buff	.45	.255	595-SN74LVC4245APWR	TSSOP-24	Octal Bus Transc	.97	.778
595-SN74LVC1G17DCKR	SC70-5	Single Buff	.36	.202	595-SN74LVC541ADBR	TSSOP-20	Octal Buff/Driver	.57	.396
595-SN74LVC1G17DCKT	SC 70-5	Single Buff	.70	.536	595-SN74LVC541ADWR	SSOP-20	Octal Buff	.72	.50
595-SN74LVC1G17DSFR	SON-6	Single Schmitt-Trigger Inverter	.52	.31	595-SN74LVC541ADW	SOP-20	Octal Buff	.58	.49
595-SN74LVC1G18DRYR	SON-6	1-of-2 Demultiplexer	.47	.32	595-SN74LVC541APW	TSSOP-20	Octal Buff	.58	.49
595-SN74LVC1G18DSFR	SON-6	1-of-2 Demultiplexer	.44	.30	595-SN74LVC573ADW	SOIC-20	Octal Trans D-Type Latch	.47	.40
595-SN74LVC1G3157DBV	SOP-6	Double-Throw Analog Switch	.37	.246	595-SN74LVC573ARGYR	QFN-20	Octal Trans D-Type Latch	.53	.369
595-SN74LVC1G3157DCK	SOP-6	Double-Throw Analog Switch	.43	.28	595-SN74LVC574ADR	SSOP-20	Octal Edge-Trigger D-Type Latch	.61	.42
595-SN74LVC1G3157DRL	SOP-6	Double-Throw Analog Switch	.50	.325	595-SN74LVC574ADW	SOP-20	Octal Edge-Trigger D-Type Latch	.50	.40
595-SN74LVC1G3157DSFR	SON-6	Single-Pole, Double-Throw Switch	.44	.318	595-SN74LVC574ADWR	SOP-20	Octal Edge-Trigger D-Type Latch	.54	.377
595-SN74LVC1G32DBVR	SOT-23-5	Single Positive-OR Gate	.37	.246	595-SN74LVC74AD	SOIC-14	D-Type Flip-Flop	.44	.35
595-SN74LVC1G32DCKR	SC70	Single Positive-OR Gate	.37	.22	595-SN74LVC74APW	TSSOP-14	D-Type Flip-Flop	.44	.35
595-SN74LVC1G32DSFR	SON-6	Single 2-Input Pos NAND Gate	.38	.25	595-SN74LVC86AD	SOP-14	Quad 2-Input Exc OR Gate	.44	.35
595-SN74LVC1G34DRYR	SON-6	Single Buffer Gate	.45	.30	595-SN74LVC86APWR	TSSOP-14	Quad 2-Input Exc OR Gate	.50	.33
595-SN74LVC1G34DSFR	SON-6	Single Buffer Gate	.43	.279	595-SN74LVC8245PWR	TSSOP-24	8-Bit Bus Transc	1.31	1.03
595-SN74LVC1G38DRYR	SON-6	Single 2-Input NAND Gate	.38	.25	595-74LVC8245MPWREP	TSSOP-24	8-Bit Bus Transc	3.11	2.54
595-SN74LVC1G38DSFR	SON-6	Single 2-Input NAND Gate	.38	.25	595-SN74LVC8245RHLR	QFN-24	8-Bit Bus Transc	1.28	1.01
595-SN74LVC1G57DCKR	SC70-6	Config Multiple-Function Gate	.43	.28	595-SN74LVC3245ADBR	SSOP-24	8-Bit Bus Transc	1.26	1.00
595-SN74LVC1G66DBVR	SOT-23-5	Single Analog Switch	.37	.246	595-SN74LVC3245ADW	SOIC-24	8-Bit Bus Transc	1.20	1.03
595-SN74LVC1G66DCKR	SC-70-5	Single Analog Switch	.43	.28	595-SN74LVC3245APW	TSSOP-24	8-Bit Bus Transc	1.25	1.04
595-SN74LVC1G79DBVR	SOT-23-5	Single Edge-Trigger D-Type Latch	.43	.28	595-SN74LVC44APWR	TSSOP-20	Octal Buff/Driver	.55	.38
595-SN74LVC1G79DCKR	SC70-5	Single Edge-Trigger D-Type Latch	.37	.246	595-SN74LVC44APWR	TSSOP-20	Octal Buff/Driver	.55	.38
595-SN74LVC1G80DBVR	SOT-23-5	Single Edge-Trigger D-Type Latch	.37	.246	595-SN74LVC44APWR	TSSOP-20	Octal Buff/Driver	.55	.38
595-SN74LVC1G80DCKR	SC70-5	Single Edge-Trigger D-Type Latch	.37	.246	595-SN74LVC44APWR	TSSOP-20	Octal Buff/Driver	.55	.38
595-SN74LVC1G80DSFR	SOT-23-5	Single 2-Input Exclusive OR Gate	.37	.246	595-SN74LVC44APWR	TSSOP-20	Octal Buff/Driver	.55	.38
595-SN74LVC1G86DCKR	SC70	Single 2-Input Exclusive OR Gate	.37	.246	595-SN74LVC44APWR	TSSOP-20	Octal Buff/Driver	.55	.38
595-SN74LVC1G97DCKR	SOP-6	Multiple-Function Gate	.37	.246	595-SN74LVT125DDBR	SSOP-14	Quad Bus Buffer	1.51	1.21
595-SN74LVC1G98DCKQ1	SOP-6	Config Multiple-Function Gate	.45	.29	595-SN74LVT244BDW	SOIC-20	3.3V ABT Octal Buff/Driver	.85	.77
595-SN74LVC1G98DCKQ2	SOP-6	Config Multiple-Function Gate	.45	.29	595-SN74LVT244BPWR	TSSOP-20	3.3V ABT Octal Buff/Driver	.87	.669
595-SN74LVC1GU04DBVR	SOT-23-5	Single Inverter Gate	.43	.28	595-SN74LVT245BDW	SOP-20	3.3V ABT Octal Bus Transc	.85	.77
595-SN74LVC1GU04DCKR	SC70-5	Single Inverter Gate	.37	.246	595-SN74LVT245BPWR	TSSOP-20	3.3V ABT Octal Bus Transc	.75	.586
595-SN74LVC1GU04DRYR	SON-6	Single Inverter Gate	.45	.30	595-SN74LVT125D	SOIC-14	3.3V ABT Quad Bus Buff	.58	.52
595-SN74LVC1GU04DSFR	SON-6	Single Inverter Gate	.43	.279	595-SN74LVT125PWR	TSSOP-14	3.3V ABT Quad Bus Buff	.48	.334
595-74LVC2G74MDCUOTEP	DCU-8	D-Type Flip-Flop	2.10	1.75	595-SN74LVTH18502APM	LQFP-64	18-Bit Universal Bus Transceiver	9.52	7.80
595-SN74LVC1T45DCKR	SOP-6	Bus Transc	.63	.44	595-SN74LVTH244ADBR	SSOP-20	3.3V ABT Octal Buff/Driver	.73	.568
595-SN74LVC1T45DPKR	USON-6	Sin.-Bit Dual-Supply 3-State Output Trans.	.59	.455	595-SN74LVTH244ADW	SOIC-20	3.3V ABT Octal Buff/Driver	.80	.73