

SEIKO Battery Protection ICs and Voltage Regulators



RoHS Compliant This product is RoHS compliant.

SII BATTERY PROTECTION ICs

S-8241 Series for 1-Cell Batteries

The S-8241 Series is a protection IC for lithium-ion/lithium polymer rechargeable batteries and includes a high precision detection circuit and a delay circuit. It is the optimal IC for protection against overcharge, overdischarge and overcurrent in 1-cell lithium-ion/lithium polymer rechargeable battery packs. **For quantities greater than listed, call for quote.**

MOUSER STOCK NO.	Seiko Part No.	Package Type	Overcharge		Overdischarge		Overcurrent Detection Voltage1	0V Batt. Charge Function	Price Each					
			Detection Voltage	Release Voltage	Detection Voltage	Release Voltage			1	100	500	1000		
Surface Mount														
628-8241ABPM-G	S-8241ABPMC-GBPT2G	SOT-23-5	4.350V	4.15V	2.3V	3.0V	0.2V	Available	.44	.37	.35	.32		

S-8242B Series for 2-Serial Cell Batteries

The S-8242B Series is a protection IC for 2-serial cell lithium-ion/lithium polymer rechargeable batteries and includes a high precision detection circuit and a delay circuit. These ICs are suitable for protecting 2-cell rechargeable lithium-ion/lithium polymer battery packs from overcharge, overdischarge and overcurrent. **For quantities greater than listed, call for quote.**

Surface Mount														
628-8242BACT	S-8242BACT-T8T1G	TSSOP-8	4.35V	4.15V	2.3V	3.0V	0.3V	Available	.84	.76	.67	.61		

S-8244 for 1-Serial to 4-Serial Cell Batteries

The S-8244 Series is used for secondary protection of lithium-ion rechargeable batteries with one to four cells and includes a high precision voltage detector circuit and a delay circuit. Short circuits between cells accommodates series connection of one to four cells. **For quantities greater than listed, call for quote.**

MOUSER STOCK NO.	Seiko Part No.	Package Type	Overcharge		Output Form	Current Consumption		Price Each						
			Detection Voltage	Release Voltage		@ 3.5V each cell	@ 2.5V each cell	1	100	500	1000			
Surface Mount														
628-8244AAA-G	S-8244AAAFN-CEAT2G	MSOP-8	4.45V	0.38+/-0.1V	CMOS output active "H"	3.0uA	2.4uA	1.02	.87	.82	.74			

S-8254 Series for 3-Serial or 4-Serial Cell Pack Batteries

The S-8254 Series is a protection IC for 3-serial or 4-serial cell lithium-ion rechargeable batteries and includes a high precision detection circuit and a delay circuit. It protects both 3-serial or 4-serial cells using the SEL pin for switching. **For quantities greater than listed, call for quote.**

MOUSER STOCK NO.	Seiko Part No.	Package Type	Overcharge		Overdischarge		Overcurrent Detection Voltage1	0V Batt. Charge Function	Price Each					
			Detection Voltage	Release Voltage	Detection Voltage	Release Voltage			1	100	500	1000		
Surface Mount														
628-8254AAJ-G	S-8254AAJFT-TB-G	TSSOP-16	4.350V	4.150V	2.40V	3.00V	0.15V	Available	1.44	1.22	1.15	1.04		

SII HIGH PRECISION VOLTAGE REGULATORS

S-812 Series

The S-812 Series is a three-terminal positive voltage regulator made using the CMOS process. Since this has higher precision output voltage and consumes less current than existing three-terminal voltage regulators, battery-powered portable equipment can have a higher performance and a longer service life. **For quantities greater than listed, call for quote.**

MOUSER STOCK NO.	Seiko Part No.	Package Type	Output Voltage (V)	I/O Voltage Difference (V) (Typ.)	Current Consumption (µA) (Typ.)	Input Voltage (V) (Max.)	Price Each			
							1	100	500	1000
Surface Mount										
628-812C25AU-G	S-812C25AUA-C2FT2G	SOT-89-3	2.5	0.590	0.9	10	.51	.46	.41	.35
628-812C25AM-G	S-812C25AMC-C2FT2G	SOT-23-5	2.5	0.590	0.9	10	.51	.46	.41	.35
628-812C30AU-G	S-812C30AUA-C2KT2G	SOT-89-3	3.0	0.440	1.0	16	.51	.46	.41	.35
628-812C30AM-G	S-812C30AMC-C2KT2G	SOT-23-5	3.0	0.440	1.0	16	.51	.46	.41	.35
628-812C33AU-G	S-812C33AUA-C2NT2G	SOT-89-3	3.3	0.370	1.0	16	.51	.46	.41	.35
628-812C33AM-G	S-812C33AMC-C2NT2G	SOT-23-5	3.3	0.370	1.0	16	.51	.46	.41	.35
628-812C35AU-G	S-812C35AUA-C2PT2G	SOT-89-3	3.5	0.340	1.0	16	.51	.46	.41	.35
628-812C35AM-G	S-812C35AMC-C2PT2G	SOT-23-5	3.5	0.340	1.0	16	.51	.46	.41	.35
628-812C40AU-G	S-812C40AUA-C2UT2G	SOT-89-3	4.0	0.270	1.2	16	.51	.46	.41	.35
628-812C40AM-G	S-812C40AMC-C2UT2G	SOT-23-5	4.0	0.270	1.2	16	.51	.46	.41	.35
628-812C50AU-G	S-812C50AUA-C3ET2G	SOT-89-3	5.0	0.160	1.2	16	.51	.46	.41	.35
628-812C50AM-G	S-812C50AMC-C3ET2G	SOT-23-5	5.0	0.160	1.2	16	.51	.46	.41	.35
Thru-Hole										
628-812C25AY-G	S-812C25AY-B-G	TO-92	2.5	0.290	0.9	10	.51	.46	.41	.35
628-812C30AY-G	S-812C30AY-B-G	TO-92	3.0	0.440	1.0	16	.51	.46	.41	.35
628-812C33AY-G	S-812C33AY-B-G	TO-92	3.3	0.370	1.0	16	.51	.46	.41	.35
628-812C35AY-G	S-812C35AY-B-G	TO-92	3.5	0.340	1.0	16	.51	.46	.41	.35
628-812C40AY-G	S-812C40AY-B-G	TO-92	4.0	0.270	1.2	16	.51	.46	.41	.35

S-814 Series

The S-814 Series is a low dropout voltage, high output voltage accuracy and low current consumption positive voltage regulator developed utilizing CMOS technology. Built-in low ON-resistance transistors provide low dropout voltage and large output current. A power-off circuit ensures long battery life. Various types of output capacitors can be used in the S-814 Series compared with the past CMOS voltage regulators. (i.e., small ceramic capacitors can also be used in the S-814 Series). These are recommended to be used for configuring portable devices and large output current applications, respectively. **For quantities greater than listed, call for quote.**

MOUSER STOCK NO.	Seiko Part No.	Package Type	Output Voltage (V)	Dropout Voltage (V)(Typ.)	Output Current (Min.)(mA)	Accuracy (%)	Current Consumption (µA)(Typ.)	Input Voltage (V)(Max.)	Price Each			
									1	100	500	1000
Surface Mount												
628-814A20AMC-G	S-814A20AMC-BCKT2G	SOT-23-5	2.0	0.510	110	±2	30	10	.51	.46	.41	.35
628-814A20AUC-G	S-814A20AUC-BCKT2G	SOT-89-5	2.0	0.510	110	±2	30	10	.51	.46	.41	.35
628-814A27AMC-G	S-814A27AMC-BCRT2G	SOT-23-5	2.7	0.380	110	±2	30	10	.51	.46	.41	.35
628-814A30AMC-G	S-814A30AMC-BCUT2G	SOT-23-5	3.0	0.300	110	±2	30	10	.51	.46	.41	.35
628-814A30AUC-G	S-814A30AUC-BCUT2G	SOT-89-5	3.0	0.300	110	±2	30	10	.51	.46	.41	.35
628-814A33AMC-G	S-814A33AMC-BCXT2G	SOT-23-5	3.3	0.300	110	±2	30	10	.51	.46	.41	.35
628-814A33AUC-G	S-814A33AUC-BCXT2G	SOT-89-5	3.3	0.300	110	±2	30	10	.51	.46	.41	.35
628-814A35AMC-G	S-814A35AMC-BCZT2G	SOT-23-5	3.5	0.240	110	±2	30	10	.51	.46	.41	.35
628-814A40AMC-G	S-814A40AMC-BDET2G	SOT-23-5	4.0	0.200	110	±2	30	10	.51	.46	.41	.35
628-814A40AUC-G	S-814A40AUC-BDET2G	SOT-89-5	4.0	0.200	110	±2	30	10	.51	.46	.41	.35
628-814A50AMC-G	S-814A50AMC-BDOT2G	SOT-23-5	5.0	0.170	110	±2	30	10	.51	.46	.41	.35
628-814A50AUC-G	S-814A50AUC-BDOT2G	SOT-89-5	5.0	0.170	110	±2	30	10	.51	.46	.41	.35

S-817 Series

The S-817 Series is a three-terminal positive voltage regulator made using the CMOS process. Since this has higher precision output voltage and consumes less current than existing three-terminal voltage regulators, battery-powered portable equipment can have a higher performance and a longer service life. **For quantities greater than listed, call for quote.**

Surface Mount														
MOUSER STOCK NO.	Seiko Part No.	Package Type	Output Voltage (V)	Dropout Voltage (V)(Typ.)	Output Current (Min.)(mA)	Accuracy (%)	Current Consumption (µA)(Typ.)	Input Voltage (V)(Max.)	1	100	500	1000		
628-817A15ANB-G	S-817A15ANB-CUET2G	SC-82AB	1.5	0.580	50	±2	1.2	10	.51	.46	.41	.35		
628-817B15AMC-G	S-817B15AMC-CWET2G	SOT-23-5	1.5	0.580	50	±2	1.2	10	.51	.46	.41	.35		
628-817B15AUA-G	S-817B15AUA-CWET2G	SOT-89-3	1.5	0.580	50	±2	1.2	10	.51	.46	.41	.35		
628-817A18ANB-G	S-817A18ANB-CUHT2G	SC-82AB	1.8	0.580	50	±2	1.2	10	.51	.46	.41	.35		
628-817B18AMC-G	S-817B18AMC-CWHT2G	SOT-23-5	1.8	0.580	50	±2	1.2	10	.51	.46	.41	.35		
628-817B18AUA-G	S-817B18AUA-CWHT2G	SOT-89-3	1.8	0.580	50	±2	1.2	10	.51	.46	.41	.35		
628-817A20ANB-G	S-817A20ANB-CUJT2G	SC-82AB	2.0	0.400	50	±2	1.2	10	.51	.46	.41	.35		
628-817B20AMC-G	S-817B20AMC-CWJT2G	SOT-23-5	2.0	0.400	50	±2	1.2	10	.51	.46	.41	.35		
628-817B20AUA-G	S-817B20AUA-CWJT2G	SOT-89-3	2.0	0.400	50	±2	1.2	10	.51	.46	.41	.35		
628-817A25ANB-G	S-817A25ANB-CUOT2G	SC-82AB	2.5	0.310	50	±2	1.2	10	.51	.46	.41	.35		
628-817B25AMC-G	S-817B25AMC-CWOT2G	SOT-23-5	2.5	0.310	50	±2	1.2	10	.51	.46	.41	.35		
628-817B25AUA-G	S-817B25AUA-CWOT2G	SOT-89-3	2.5	0.310	50	±2	1.2	10	.51	.46	.41	.35		

