


PANASONIC Chip Resistor Arrays



This product is RoHS compliant.

PANASONIC THICK FILM CONVEX TERMINATION CHIP RESISTOR ARRAYS

- Features:**
- Operating Temperature Range: -55°C to +125°C
 - High density
 - Improvement of placement efficiency
 - Tolerance: 5%



Type (inches)	Dimensions (mm)							
	L	W	T	A1	A2	B	P	G
EXB28V (0402x4)	2.00±0.10	1.00±0.10	0.35±0.10	0.45±0.10	0.35±0.10	0.20±0.10	(0.50)	0.25±0.10
EXB28HV (0402x8)	3.80±0.10	1.60±0.10	0.45±0.10	0.35±0.10	0.35±0.10	0.30±0.10	(0.50)	0.30±0.10
EXB24V (0603x2)	1.60±0.20	1.60±0.15	0.50±0.10	0.65±0.15	---	0.30±0.20	(0.80)	0.30±0.20
EXB38V (0603x4)	3.20±0.20	1.60±0.15	0.50±0.10	0.65±0.15	0.45±0.15	0.30±0.20	(0.80)	0.35±0.20

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	Panasonic Part Number	Fig.	Value (Ω)	No. of Terminals	No. of Resistors	Case Size	Price Each					
							1	25	100	250	500	1000
EXB2 Series Convex Termination Chip Resistor Arrays (CONT.)												
667-EXB-28VR000X	EXB-28VR000X	A	0	8	4	0402	.12	.047	.038	.029	.022	.017
667-EXB-28V3R3JX	EXB-28V3R3JX	A	3.3	8	4	0402	.12	.06	.038	.029	.022	.017
667-EXB-28V6R8JX	EXB-28V6R8JX	A	6.8	8	4	0402	.12	.06	.038	.029	.022	.017
667-EXB-28V680JX	EXB-28V680JX	A	68	8	4	0402	.12	.047	.038	.029	.022	.017
667-EXB-28V471JX	EXB-28V471JX	A	470	8	4	0402	.12	.047	.038	.029	.022	.017
667-EXB-28V681JX	EXB-28V681JX	A	680	8	4	0402	.12	.06	.038	.029	.022	.017
667-EXB-28V472JX	EXB-28V472JX	A	4.7K	8	4	0402	.12	.047	.038	.029	.022	.017
667-EXB-28V682JX	EXB-28V682JX	A	6.8K	8	4	0402	.12	.047	.038	.029	.022	.017
667-EXB-28V333JX	EXB-28V333JX	A	33K	8	4	0402	.12	.047	.038	.029	.022	.017
667-EXB-28V683JX	EXB-28V683JX	A	68K	8	4	0402	.12	.06	.038	.029	.022	.017
667-EXB-28V334JX	EXB-28V334JX	A	330K	8	4	0402	.12	.06	.038	.029	.022	.017
667-EXB-28V474JX	EXB-28V474JX	A	470K	8	4	0402	.12	.047	.038	.029	.022	.017
667-EXB-28V684JX	EXB-28V684JX	A	680K	8	4	0402	.12	.06	.038	.029	.022	.017
667-EXB-2HV2R2JV	EXB-2HV2R2JV	B	2.2	16	8	0402	.35	.16	.118	.093	.08	.06
667-EXB-2HV3R3JV	EXB-2HV3R3JV	B	3.3	16	8	0402	.35	.16	.118	.093	.08	.06
667-EXB-2HV4R7JV	EXB-2HV4R7JV	B	4.7	16	8	0402	.35	.16	.118	.093	.08	.06
667-EXB-2HV6R8JV	EXB-2HV6R8JV	B	6.8	16	8	0402	.35	.16	.118	.093	.08	.06
667-EXB-2HV680JV	EXB-2HV680JV	B	68	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV271JV	EXB-2HV271JV	B	270	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV471JV	EXB-2HV471JV	B	470	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV681JV	EXB-2HV681JV	B	680	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV472JV	EXB-2HV472JV	B	4.7K	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV682JV	EXB-2HV682JV	B	6.8K	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV223JV	EXB-2HV223JV	B	22K	16	8	0402	.35	.16	.118	.093	.08	.06
667-EXB-2HV273JV	EXB-2HV273JV	B	27K	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV333JV	EXB-2HV333JV	B	33K	16	8	0402	.35	.16	.118	.093	.08	.06
667-EXB-2HV473JV	EXB-2HV473JV	B	47K	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV683JV	EXB-2HV683JV	B	68K	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV224JV	EXB-2HV224JV	B	220K	16	8	0402	.35	.16	.118	.093	.08	.06
667-EXB-2HV274JV	EXB-2HV274JV	B	270K	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV334JV	EXB-2HV334JV	B	330K	16	8	0402	.35	.143	.118	.093	.08	.06
667-EXB-2HV474JV	EXB-2HV474JV	B	470K	16	8	0402	.35	.16	.118	.093	.08	.06
667-EXB-2HV684JV	EXB-2HV684JV	B	680K	16	8	0402	.35	.16	.118	.093	.08	.06
667-EXB-2HV105JV	EXB-2HV105JV	B	1M	16	8	0402	.35	.143	.118	.093	.08	.06
EXB3 Series Convex Termination Chip Resistor Arrays												
667-EXB-34V1R0JV	EXB-34V1R0JV	C	1	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V2R2JV	EXB-34V2R2JV	C	2.2	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V3R3JV	EXB-34V3R3JV	C	3.3	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V4R7JV	EXB-34V4R7JV	C	4.7	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V6R8JV	EXB-34V6R8JV	C	6.8	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V100JV	EXB-34V100JV	C	10	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V330JV	EXB-34V330JV	C	33	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V470JV	EXB-34V470JV	C	47	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V680JV	EXB-34V680JV	C	68	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V101JV	EXB-34V101JV	C	100	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V221JV	EXB-34V221JV	C	220	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V331JV	EXB-34V331JV	C	330	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V471JV	EXB-34V471JV	C	470	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V681JV	EXB-34V681JV	C	680	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V102JV	EXB-34V102JV	C	1K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V222JV	EXB-34V222JV	C	2.2K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V332JV	EXB-34V332JV	C	3.3K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V472JV	EXB-34V472JV	C	4.7K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V682JV	EXB-34V682JV	C	6.8K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V223JV	EXB-34V223JV	C	22K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V333JV	EXB-34V333JV	C	33K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V473JV	EXB-34V473JV	C	47K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V683JV	EXB-34V683JV	C	68K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V104JV	EXB-34V104JV	C	100K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V224JV	EXB-34V224JV	C	220K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V334JV	EXB-34V334JV	C	330K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V474JV	EXB-34V474JV	C	470K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V684JV	EXB-34V684JV	C	680K	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-34V105JV	EXB-34V105JV	C	1M	4	2	0603	.23	.086	.065	.048	.036	.024
667-EXB-38VR000V	EXB-38VR000V	A	0	8	4	0603	.12	.045	.034	.025	.018	.012
667-EXB-38V1R0JV	EXB-38V1R0JV	A	1	8	4	0603	.12	.045	.034	.025	.018	.012
667-EXB-38V2R2JV	EXB-38V2R2JV	A	2.2	8	4	0603	.12	.045	.034	.025	.018	.012
667-EXB-38V3R3JV	EXB-38V3R3JV	A	3.3	8	4	0603	.12	.045	.034	.025	.018	.012
667-EXB-38V6R8JV	EXB-38V6R8JV	A	6.8	8	4	0603	.12	.045	.034	.025	.018	.012
667-EXB-38V680JV	EXB-38V680JV	A	68	8	4	0603	.12	.045	.034	.025	.018	.012
667-EXB-38V471JV	EXB-38V471JV	A	470	8	4	0603	.12	.045	.034	.025	.018	.012
667-EXB-38V333JV	EXB-38V333JV	A	33K	8	4	0603	.12	.045	.034	.025	.018	.012
667-EXB-38V684JV	EXB-38V684JV	A	680K	8	4	0603	.12	.045	.034	.025	.018	.012
667-EXB-38V105JV	EXB-38V105JV	A	1M	8	4	0603	.12	.045	.034	.025	.018	.012

NEW FROM PANASONIC

Networks / Arrays

Panasonic

NEW FROM PANASONIC

NEW FROM PANASONIC

NEW FROM PANASONIC