



**Standard Recovery Rectifier High Voltage Surface-Mount****eSMP® Series****SMF (DO-219AB)****FEATURES**

- For surface mounted applications
- Low profile package
- Ideal for automated placement
- Glass passivated
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Meets JESD 201 class 2 whisker test
- Wave and reflow solderable
- Base P/N-M3-halogen-free, RoHS-compliant
Base P/N-M or P/N-HM3 - halogen-free, RoHS-compliant and AEC-Q101 qualified
- Compatible to SOD-123W package case outline or SOD-123F and SOD-123FL
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

**LINKS TO ADDITIONAL RESOURCES****MECHANICAL DATA****Case:** SMF (DO-219AB)**Polarity:** band denotes cathode end**Weight:** approx. 15 mg**Packaging codes / options:**

18 or I = 10K per 13" reel (8 mm tape)

08 or H = 3K per 7" reel (8 mm tape)

Circuit configuration: single**PARTS TABLE**

PART	ORDERING CODE	MARKING	REMARKS
S07B-M	S07B-M3-18 or S07B-M3-08	Y5	Tape and reel
	S07B-M-18 or S07B-M-08	UB	
	S07B-M3/H or S07B-M3/I	Y5	
	S07B-HM3/H or S07B-HM3/I	UB	
S07D-M	S07D-M3-18 or S07D-M3-08	Y6	Tape and reel
	S07D-M-18 or S07D-M-08	UD	
	S07D-M3/H or S07D-M3/I	Y6	
	S07D-HM3/H or S07D-HM3/I	UD	
S07G-M	S07G-M3-18 or S07G-M3-08	Y7	Tape and reel
	S07G-M-18 or S07G-M-08	UG	
	S07G-M3/H or S07G-M3/I	Y7	
	S07G-HM3/H or S07G-HM3/I	UG	
S07J-M	S07J-M3-18 or S07J-M3-08	Y8	Tape and reel
	S07J-M-18 or S07J-M-08	UJ	
	S07J-M3/H or S07J-M3/I	Y8	
	S07J-HM3/H or S07J-HM3/I	UJ	
S07M-M	S07M-M3-18 or S07M-M3-08	Y9	Tape and reel
	S07M-M-18 or S07M-M-08	UM	
	S07M-M3/H or S07M-M3/I	Y9	
	S07M-HM3/H or S07M-HM3/I	UM	

**ABSOLUTE MAXIMUM RATINGS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	PART	SYMBOL	VALUE	UNIT
Maximum repetitive peak reverse voltage		S07B-M	V_{RRM}	100	V
		S07D-M	V_{RRM}	200	V
		S07G-M	V_{RRM}	400	V
		S07J-M	V_{RRM}	600	V
		S07M-M	V_{RRM}	1000	V
Maximum RMS voltage		S07B-M	V_{RMS}	70	V
		S07D-M	V_{RMS}	140	V
		S07G-M	V_{RMS}	280	V
		S07J-M	V_{RMS}	420	V
		S07M-M	V_{RMS}	700	V
Maximum DC blocking voltage		S07B-M	V_{DC}	100	V
		S07D-M	V_{DC}	200	V
		S07G-M	V_{DC}	400	V
		S07J-M	V_{DC}	600	V
		S07M-M	V_{DC}	1000	V
Maximum average forward rectified current	$T_L = 110\text{ }^{\circ}\text{C}$ ⁽¹⁾		$I_{F(AV)}$	1.5	A
	$T_A = 65\text{ }^{\circ}\text{C}$ ⁽¹⁾		$I_{F(AV)}$	0.7	A
Peak forward surge current 8.3 ms single half	$T_L = 25\text{ }^{\circ}\text{C}$		I_{FSM}	25	A

Note⁽¹⁾ Averaged over any 20 ms period**THERMAL CHARACTERISTICS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Thermal resistance junction to ambient air ⁽¹⁾		R_{thJA}	180	K/W
Operating junction and storage temperature range		T_J, T_{stg}	-65 to +175	$^{\circ}\text{C}$

Note⁽¹⁾ Mounted on epoxy substrate with 3 mm x 3 mm Cu pads ($\geq 40\text{ }\mu\text{m}$ thick)**ELECTRICAL CHARACTERISTICS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Instantaneous forward voltage	$I_F = 1\text{ A}$ ⁽¹⁾	S07B-M	V_F			1.1	V
		S07D-M	V_F			1.1	V
		S07G-M	V_F			1.1	V
		S07J-M	V_F			1.1	V
		S07M-M	V_F			1.1	V
Maximum DC reverse current at rated DC blocking voltage	$T_A = 25\text{ }^{\circ}\text{C}$	S07B-M	I_R			10	μA
		S07D-M	I_R			10	μA
		S07G-M	I_R			10	μA
		S07J-M	I_R			10	μA
		S07M-M	I_R			10	μA
	$T_A = 125\text{ }^{\circ}\text{C}$	S07B-M	I_R			50	μA
		S07D-M	I_R			50	μA
		S07G-M	I_R			50	μA
		S07J-M	I_R			50	μA
		S07M-M	I_R			50	μA
Reverse recovery time	$I_F = 0.5\text{ A}, I_R = 1\text{ A}, I_{rr} = 0.25\text{ A}$	S07B-M	t_{rr}			1800	ns
		S07D-M	t_{rr}			1800	ns
		S07G-M	t_{rr}			1800	ns
		S07J-M	t_{rr}			1800	ns
		S07M-M	t_{rr}			1800	ns
Typical capacitance	4 V, 1 MHz	S07B-M	C_j		4		pF
		S07D-M	C_j		4		pF
		S07G-M	C_j		4		pF
		S07J-M	C_j		4		pF
		S07M-M	C_j		4		pF

Note⁽¹⁾ Pulse test: 300 μs pulse width, 1 % duty cycle



TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)




Fig. 1 - Forward Current Derating Curve




Fig. 3 - Typical Instantaneous Reverse Characteristics




Fig. 2 - Typical Instantaneous Forward Characteristics






Fig. 4 - Capacitance vs. Reverse Voltage



PACKAGE DIMENSIONS in millimeters (inches): **SMF (DO-219AB)**




foot print recommendation:



Created - Date: 15. February 2005
Rev. 6 - Date: 24.Feb.2021
Document no.: S8-V-3915.01-001 (4)
22989



ORIENTATION IN CARRIER TAPE - SMF (DO-219AB)



Document no.: S8-V-3717.02-003 (4)

Created - Date: 09. Feb. 2010

22670