


## 1 Description

Coto's new S117X Silicon Carbide (SiC) MOSFET relay supports and sustains load voltages of 1700 V while carrying a current of up to 170 mA. Advantages of the S117X SiC Relay include low switching loss, high breakdown voltage, low  $R_{dS\text{ON}}$  resistance. The extreme durability of the SiC material ensures stable performance in volatile environments under variable humidity, across a wide temperature range. Ideal applications include those requiring high voltage, high temperature and high frequency features. Target markets include Battery Management Systems, Factory Automation Control, EV Charging stations and Solar Inverters & Smart Grids.

## Device Information

Part Series	Package	Body Size (mm)
S117T	DIP Thru-Hole	8.8 x 6.4 x 3.4
S117S	DIP Surface Mount	8.8 x 6.4 x 3.4

## Device Package




## 2 Features

- Contact Form: 1A
- Load Voltage: 1700V (AC Peak or DC)
- Load Current: 120 mA
- Low ON-Resistance: 20Ω Maximum
- Low Off-State Leakage Current: 1µA Maximum
- Package Type: 6-DIP or SMD
- Silicon Carbide FET Output

## 3 Applications

- Battery Management Systems
- Factory Automation Control
- EV Charging Stations
- Solar Inverters & Smart Grids


## 4 Device Schematic




## 5 Dimensions

*in Inches (Millimeters)*

S117T (Thru-Hole)



S117S (Surface Mount)



## 6 Specifications

### 6.1 Absolute Maximum Ratings

Parameters	Symbol	Rating	Unit
Input	Continuous LED Current	I <sub>F</sub>	50
	Peak LED Current (f=100Hz Duty=1%)	I <sub>FP</sub>	1000
	LED Reverse Voltage	V <sub>R</sub>	5
	Input Power Dissipation	P <sub>IN</sub>	75
Output	Load Voltage	V <sub>L</sub>	1700 V (AC Peak or DC)
	A (AC)		120 mA
	Load Current	I <sub>L</sub>	150 mA
	B (DC)		170 mA
	C (DC)		
	Peak Load Current 100 ms (1 pulse)	I <sub>PEAK</sub>	600 mA
Output Power Dissipation		P <sub>OUT</sub>	450 mW
Total Power Dissipation		P <sub>T</sub>	500 mW
I/O Breakdown Voltage (RH = 60%, 1 min)		V <sub>I/O</sub>	3750 Vrms
I/O Breakdown Voltage (Suffix-V) (RH = 60%, 1 min)		V <sub>I/O</sub>	5000 Vrms
Operating Temperature		T <sub>OPR</sub>	-40 to +85 °C
Storage Temperature		T <sub>STG</sub>	-40 to +100 °C
Pin Soldering Temperature (10 sec max)		T <sub>SOL</sub>	260 °C

### 6.2 Electrical Characteristics


Parameters	Symbol	Conditions	Min.	Typ.	Max.	Unit
Input	V <sub>F</sub>	I <sub>F</sub> =10mA		1.3	1.5	V
	I <sub>FON</sub>			1.0	5.0	mA
	V <sub>F OFF</sub>		0.7			V
	I <sub>F OFF</sub>			0.35	0.8	mA
Output	R <sub>ON</sub>	I <sub>F</sub> =10mA, I <sub>L</sub> =Rating, Time to flow is within 1 sec		15	20	Ω
		I <sub>F</sub> =10mA, I <sub>L</sub> =<5mA		7.5	10	Ω
	I <sub>LEAK</sub>	V <sub>L</sub> =Rating			1	μA
	C <sub>OUT</sub>	V <sub>L</sub> =0, f=1MHz		-		pF
Transmission	T <sub>ON</sub>	I <sub>F</sub> =10mA, I <sub>L</sub> =Rating		0.15	0.5	ms
	T <sub>OFF</sub>			0.04	0.1	ms
Coupled	R <sub>I/O</sub>	DC500V	10 <sup>10</sup>			Ω
	C <sub>I/O</sub>	f=1MHz		0.8	1.5	pF

#### Environmental Ratings:


All electrical parameters measured at 25°C unless otherwise specified.

## 7 CotoMOS® S117X Series Graphs


### Load Current Vs. Ambient Temperature




### On-Resistance Vs. Ambient Temperature




### Turn-On Time Vs. Ambient Temperature




### Turn-Off Time Vs. Ambient Temperature



### LED Operate Current Vs. Ambient Temperature




### LED Turn-Off Current Vs. Ambient Temperature




## 7 CotoMOS® S117X Series Graphs


**LED Forward Voltage Vs. Ambient Temperature**




**Voltage Vs. Current Characteristics of Output at MOSFET Portion**




**Off-State Leakage Current Vs. Load Voltage**




**Turn-On Time Vs. LED Forward Current**



**Turn-Off Time Vs. LED Forward Current**




**Output Capacitance Vs. Applied Voltage**




## 8 Using Methods

Examples of resistance value to control LED forward current ( $I_F=5\text{mA}$ )




E	R
3.3V	Approx. 333 $\Omega$
5V	Approx. 640 $\Omega$
12V	Approx. 1.9K $\Omega$
15V	Approx. 2.5K $\Omega$
24V	Approx. 4.1K $\Omega$

1. LED forward current must be more than 5mA, at E min.
2. LED forward current must be less than 50mA, at E max.



## 9 Connections

Regulate the spike voltage generated on the inductive load as follows:




## 10 Recommended Soldering Conditions

### 10.1 Infrared Reflow Soldering

- Peak reflow soldering: 240°C or below (package surface temperature)
- Time of peak reflow temperature: 20-30 seconds
- Time of temperature higher than 240°C: 30-60 seconds
- Time to preheat temperature from 180~190°C: 90-120 seconds
- Number of reflows: One
- Flux: Rosin flux containing small amount of chlorine  
(The flux with a maximum chlorine content of 0.2 Wt% is recommended.)

### 10.2 Recommended Temperature Profile of Infrared Reflow




### 10.3 Cautions

- Fluxes: Avoid removing the residual flux with freon-based and chlorine-based cleaning solvent.
- Avoid shorting between portion of frame and leads.

## 11 CotoMOS Relay Packaging Information (Surface Mount Only)


### 11.1 6-pin SOP Carrier Tape & Reel Units: mm




#### Notes

1. There is a leader of 230mm minimum which consists of carrier and/or cover tape followed by a minimum of 160mm of carrier tape sealed with cover tape.
2. There is a minimum of 160mm of empty component pockets sealed with cover tape.
3. Device pockets are in accordance with EIA standard EIA-481-A and specifications provided above.

## 11.2 Device Marking



## 11.3 Recommended Mounting Pad



## 12 IMPORTANT NOTICE AND DISCLAIMER

COTO TECHNOLOGY, INC. ("COTO") PROVIDES THIS DATA SHEET "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS AND IMPLIED, WITH RESPECT TO INFORMATION SET FORTH HEREIN, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF ACCURACY, COMPLETENESS, MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE AND NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS. Your receipt of this data sheet constitutes your acknowledgement and acceptance of, and agreement to, all of the terms, conditions, notes, disclaimers and limitations set forth herein.

This data sheet is subject to change without notice. Coto reserves the right to make, from time to time, changes to specifications set forth herein as may be necessary or desirable to improve the performance, reliability and/or manufacturability of the products described herein. As such, before placing an order of any Coto product described herein, you must verify that the information set forth herein is current with respect to such product, and Coto assumes no responsibility for any damages which you may incur due to your failure to do so.

Coto grants you permission to use this data sheet only for information and reference purposes, and any other use of this data sheet by you is prohibited. No license to any intellectual property right of Coto or any third party is granted hereunder.

You are solely responsible for (1) deciding whether to purchase or use any Coto product, (2) selecting appropriate Coto products for your application, (3) designing, validating and testing your application incorporating or involving any Coto product and (4) ensuring that such application meets applicable safety, security, regulatory or other requirements or standards. Any purchase or use of any Coto product must fully comply with all applicable laws and regulations, including, without limitations, import and export regulations.

Coto products described herein have been designed, developed and manufactured to be used in the standard commercial applications similar to those shown herein ("Specific Applications"). Any application requiring measures of reliability, robustness, safety or certifications not shown or beyond those shown herein is at the user's risk and is not warranted or guaranteed by Coto. Therefore, you are advised to use Coto products described herein only in Specific Applications.

Your purchase and use of Coto products, including, without limitation, those products described herein, are subject to Coto's terms and conditions of sale and other applicable terms available on Coto's website or otherwise provided or made available in conjunction with such products. Unless such terms and conditions state otherwise, COTO PRODUCTS ARE PROVIDED "AS IS" AND WITH ALL FAULTS, AND ANY AND ALL WARRANTIES, EXPRESS AND IMPLIED, WITH RESPECT TO SUCH PRODUCTS, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE AND NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS, ARE DISCLAIMED. Coto's provision of this data sheet does not expand or otherwise alter Coto's applicable warranties or warranty disclaimers for Coto products.

Coto disclaims responsibility for, and you will fully defend, indemnify and hold harmless Coto, its affiliates and its and their respective equity holders, directors, officers, employees, representatives, agents, successors and assigns against and for, any and all claims, damages, costs, losses and liabilities arising out of your use of this data sheet or your purchase or use of any Coto product described herein.