

MOSFET - Power, Single N-Channel, STD Gate, TCPAK1012

80 V, 0.79 mΩ, 643 A

NVBYST0D8N08X

Features

- Low Q_{RR} , Soft Recovery Body Diode
- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Synchronous Rectification (SR) in DC-DC and AC-DC
- Primary Switch in Isolated DC-DC Converter
- Motor Drives
- Automotive 48V System


MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-to-Source Voltage		V _{DSS}	80	V
Gate-to-Source Voltage		V _{GS}	±20	V
Continuous Drain Current	T _C = 25 °C	I _D	643	A
	T _C = 100 °C		455	
Power Dissipation	T _C = 25 °C	P _D	652	W
Pulsed Drain Current	T _C = 25 °C t _p = 100 μs	I _{DM}	1976	A
Operating Junction and Storage Temperature Range		T _J , T _{stg}	−55 to +175	°C
Continuous Source-Drain Current (Body Diode)		I _S	1097	A
Single Pulse Avalanche Energy (I _{PK} = 132 A)		E _{AS}	871	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 seconds)		T _L	260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface-mounted on FR4 board using a 1 in², 1 oz. Cu pad.
2. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
3. EAS is based on started $T_J = 25^\circ\text{C}$, rated IAS, $V_{DD} = 64 \text{ V}$, $V_{GS} = 10 \text{ V}$, 100% avalanche tested.


$V_{(BR)DSS}$	$R_{DS(ON)} \text{ MAX}$	$I_D \text{ MAX}$
80 V	0.79 mΩ @ $V_{GS} = 10 \text{ V}$	643 A



N-CHANNEL MOSFET



MARKING DIAGRAM



0D8N08X = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

Device	Package	Shipping [†]
NVBYST0D8N08X	TCPAK1012	1500 / Tape & Reel

[†] For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, [BRD8011/D](http://www.onsemi.com/BRD8011/D).

THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case (Top)	$R_{\theta JC}$	0.23	°C/W
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	38	
Thermal Characterization Parameter, Junction-to-Source Lead (Pin 1-7)*	Ψ_{JL}	3.9	
Thermal Characterization Parameter, Junction-to-Drain Lead (Pin 9-16)*	Ψ_{JL}	3.3	

* Low thermal conductivity test boards compliant with JEDEC Standard 51-3 for leaded surface-mount packages. 1s0p PCB board with a 1 in² copper plane, tested under natural convection conditions.

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
-----------	--------	-----------------	-----	-----	-----	------

OFF CHARACTERISTICS

Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}, I_D = 1\text{ mA}, T_J = 25^\circ\text{C}$	80	–	–	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$\Delta V_{(BR)DSS} / \Delta T_J$	$I_D = 1\text{ mA}$, Referenced to 25°C	–	37	–	mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 80\text{ V}, T_J = 25^\circ\text{C}$	–	–	2	μA
		$V_{DS} = 80\text{ V}, T_J = 125^\circ\text{C}$	–	–	250	
Gate-to-Source Leakage Current	I_{GSS}	$V_{GS} = 20\text{ V}, V_{DS} = 0\text{ V}$	–	–	100	nA

ON CHARACTERISTICS

Drain-to-Source On Resistance	$R_{DS(on)}$	$V_{GS} = 10\text{ V}, I_D = 80\text{ A}, T_J = 25^\circ\text{C}$	–	0.67	0.79	mΩ
Gate Threshold Voltage	$V_{GS(TH)}$	$V_{GS} = V_{DS}, I_D = 703\text{ μA}, T_J = 25^\circ\text{C}$	2.4	–	3.6	V
Gate Threshold Voltage Temperature Coefficient	$\Delta V_{GS(TH)} / \Delta T_J$	$V_{GS} = V_{DS}, I_D = 703\text{ μA}$	–	–7.5	–	mV/°C
Forward Transconductance	g_{FS}	$V_{DS} = 5\text{ V}, I_D = 80\text{ A}$	–	324	–	S

CHARGES, CAPACITANCES & GATE RESISTANCE

Input Capacitance	C_{ISS}	$V_{DS} = 40\text{ V}, V_{GS} = 0\text{ V}, f = 1\text{ MHz}$	–	13097	–	pF
Output Capacitance	C_{OSS}		–	3744	–	
Reverse Transfer Capacitance	C_{RSS}		–	56	–	
Output Charge	Q_{OSS}		–	268	–	nC
Total Gate Charge	$Q_{G(TOT)}$	$V_{DD} = 40\text{ V}, I_D = 80\text{ A}, V_{GS} = 10\text{ V}$	–	182	–	
Threshold Gate Charge	$Q_{G(TH)}$		–	40	–	
Gate-to-Source Charge	Q_{GS}		–	59	–	
Gate-to-Drain Charge	Q_{GD}		–	28	–	
Gate Plateau Voltage	V_{GP}		–	4.6	–	
Gate Resistance	R_G	$f = 1\text{ MHz}$	–	0.26	–	Ω

SWITCHING CHARACTERISTICS

Turn-On Delay Time	$t_{d(ON)}$	Resistive Load, $V_{GS} = 0/10\text{ V}$, $V_{DD} = 64\text{ V}, I_D = 80\text{ A}$, $R_G = 2.5\text{ Ω}$	–	50	–	ns
Rise Time	t_r		–	16	–	
Turn-Off Delay Time	$t_{d(OFF)}$		–	86	–	
Fall Time	t_f		–	14	–	

SOURCE-TO-DRAIN DIODE CHARACTERISTICS

Forward Diode Voltage	V_{SD}	$I_S = 80\text{ A}, V_{GS} = 0\text{ V}, T_J = 25^\circ\text{C}$	–	0.79	1.2	V
		$I_S = 80\text{ A}, V_{GS} = 0\text{ V}, T_J = 125^\circ\text{C}$	–	0.63	–	

NVBYST0D8N08X

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified) (continued)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
SOURCE-TO-DRAIN DIODE CHARACTERISTICS						
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, I _S = 80 A, dI/dt = 1000 A/μs, V _{DD} = 64 V	–	55	–	ns
Charge Time	t _a		–	28	–	
Discharge Time	t _b		–	27	–	
Reverse Recovery Charge	Q _{RR}		–	609	–	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate Voltage




Figure 4. On-Resistance vs. Drain Current




Figure 5. Normalized ON Resistance vs. Junction Temperature




Figure 6. Drain Leakage Current vs. Drain Voltage

NVBYST0D8N08X

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristics




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Characteristics




Figure 11. Safe Operating Area (SOA)




Figure 12. Avalanche Current vs Pulse Time (UIS)

NVBYST0D8N08X

TYPICAL CHARACTERISTICS




Figure 13. Gate Threshold Voltage vs Junction Temperature




Figure 14. Maximum Current vs. Case Temperature




Figure 15. Transient Thermal Response

NVBYST0D8N08X


REVISION HISTORY

Revision	Description of Changes	Date
0	Thermal characteristics update. Maximum power & drain current update. Switching curve update. FBSOA & UIS update. BVDSS temp. coefficient update.	08/21/2025

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.




NVBYST0D8N08X

PACKAGE DIMENSIONS



TCPAK16 8.80x10.10, 1.20P (TCPAK1012)
CASE 762AA
ISSUE E



DATE 23 MAY 2025



NOTES:


1. UNIT DIMENSION: MILLIMETER
2. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH OR MOLD GATE REMAINS. MOLD FLASH OR GATE REMAINS SHALL NOT EXCEED 0.150mm PER SIDE.
3. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.

△ CENTER PAD IS FOR PKG MECHANICAL SUPPORT ONLY. NO SOLDERING REQUIRED.



MILLIMETERS			
DIM	MIN	NOM	MAX
A	1.30	1.35	1.40
A1	0.00	0.05	0.10
b	0.67	0.72	0.77
b1	0.65	0.70	0.75
c	0.21	0.26	0.31
D	10.00	10.10	10.20
D1	8.50	8.60	8.70
D3	0.55	0.60	0.75
E	8.70	8.80	8.90
E1	6.04	6.14	6.24
E2	---	---	8.70
e	1.20 BSC		
e/2	0.60 BSC		
e1	0.85 BSC		
e2	2.00 BSC		
k	1.70	1.80	1.90
H	11.80	12.00	12.20
L	0.80	1.00	1.20
L1	1.40	1.60	1.80
L2	0.30 BSC		
Θ	---	2.5°	5°

GENERIC MARKING DIAGRAM*



XXXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Assembly Lot Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marketing.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales