



WIDEBAND, LOW NOISE, LOW CURRENT

Monolithic Amplifier

PMA2-63LN+

50Ω 0.4 to 6 GHz

THE BIG DEAL

- Ultra wideband, 0.4 to 6 GHz
- Excellent noise figure, 0.5 dB at 2 GHz
- Low Current, 44 mA at 5V
- High Gain, 19.5 dB at 2 GHz
- High IP3, +31.7 dBm at 2 GHz

*Generic photo used for illustration purposes only*

CASE STYLE: MC1631-1

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- 5G
- Fixed-Satellite
- Cellular Infrastructure
- Defense

PRODUCT OVERVIEW

The PMA2-63LN+ is a PHEMT based wideband, low noise MMIC amplifier with an unique combination of high gain, high IP3 and low noise figure, making it ideal for sensitive, high-dynamic-range receiver applications. This design operates on a single +5V supply, is well matched for 50 ohm and comes in a tiny, low profile package (2 x 2 mm, 8 lead MCLP), accommodating dense circuit board layouts.

KEY FEATURES

| Feature | Advantages |
|--|--|
| Excellent Noise Figure up to 6 GHz • 0.5 dB typ. at 2 GHz • 0.7 dB typ. at 4 GHz | Enables lower system noise figure performance. |
| High IP3 • +31.7 dBm at 2 GHz • +31.6 dBm at 4 GHz | Combination of low noise figure and high IP3 makes this MMIC amplifier ideal for use in low noise receiver front end (RFE) as it gives the user advantages of sensitivity and two-tone IM performance at both ends of the dynamic range. |
| Low operating voltage & current +5V & 44 mA | Low voltage & current consumption is ideal for use in amplifier chain. |
| 2 x 2mm 8-lead MCLP package | Tiny footprint saves space in dense layouts while providing low inductance, repeatable transitions, and excellent thermal contact to the PCB. |

REV. B
ECO-011027
PMA2-63LN+
GY/RS/CP
240327

Mini-Circuits®www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 1 OF 4



WIDEBAND, LOW NOISE, LOW CURRENT

Monolithic Amplifier

PMA2-63LN+

50Ω 0.4 to 6 GHz

ELECTRICAL SPECIFICATIONS¹ AT +25°C, ZO=50Ω UNLESS NOTED OTHERWISE

| Parameter | Condition (GHz) | V _{DD} =+5 V & Vladj=Open | | | Units |
|---|-----------------|------------------------------------|-------|-------|-------|
| | | Min. | Typ. | Max. | |
| Frequency Range | | 0.4 | | 6 | GHz |
| Gain | 0.4 | 21.1 | 24.1 | 25.8 | dB |
| | 1.0 | 19.9 | 22.7 | 24.4 | |
| | 2.0 | 17.2 | 19.5 | 21.0 | |
| | 4.0 | 13.1 | 14.7 | 16.5 | |
| | 6.0 | — | 11.5 | — | |
| Input Return Loss | 0.4 | | 7.7 | | dB |
| | 1.0 | | 9.5 | | |
| | 2.0 | | 12.0 | | |
| | 4.0 | | 14.2 | | |
| | 6.0 | | 12.0 | | |
| Output Return Loss | 0.4 | | 9.4 | | dB |
| | 1.0 | | 9.1 | | |
| | 2.0 | | 7.7 | | |
| | 4.0 | | 7.1 | | |
| | 6.0 | | 6.4 | | |
| Output Power at 1dB Compression ² | 0.4 | | +17.2 | | dBm |
| | 1.0 | | +17.1 | | |
| | 2.0 | | +17.7 | | |
| | 4.0 | | +18.4 | | |
| | 6.0 | | +17.9 | | |
| Output IP3 | 0.4 | | +31.3 | | dBm |
| | 1.0 | | +30.9 | | |
| | 2.0 | | +31.7 | | |
| | 4.0 | | +31.6 | | |
| | 6.0 | | +32.8 | | |
| Noise Figure | 0.4 | | 0.5 | | dB |
| | 1.0 | | 0.5 | | |
| | 2.0 | | 0.5 | | |
| | 4.0 | | 0.7 | | |
| | 6.0 | | 1.0 | | |
| Device Operating Voltage (V _{DD}) | | +4.75 | +5.0 | +5.25 | V |
| Device Operating Current (I _{DD}) | | — | 44 | 61 | mA |
| Device Current Variation vs. Temperature ² | | | -81 | | µA/°C |
| Device Current Variation vs. Voltage | | | 0.014 | | mA/mV |
| Thermal Resistance, junction-to-ground lead | | | 65 | | °C/W |

1. Measured on Mini-Circuits Characterization Test Board TB-PMA2-63LNE+. See Characterization Test & Application Circuit (Fig. 2)


2. Device Current Variation vs. Temperature= (Current in mA at 85°C - Current in mA at -45°C)/130°C

3. Device Current Variation vs. Voltage = (Current in mA at 5.25V - Current in mA at 4.75V) / ((5.25V-4.75V)*1000 mA/mV)

ABSOLUTE MAXIMUM RATINGS⁵

| Parameter | Ratings |
|-------------------------------------|--|
| Operating Temperature (ground lead) | -40°C to +85°C |
| Storage Temperature | -65°C to +150°C |
| Junction Temperature | 137°C |
| Total Power Dissipation | 0.8 W |
| Input Power (CW), Vd=5V | +22 dBm (5 minutes max.) +13 dBm (continuous) |
| DC Voltage at Pad 1 | +1.2 V |
| DC Voltage at Pad 6 | +7 V |

5. Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.

VOLTAGE LEVEL AT CURRENT ADJUSTMENT PAD (VLADJ) VS. DEVICE CURRENT (IDD)⁴

4. When Vladj connection is Open, Vladj=0.92V given a device with IDD=44 mA typ. For RF Performance at different Vladj, please see View Data and Graph.




WIDEBAND, LOW NOISE, LOW CURRENT

Monolithic Amplifier

PMA2-63LN+


50Ω 0.4 to 6 GHz

SIMPLIFIED SCHEMATIC & PAD DESCRIPTION



| Function | Pad Number | Description (See Figure 2) |
|----------------|------------|---|
| RF-IN | 3 | Connects to RF input via C1 |
| RF-OUT & DC-IN | 6 | Connects to RF out via C2 and connects to V _{DD} via L1 |
| Iadj | 1 | Current Adjustment Pad. Can adjust device current by supplying different voltage levels |
| No Connection | 2,5,7 & 8 | Not used internally. Connected to ground on Test Board |
| Ground | 4 & Paddle | Connects to ground on Test board. |

CHARACTERIZATION TEST & APPLICATION CIRCUIT



| Components | Size | Value | Manufacturer | P/N |
|------------|------|-------|--------------|-------------------|
| C1 | 0402 | 150pF | Murata | GRM1555C1H151JA01 |
| C2 | | 150pF | | GRM1555C1H151JA01 |
| C3 | | 100pF | | GRM1555C1H101JA1D |
| C4 | | 1uF | | GRM155R61E105KA12 |
| L1 | | 56nH | Coilcraft | 0402CS-56NXGL |


Fig 2. Application and Characterization Circuit

Note: This block diagram is used for characterization. (DUT soldered on Mini-Circuits Characterization test board TB-PMA2-63LNE+) Gain, Return loss, Output power at 1dB compression (P1dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

PRODUCT MARKING



Marking may contain other features or characters for internal lot control



WIDEBAND, LOW NOISE, LOW CURRENT

Monolithic Amplifier

PMA2-63LN+

50Ω 0.4 to 6 GHz


Mini-Circuits®

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

| | |
|---------------------------------------|---|
| Performance Data | Data Table Swept Graphs S-Parameter (S2P Files) Data Set (.zip file) |
| Case Style | MC1631-1 Plastic package, exposed paddle, lead finish: tin silver over nickel |
| Tape & Reel | F66 |
| Standard quantities available on reel | 7" reels with 20, 50, 100, 200, 500, 1K, 2K or 3K devices |
| Suggested Layout for PCB Design | PL-683 |
| Evaluation Board | TB-PMA2-63LNE+ |
| Environmental Ratings | ENV08T1 |

ESD RATING

Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

MSL TEST FLOW CHART**NOTES**

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits®www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 4 OF 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[PMA2-63LN+](#)