




ebm-papst MFG. NOTES


I N/A

SEE SHEET 1 FOR REVISION HISTORY






BE SURE GRILL
GUARDS OVER-LAP
AS SHOWN.

DETAIL **A**
SCALE 0.500
(2 PLACES)



ISOMETRIC VIEW
SCALE 0.046



ebm-papst Inc. DISCLOSURE
THIS DOCUMENT IS THE PROPERTY OF ebm-papst Inc. ITS USE IS AUTHORIZED BY ebm-papst Inc. ONLY. ALL QUESTIONS MUST BE REFERRED TO ebm-papst Inc. PERSONNEL: DESIGN ENG., MFG.ENG., AND / OR PURCHASING.
CAUTION: ANY PRINTED COPY IS UNCONTROLLED AND TO BE USED FOR REFERENCE ONLY. REFER TO ebm-papst Inc. CAD SYS. FOR VERIFICATION.
Form No. 1073 Rev. H

MATERIAL: AS NOTED
FINISH: SEE SHEET 1
IF APPLICABLE, ENTER SECOND FINISH AND DESCRIPTION HERE
ALL INNER BEND RADII = 1mm BOTTOM BEND UNLESS OTHERWISE STATED
TOLERANCES, UNLESS OTHERWISE STATED:
DECIMAL .XXX ± .020 HOLES .XXX ± .003 TOLERANCE .XX ± .030 ANGLES ± 1° REF
BEND DEDUCTION N/A
COSMETICS PER ebm-papst SPEC-0-1
SEE CAD FOR DIMS. NOT SHOWN
BREAK ALL SHARP EDGES
ALL DIMENSIONS ARE IN INCHES
TOLERANCES FOR CNC FLAT .XXX EXCLUDING HOLE DIA. +/- .010

PART NO. EGIR-480-560-23
TITLE R3G560-AP23-09 K-MOD, SPECIAL
FIRST USED ON N/A
DESIGN ENG. CHW ORIG. DATE 11-Jun-13 E# ELECT.

ebm-papst

REVISION 003 SHEET 2 of 2