

**SC1205-01UTG**


Bidirectional Discrete TVS Diode, General Purpose Surge Protection

**PRELIMINARY & CONFIDENTIAL**

Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Parts numbers and specifications are subject to change until the datasheet is made final.


Note: This package image is for example and reference only. For detail package drawing, please refer to the package section in this datasheet.

**Pinout****Functional Block Diagram****Description**

The SC1205-01UTG bidirectional TVS is fabricated in a proprietary silicon avalanche technology. These diodes provide a high ESD (electrostatic discharge) protection level for electronic equipment. The SC1205-01UTG TVS can safely absorb repetitive ESD strikes of  $\pm 30$  kV (contact and air discharge as defined in IEC 61000-4-2) without any performance degradation. Additional, each TVS can safely dissipate a 7A 8/20μs surge event as defined in IEC 61000-4-5 2nd edition.

**Features**

- ESD, IEC 61000-4-2,  $\pm 30$  kV contact,  $\pm 30$  kV air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Surge Tolerance, 7A (8/20μs as defined in IEC 61000-4-5 2nd edition)
- Low leakage current of 1nA (TYP) at 4.5V
- Halogen free, lead free and RoHS compliant
- Moisture Sensitivity Level (MSL -1)

**Applications****Applications**

- Switches / Buttons
- Test Equipment / Instrumentation
- Point-of-Sale Terminals
- Medical Equipment
- Notebooks / Desktops / Servers
- Computer Peripherals
- Battery

**Life Support Note:**

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

**SC1205-01UTG**

Bidirectional Discrete TVS Diode, General Purpose Surge Protection

**PRELIMINARY & CONFIDENTIAL**

Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Part numbers and specifications are subject to change until the datasheet is made final.

**Absolute Maximum Ratings**

Symbol	Parameter	Value	Units
$I_{PP}$	Peak Current ( $t_p=8/20\mu s$ )	7	A
$T_{OP}$	Operating Temperature	-40 to 125	°C
$T_{STOR}$	Storage Temperature	-55 to 150	°C

**CAUTION:** Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.



**Electrical Characteristics ( $T_{OP}=25^\circ C$ )**

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	$V_{RWM}$	$I_R=1\mu A$			4.5	V
Breakdown Voltage	$V_{BR}$	$I_R=1mA$	5.3	5.5		V
Reverse Leakage Current	$I_{LEAK}$	$V_R=4.5V$		1	20	nA
Clamp Voltage <sup>1</sup>	$V_c$	$I_{PP}=7, t_p=8/20\mu s$		10		V
Dynamic Resistance <sup>2</sup>	$R_{DYN}$	TLP, $t_p=100ns$		0.17		Ω
ESD Withstand Voltage <sup>1</sup>	$V_{ESD}$	IEC 61000-4-2 (Contact Discharge)	±30			kV
		IEC 61000-4-2 (Air Discharge)	±30			kV
Diode Capacitance <sup>1</sup>	$C_{IO-GND}$	Reverse Bias=4.5V, f=1MHz		7	9	pF

**Note:**

1. Parameter is guaranteed by design and/or component characterization.

2. Transmission Line Pulse (TLP) with 100ns width, 0.2ns rise time, and average window t1=70ns to t2= 90ns

**Capacitance vs Reverse Bias****Clamping Voltage vs  $I_{PP}$** 


**SC1205-01UTG**

Bidirectional Discrete TVS Diode, General Purpose Surge Protection


**PRELIMINARY & CONFIDENTIAL**

Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Parts numbers and specifications are subject to change until the datasheet is made final.


Positive Transmission Line Pulsing (TLP) Plot





Negative Transmission Line Pulsing (TLP) Plot



IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage



IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage

8/20 $\mu$ s Pulse Waveform

**SC1205-01UTG**


Bidirectional Discrete TVS Diode, General Purpose Surge Protection

**PRELIMINARY & CONFIDENTIAL**


Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Parts numbers and specifications are subject to change until the datasheet is made final.

**Soldering Parameters**


Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ( $T_{s(\min)}$ )	150°C
	- Temperature Max ( $T_{s(\max)}$ )	200°C
	- Time (min to max) ( $t_s$ )	60 – 120 secs
Average ramp up rate (Liquidus) Temp ( $T_L$ ) to peak		3°C/second max
Reflow	$T_{s(\max)}$ to $T_L$ - Ramp-up Rate	3°C/second max
	- Temperature ( $T_L$ ) (Liquidus)	217°C
	- Temperature ( $t_L$ )	60 – 150 seconds
Peak Temperature ( $T_p$ )		260 <sup>0/-5</sup> °C
Time within 5°C of actual peak Temperature ( $t_p$ )		30 seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature ( $T_p$ )		8 minutes Max.
Do not exceed		260°C

**Ordering Information**

Part Number	Package	Min. Order Qty.
SC1205-01UTG	0201DFN	15000

**Part Marking System****Product Characteristics**

Lead Plating	Ag (EF <sup>2</sup> )
Lead material	Ni/Fe
Substrate Material	Silicon
Body Material	Molded Compound
Flammability	UL Recognized compound meeting flammability rating V-0


**Part Numbering System**

**SC1205-01UTG**


## Bidirectional Discrete TVS Diode, General Purpose Surge Protection

**PRELIMINARY & CONFIDENTIAL**

Littelfuse, Inc. has characterized initial samples of this device and is currently conducting reliability testing. Parts numbers and specifications are subject to change until the datasheet is made final.

**Package Dimensions — 0201DFN**

Symbol	0201DFN					
	Millimeters			Inches		
	Min	Typ	Max	Min	Typ	Max
<b>A</b>	0.280	—	0.320	0.011	—	0.013
<b>A1</b>	0.000	—	0.050	0.000	—	0.002
<b>b</b>	0.200	0.250	0.300	0.008	0.010	0.012
<b>L</b>	0.130	0.185	0.240	0.005	0.007	0.009
<b>D</b>	0.550	0.600	0.650	0.022	0.024	0.026
<b>E</b>	0.250	0.300	0.350	0.010	0.012	0.014
<b>h</b>	0.000	0.050	0.10	0.000	0.002	0.004
<b>e</b>	0.350 BSC			0.014 BSC		

**Embossed Carrier Tape & Reel Specification — 0201DFN**

Symbol	Millimeters
<b>A0</b>	0.38+/-0.03
<b>B0</b>	0.68+/-0.03
<b>K0</b>	0.34+/-0.03
<b>P0</b>	4.00+/-0.10
<b>P1</b>	2.00+/-0.05
<b>P2</b>	2.00+/-0.05
<b>T</b>	0.18+/-0.03
<b>E</b>	1.75+/-0.10
<b>F</b>	3.50+/-0.05
<b>D0</b>	1.55+/-0.05
<b>D1</b>	0.20+/-0.05
<b>W</b>	8.00 + 0.30 -0.10

**Product Disclaimer:** Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. <http://www.littelfuse.com/disclaimer-electronics>.