

OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS

Parameters	Conditions	ECX-L2 (+2.5V)			ECX-L3 (+3.3V)			Units
		MIN	TYP	MAX	MIN	TYP	MAX	
Frequency Range		10.000		1500.0	10.000		1500.0	MHz
Operating Temperature	Standard	0		+70	0		+70	°C
	Extended (N Option)	-40		+85	-40		+85	°C
Storage Temperature		-55		+125	-55		+125	°C
Supply Voltage	V _{DD}	+2.375	+2.5	+2.625	+3.135	+3.3	+3.465	VDC
Frequency Stability *	Option A			±100			±100	ppm
	Option B			±50			±50	ppm
	Option C			±25			±25	ppm
	Option D			±20			±20	ppm
Input Current	10.0 ~ 100.0 MHz			16			18	mA
	100.1 ~ 250.0 MHz			18			20	mA
	250.1 ~ 500 MHz			21			22	mA
	500.1 ~ 1500.0 MHz			26			28	mA
Output Symmetry	@ 50% V _{DD} level			45/55			45/55	%
Output Load	Load between each Output			100			100	Ω
Output Enable	Pin 1 **	0.7%			0.7%			Vdd
Output Disable	Pin 1			0.3%			0.3%	Vdd
Disable Current			16		16			mA
Output Enable Time				200			200	ns
Output Disable Time	Pin 1 = VIL			50			50	ns
Differential Output Voltage		175	350		175	350		mV
Offset Voltage			1.25			1.25		V
Rise and Fall Times	10% V _{DD} to 90% Level	150	350	500	150	350	500	pS
Aging	@ +25°C (first year)			±2			±2	PPM
Start-up Time	@ +25°C (first year)			10			10	ms
Absolute Voltage Range				+3.63			+3.63	VDC
Moisture Sensitivity Level				1				
Termination Finish				Au				
ESD Sensitivity	Human Body Model			3kV Max.				

*Note: Inclusive of 25 °C tolerance, operating temperature, input voltage change, load change, shock and vibration.


**Note: Internal pull-up resistor active output if pin 1 is left open.

Part Numbering Guide: Example ECX-L35BN-156.250						
Series	Voltage	Package Size (mm)	Stability	Operating Temperature	Frequency	Packaging
ECX-L (LVDS Output)	2 = +2.5V 3 = +3.3V	2 = 2.5 x 2 3 = 3.2 x 2.5 5 = 5 x 3.2 7 = 7 x 5	A = ± 100 ppm B = ± 50 ppm C = ± 25 ppm D = ± 20 ppm	L = -10 ~ +70°C M = -20 ~ +70°C N = -40 ~ +85°C P = -40 ~ +105°C	Customer Specified	Blank =(Bulk) -TR=Tape & Reel (1K Min/Mult)

Phase Noise and Jitter Data (typical)

SSB Phase Noise Data (dBc/Hz typical)	Frequency (offset)	77.760	122.880	125.000	156.250	212.5	491.520	622.080	1000	1250
10 Hz		-64	-68	-63	-55	-62	-61	-48	-52	-42
100 Hz		-84	-99	-94	-85	-93	-86	-85	-82	-81
1 KHz		-118	-113	-113	-109	-105	-100	-101	-93	-93
10 KHz		-128	-119	-118	-116	-113	-105	-102	-97	-96
100 KHz		-137	-120	-119	-118	-115	-105	-103	-97	-97
1 MHz		-145	-140	-137	-139	-135	-126	-124	-116	-119
5 MHz		-152	-142	-146	-146	-143	-137	-133	-127	-129
Phase Jitter pS 12 KHz ~ 20 MHz, RMS		0.9	0.8	1.1	0.9	1.0	1.1	1.2	1.5	1.1

Phase Noise Plot of ECX-L35BN-77.760 (typical)



Package Data	
Item	Description
Lid	Metal
Base	Ceramic
Plating	Gold/Nickel Surface/Under

Dimensions (mm)

7 = 7x5 Package




Figure 1) Top, Side, Bottom & Land

5 = 5x3.2 Package




Figure 2) Top, Side, Bottom & Land

3 = 3.2x2.5 Package




Figure 3) Top, Side, Bottom & Land

2 = 2.5x2 Package





Figure 4) Top, Side, Bottom & Land

Suggested Reflow Profile



Pin Connections

Pin #	Function
1	O/E or No Connect
2	No Connect
3	Ground
4	Differential Output
5	Complementary Output
6	Supply Voltage

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ECS:](#)

[ECX-L37BN-125.000](#) [ECX-L37BN-75.000](#) [ECX-L37BN-212.500](#) [ECX-L37BN-100.000](#) [ECX-L37BN-200.000](#) [ECX-L35BN-120.000](#) [ECX-L35CM-80.000](#) [ECX-L37BN-250.000](#) [ECX-L37CM-155.520](#) [ECX-L35CM-1000.000](#) [ECX-L35BN-20.000](#) [ECX-L37CM-106.250](#) [ECX-L37BN-50.000](#) [ECX-L37BN-500.000](#) [ECX-L37CM-50.000](#) [ECX-L37CM-24.576](#) [ECX-L35BN-250.000](#) [ECX-L32BN-10.000](#) [ECX-L35BN-40.000](#) [ECX-L37BN-150.000](#) [ECX-L37BN-80.000](#) [ECX-L37CM-622.080](#) [ECX-L35BN-156.250](#) [ECX-L37CM-100.000](#) [ECX-L37CM-125.000](#) [ECX-L37CM-30.000](#) [ECX-L37CM-1000.000](#) [ECX-L37BN-60.000](#) [ECX-L37BN-106.250](#) [ECX-L37CM-500.000](#) [ECX-L35BN-125.000](#) [ECX-L37BN-312.500](#) [ECX-L37BN-156.250](#) [ECX-L37BN-25.000](#) [ECX-L35CM-500.000](#) [ECX-L35BN-100.000](#) [ECX-L37BN-40.000](#) [ECX-L37CM-25.000](#) [ECX-L35DM-100.000](#) [ECX-L35AM-200.000](#) [ECX-L35AM-250.000](#) [ECX-L37BM-125.000](#) [ECX-L37BM-166.6667](#) [ECX-L37BM-62.500](#) [ECX-L37DM-300.000](#) [ECX-L37BM-622.080](#) [ECX-L37AM-500.000](#) [ECX-L37BM-350.000](#) [ECX-L37CM-311.040](#) [ECX-L37CM-350.000](#) [ECX-L37DM-1000.000](#) [ECX-L37BN-300.000](#) [ECX-L35AM-575.250](#) [ECX-L37BM-500.000](#) [ECX-L37CN-800.000](#) [ECX-L37BM-266.666666](#) [ECX-L35AM-300.000](#) [ECX-L35CM-400.000](#) [ECX-L37BM-270.000](#) [ECX-L37BN-266.666](#) [ECX-L37CM-781.250](#) [ECX-L37CN-869.215](#) [ECX-L37CN-622.000](#) [ECX-L35DM-500.000](#) [ECX-L37AN-311.040](#) [ECX-L37CM-400.000](#) [ECX-L35BM-309.000](#) [ECX-L37BM-400.000](#) [ECX-L37DM-945.000](#) [ECX-L35BM-350.000](#) [ECX-L37BM-360.000](#) [ECX-L37BN-350.000](#) [ECX-L37CN-300.000](#) [ECX-L35CN-1000.000](#) [ECX-L37AM-300.000](#) [ECX-L37BM-625.000](#) [ECX-L37DM-600.000](#) [ECX-L37DM-100.000](#) [ECX-L37CN-200.000](#) [ECX-L37CM-600.000](#) [ECX-L25CN-622.080](#) [ECX-L35AM-1100.000](#) [ECX-L37AN-256.000](#) [ECX-L37BM-312.500](#) [ECX-L37CN-1310.720](#) [ECX-L35CN-275.000](#) [ECX-L35BM-1000.000](#) [ECX-L35BM-312.500](#) [ECX-L37DM-105.000](#) [ECX-L37DM-210.000](#) [ECX-L35DM-1000.000](#) [ECX-L37BN-133.300](#) [ECX-L37DM-155.520](#) [ECX-L37AN-155.520](#) [ECX-L37DM-150.000](#) [ECX-L37AN-212.500](#) [ECX-L37BM-106.000](#) [ECX-L35AM-1280.000](#) [ECX-L35CN-125.000](#) [ECX-L37AN-200.000](#)