

ME A-1600-SM

GNSS and Iridium screw mount

Part #: 189-00059-01

Description

The MEA-1600-SM Screw Mount Antenna is a 2-in-1 antenna solution, with high gain and efficiency ideal for maintaining constant global connectivity via Iridium. The MEA-1600-SM covers all GPS/GLONASS/Galileo and Iridium frequencies. This is an ideal antenna for Iridium SBD, navigation and telematics systems, IoT applications and remote connectivity. This screw mount antenna is easy to install with maximum durability. The MEA-1600-SM has a two cables with a SMA-Male standard connector, 3m standard cable length and is fully customizable by offering additional connector types, cable lengths and cable types. This antenna is low profile, rugged and IP67 rated.

Cable 1 - GNSS Ceramic Active Antenna

Frequency Range	1575.42 MHz	1598-1606 MHz
Band	1575 MHz	1602 MHz
Return Loss	≤ -15.0 dB	
VSWR	≤ 1.4:1 dB	
Efficiency	68.1%	
Impedance	50 Ohms	
Active Gain	28 dB @ 2.7 V	
Radiation Pattern	Hemispherical	
Polarization	RHCP	
Saw Filter Type	Pre-filter	
Noise Figure	1.5 dB Typ	
Voltage	1.5 – 3.6 V	
Current Consumption	9 mA Typ	
Power Consumption	24.3 mW Typ	
ESD Protection	2kV	
Patch Size	25 x 25 x 4 mm	

Cable 2 - Iridium Antenna

Frequency Range	1616 - 1627 MHz
Band	1621 MHz
Return Loss	-12.5 dB
VSWR	1.6:1
Efficiency	68.1%
Peak Gain	5.2 dBic
Average Gain	-1.8 dB
Radiation Pattern	Hemispherical
Polarization	RHCP



Features





- 2in1 antenna: GPS/GLONASS/Galileo and Iridium
- High performance
- Low Profile
- Cable 1: GPS/GLONASS /Galileo - 1575-1606 MHz
- Cable 2: Iridium - 1616-1627 MHz
- Iridium certified antenna
- Easy mounting: Screw Mount
- Anti-Rotation Mounting
- Customizable Cable and Connector
- Low profile 80 × 74 × 25.6 mm
- IP67
- IP69

Applications

- Iridium SBD
- Satellite IoT applications
- Telematic
- Navigation
- Satellite Communications
- Remote surveillance
- Monitoring

Mechanical Specifications	
Antenna Dimensions	80 x 74 x 25.6 mm
Operating Temperature	-40 °C to +85 °C
Certificates	Iridium Certified, IP67, IP69
Connector	SMA male
Antenna Color	Black, White
Radome Type	PC + ASA
Substance Compliance	RoHS
Cable Length	300 cm
Mounting style	Screw mount
Max. Tighten Torque	5 Nm

*Antenna Measurement Conditions:
Mounted on metal plate of 30x30cm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Maxtena:

[MEA-1600-SM](#)