

[kingston.com/usb](http://kingston.com/usb)

## DATATRAVELER MAX SERIES

# Unparalleled Performance

Kingston's DataTraveler® Max series USB flash drives leverage the latest USB 3.2 Gen 2 standard to deliver record-breaking read/write speeds up to 1,000/900MB/s<sup>2</sup>. Designed with portability and convenience in mind, the unique ridged casing protects the connector when not in use and is easily moved with a single motion. Available in USB Type-C<sup>®1</sup> and Type-A connections to support next-gen and traditional laptops and desktops. The DT Max series delivers premium performance and expanded capacities up to 1TB<sup>3</sup> making them the ideal solution for transferring and storing large digital files such as HD photos, 4K/8K videos, music and more.

Both the Type-C and Type-A connector varieties in the DT Max series are backed by a limited five-year warranty, free technical support and legendary Kingston reliability.

- › **Advanced USB 3.2 Gen 2 Drives**
- › **Unique ridged casing with keyring loop**
- › **Up to 1,000MB/s<sup>2</sup> read speeds**
- › **Capacities up to 1TB<sup>3</sup>**

[more >>](#)

## FEATURES / BENEFITS

**Latest USB 3.2 Gen 2 Standard** — Move your files in a flash with incredible speeds up to 1,000MB/s Read, 900MB/s Write.<sup>2</sup>

**Uncompromised Storage** — Available in a range of high capacities from 256GB-1TB<sup>3</sup> to carry your digital library on the go.

**Dual Option for Connectivity** — USB Type-C® and Type-A connector varieties to support next-gen and traditional laptops or desktops for seamless file transfers.

**Unique Design** — Convenient one-handed sliding cap, LED status indicator, and functional keyring loop.

## SPECIFICATIONS

### Capacities<sup>3</sup>

256GB, 512GB, 1TB

### Interface

USB 3.2 Gen 2

### Speed<sup>2</sup>

Up to 1,000MB/s read, 900MB/s write

### Dimensions

Type-C: 82.17 mm x 22.00 mm x 9.02 mm  
Type-A: 91.17 mm 22.00 mm x 9.02 mm

### Weight

Type-C: 12g

Type-A: 14g

### Operating temperature

0°C~60°C

### Storage temperature

-20°C~85°C

### Warranty/support

5-year warranty with free technical support

### Compatible with

Windows® 11, 10, 8.1, macOS® (v. 10.14.x +), Linux (v. 2.6.x +),  
Chrome OS™



## KINGSTON PART NUMBERS

Type-C
DTMAX/256GB
DTMAX/512GB
DTMAX/1TB

Type-A
DTMAXA/256GB
DTMAXA/512GB
DTMAXA/1TB

## COMPATIBILITY TABLE

	USB 3.2 Gen 2
Windows® 11	✓
Windows® 10	✓
Windows® 8.1	✓
macOS® (v. 10.14.x +)	✓
Linux (v. 2.6.x +)	✓
Chrome OS™	✓

1. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum.

2. Speed may vary due to host hardware, software and usage.

3. Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Memory Guide.



THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.  
©2022 Kingston Technology Corporation, 17600 Newhope Street, Fountain Valley, CA 92708 USA. All rights reserved.  
All trademarks and registered trademarks are the property of their respective owners. MKD-452

**Kingston**  
TECHNOLOGY

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kingston:](#)

[DTMAXA/1TB](#) [DTMAX/256GB](#) [DTMAXA/512GB](#) [DTMAXA/256GB](#) [DTMAX/512GB](#) [DTMAX/1TB](#)