


Digi-Temp® - Thermometers

Continuous Temperature Measuring

A comprehensive system of thermometers based on proprietary formulations of liquid crystals that change color at a designated temperature. Current temperature is displayed as a Green event.

DigiTemp® EZ Easy Read

- Instant Response - Continuous Readout
- No Batteries or Glass - Non Toxic
- Temperature Range: -22 to 248°F (-30 to 120°C)
- Accuracy
 - 30 to 59°C (±1°C)
 - 60 to 89°C (±2°C)
 - 90 to 120°C (±3°C)
- Self Adhesive
- Cost Effective



Specifications:

- Size: 5.2" x 0.59" (132mm x 15mm)
- Type: Horizontal, self adhesive
- Scale: °F and °C



7 LEVEL THERMOMETER

1	°F	-22	-13	-4	5	14	23	32
2	°C	-30	-25	-20	-15	-10	-5	0
3	°F	32	41	50	59	68	77	86
4	°C	0	5	10	15	20	25	30
5	°F	86	95	104	113	121	131	140
6	°C	30	35	40	45	50	55	60
7	°F	140	149	158	167	176	185	194
8	°C	60	65	70	75	80	85	90
9	°F	194	203	212	221	230	239	248
10	°C	90	95	100	105	110	115	120

Specifications:

- Size: 0.5" x 1.77" (12.5mm x 45mm)
- Type: Horizontal, self adhesive
- Scale: °F and °C

7 LEVEL THERMOMETER

°F	50	55	60	65	70	75	80
°C	9	12	15	18	21	24	27

Specifications:


- Size: 2.75" x 0.394" (70mm x 10mm)
- Type: Vertical, self adhesive
- Scale: °F and °C

16 LEVEL THERMOMETER

1	°F	26	28	30	32	34	36	38	40	42	44	46	48	50	52	54	56
2	°C	-3	-2	-1	0	1	2	3	4	6	7	8	9	10	11	12	13
3	°F	58	60	62	64	66	68	70	72	74	76	78	80	82	84	86	88
4	°C	14	16	17	18	19	20	21	22	23	24	26	27	28	29	30	31
5	°F	90	92	94	96	98	100	102	104	106	108	110	112	114	116	118	120
6	°C	32	33	34	35	37	38	39	40	41	42	43	44	45	47	48	49


Specifications:

- Size: 5" x 0.5" (127mm x 12.5mm)
- Type: Vertical, self adhesive
- Scale: °F and °C



Specifications:

- Size: 3.5" x 0.5" (189mm x 12.5mm)
- Type: Horizontal, self adhesive
- Scale: °F and °C



Specifications:

- Size: 2.5" x 0.5" (63.5mm x 12.5mm)
- Type: Vertical, self adhesive
- Scale: °F and °C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SpotSee:

<u>2024 AKC36</u>	<u>4002A ADP10</u>	<u>4002A ADP100</u>	<u>4002B ADP10</u>	<u>4060C ADP100</u>	<u>4060D ADP10</u>	<u>4060D ADP100</u>
<u>4060E ADP10</u>	<u>4060E ADP100</u>	<u>4003E ADP100</u>	<u>4060A ADP10</u>	<u>4060A ADP100</u>	<u>4060B ADP10</u>	<u>4060B ADP100</u>
<u>4060C ADP10</u>	<u>4003B ADP100</u>	<u>4003C ADP10</u>	<u>4003C ADP100</u>	<u>4003D ADP10</u>	<u>4003D ADP100</u>	<u>4003E ADP10</u>
<u>4002B ADP100</u>	<u>4002C ADP10</u>	<u>4002C ADP100</u>	<u>4003A ADP10</u>	<u>4003A ADP100</u>	<u>4003B ADP10</u>	<u>2000 AVKC36</u>