



## Main Features

- ♦ Onboard Intel® Celeron® processor J6413 Quad Core 1.8GHz
- ♦ 1 x DP++ and 1 x HDMI for dual independent display support
- ♦ 1 x Intel® 2,5GbE LAN port, support WoL & PXE
- ♦ 2 x Marvell PHY GbE LAN ports, support WoL
- ♦ 2 x RS232/422/485 with auto-flow control and 2.5KV isolation protection
- ♦ 2 x USB 3.0, 4 x USB 2.0

- ♦ 1 x Front access 2.5" SATA HDD/SSD tray, support ComboStorage (2.5" SSD + MicroSD card)
- ♦ 2 x mini PCIe socket support optional modules and mSATA device
- ♦ 1 x M.2 3042/3052 Key B socket
- ♦ TPM 2.0 onboard
- ♦ Support +24VDC input, support ATX power mode

## Product Overview

Powered by Intel® Celeron® processor J6413 (formerly code-named "Elkhart Lake"), the NIFE 210 presents an intelligent fanless PC-based controller and IoT gateway for factory automation. The NIFE 210 supports up to 32GB DDR4 memory and has several options on storage devices like mSATA, front-access 2.5" SSD/HDD, and supports ComboStorage (2.5" SSD + MicroSD card) for applications requiring storage redundancy and capacity expansion. The NIFE 210 features all-front I/O for easy installation and maintenance and has high integration ability with three LAN ports, two isolated COM ports, and optional M.2 and mini-PCIe modules, allowing reliable connection with devices in factory automation applications (with optional PROFIBUS, PROFINET, DeviceNET, EtherCAT, EtherNet/IP, CANopen, SERCOSIII master module), IoT applications (with optional Wi-Fi, 5G/4G LTE module) and communication applications (with optional GPIO, RS232/422/485), and features onboard TPM 2.0 for enhanced security. The NIFE 210 is designed for industrial environments and is compliant with EN61000-6-2, and EN61000-6-4 to ensure the reliability and safety of industrial equipment and systems, support DIN-rail mounting, 24V DC power input with +/-20% range and reverse polarity protection, and can be operated in an extended operating temperature range of -10~60 °C, making it ideal for the next generation of M2M intelligent systems, serving as both a factory automation controller and a gateway.

## Specifications

### CPU Support

- ♦ Onboard Intel® Celeron® processor J6413 Quad Core 1.8GHz

### Main Memory

- ♦ 1 x SO-DIMM DDR4 non ECC up to 3200 MT/s, 32GB max.

### Display Option

- ♦ Dual independent display
  - 1 x HDMI
  - 1 x DP 1.4++

### Status LEDs

- ♦ 1 x Power LED
- ♦ 1 x HDD/SSD access LED
- ♦ 1 x Battery LED
- ♦ 4 x COM ports Tx/Rx LED
- ♦ 5 x Programmable GPO LEDs

### Storage Device

- ♦ 1 x 2.5" HDD/SSD (external, SATA 3.0), support ComboStorage (2.5" SSD + MicroSD card)
- ♦ 1 x mSATA (via internal mini-PCIe socket)

### Top I/O Interface

- ♦ 1 x 3-pin remote switch
- ♦ 6 x Antenna holes


### Front I/O Interface

- ♦ ATX power on/off switch
- ♦ 1 x Intel® I226-V 2,5GbE LAN port, support WoL and PXE
- ♦ 2 x Marvell PHY GbE LAN ports, support WoL
- ♦ 1 x DP 1.4 ++
- ♦ 1 x HDMI 2.0
- ♦ 2 x USB 3.0 (900mA per each)
- ♦ 4 x USB 2.0 (500mA per each)
- ♦ 1 x Front access 2.5" HDD/SSD tray (SATA 3.0) or ComboStorage (2.5" SSD + MicroSD card)
- ♦ 2 x DB9 for COM1/COM2 RS232/422/485 with auto-flow control and 2.5KV isolation protection
- ♦ 1 x 3-pin DC input, typical 24V DC input with ±20% range

### Expansion Slot

- ♦ 1 x mini-PCIe full size (PCIe x1, USB 2.0, SATA, SIM)
- ♦ 1 x mini-PCIe full size for Fieldbus (FBI) module (PCIe x1, USB 2.0)
- ♦ 1 x M.2 3042/3052 Key B (PCIe x1, USB 3.0, SIM)

## Dimension Drawing



### Power Requirement

- ♦ 24V DC input with +/-20% range, with reverse polarity protection
- ♦ 1 x Optional 24V, 60W power adapter

### Dimensions

- ♦ 85mm (W) x 157mm (D) x 214mm (H)

### Construction

- ♦ Aluminum and metal chassis with fanless design

### Environment

- ♦ Operating temperature:
- ♦ Ambient with air flow: -10°C to 60°C (according to IEC60068-2-1, IEC60068-2-2, IEC60068-2-14)
- ♦ Storage temperature: -20°C to 80°C
- ♦ Relative humidity: 10% to 95% (non-condensing)
- ♦ Shock protection:
  - HDD: 20G, half sine, 11ms, IEC60068-2-27
  - SSD: 50G, half sine, 11ms, IEC60068-2-27
- ♦ Vibration protection w/ SSD condition:
  - Random: 2Grms @ 5~500Hz, IEC60068-2-64
  - Sinusoidal: 2Grms @ 5~500Hz, IEC60068-2-64

### Certifications

- ♦ CE approval
  - EN61000-6-2
  - EN61000-6-4
- ♦ FCC Class A
- ♦ LVD

### OS Support

- ♦ Windows 11 Pro, 64-bit
- ♦ Windows 10 Enterprise, 64-bit
- ♦ Linux Kernel 5.10

## Ordering Information

- ♦ **NIFE 210-E01 (P/N: 10J70021000X0)**  
Intel® Celeron® processor J6413 Quad Core 1.8GHz fanless system
- ♦ **24V, 60W AC/DC power adapter w/o power cord (P/N: 7400060054X00)**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Nexcom:](#)

[10J70021000X0](#)