

ASUS NUC 14 PRO+

Style Meets Unparalleled Performance



ASUS NUC 14 Pro+ ultracompact PC offers superior performance that bests all other competitive mini-PCs. It features an eye-catching 5x4-inch premium anodized aluminum chassis with a dynamic cooling system that is whisper quiet. Its toolless chassis access allows channel customers and system integrators to reduce their integration time and costs. Plus, the ASUS NUC 14 Pro+ is the first NUC Pro to harness the prowess of the Intel® Core™ Ultra 9 processor to locally run generative AI workloads. With improved I/O capabilities for increased productivity and collaboration and certified Bluetooth® dongle-free connectivity, ASUS NUC 14 Pro+ makes a home office as efficient as the workplace.

Key Selling Points

Performance: Superior performance besting all other competitive mini-PCs

Design: Features an eye-catching 5 x 4-inch anodized aluminum chassis

AI Ready: Harnesses the prowess of the Intel® Core™ Ultra 9 processor to locally run generative AI workloads

Wi-Fi Sensing: Takes advantage of Wi-Fi sensing to deliver instant availability while reducing power consumption

Wireless Connectivity: Delivers seamless connectivity for certified Bluetooth® dongle-free experiences

Customizable: Designed for toolless chassis access making upgrades easier, safer, and faster

Audience:

- Small and Medium Business Enterprises
- Remote Workers
- Style-conscious Business Executives

Target Usages:

- Collaboration
- Content Creation / Productivity / Entertainment
- Remote Work/Work from Home
- Digital Signage

ASUS NUC 14 PRO+

Mini-PC & Kit Specifications



Image A

| Marketing Name | ASUS NUC 14 Pro+ Mini-PC | ASUS NUC 14 Pro Kit |
|------------------------|---|---|
| Project Code | NUC14RVS | NUC14RVS-B |
| Photo | Image A | TBD |
| ASUS Logo | Yes | No |
| ASUS NUC Logo | Yes | No |
| Color | Silver | Silver |
| OS Support | Windows 11 64-bit | Windows 11 64-bit Ubuntu 24.04 LTS 64-bit RedHat Enterprise Linux 64-bit |
| CPU | Intel® Core™ Ultra 9 Processor 185H, cTDP 65W Intel® Core™ Ultra 7 Processor 165H, cTDP 65W Intel® Core™ Ultra 7 Processor 155H, cTDP 65W Intel® Core™ Ultra 5 Processor 135H, cTDP 65W Intel® Core™ Ultra 5 Processor 125H, cTDP 65W | Intel® Core™ Ultra 9 Processor 185H, cTDP 65W Intel® Core™ Ultra 7 Processor 165H, cTDP 65W Intel® Core™ Ultra 7 Processor 155H, cTDP 65W Intel® Core™ Ultra 5 Processor 135H, cTDP 65W Intel® Core™ Ultra 5 Processor 125H, cTDP 65W |
| Chipset | Integrated | Integrated |
| Graphics | Intel® Arc™ GPU ¹ | Intel® Arc™ GPU ¹ |
| Memory | 2 x SO-DIMM, Up to DDR5-5600, 48GB*2 | 2 x SO-DIMM, Up to DDR5-5600, 48GB*2 |
| Storage | 1 x M.2 2280 PCIe Gen4x4, supports 128GB~4TB NVMe SSD 1 x M.2 2242 PCIe Gen4x4, supports 128GB~2TB NVMe SSD | 1 x M.2 2280 PCIe Gen4x4, supports 128GB~4TB NVMe SSD 1 x M.2 2242 PCIe Gen4x4, supports 128GB~2TB NVMe SSD |
| Wireless Network | Intel® Wi-Fi 6E AX211 (Gig+), Bluetooth 5.3 | Intel® Wi-Fi 6E AX211 (Gig+), Bluetooth 5.3 |
| LAN | Intel® Ethernet Controller I226-V/LM, 2.5G ² | Intel® Ethernet Controller I226-V/LM, 2.5G ² |
| Audio | N/A | N/A |
| TPM | fTPM | fTPM |
| Card Reader | None | None |
| HDMI CEC | Yes, 2 ports on back panel | Yes, 2 ports on back panel |
| Front I/O Ports | 1 x USB 3.2 Gen2x2 Type-C 2 x USB 3.2 Gen2 Type-A | 1 x USB 3.2 Gen2x2 Type-C 2 x USB 3.2 Gen2 Type-A |
| Back I/O Ports | 2 x Thunderbolt 4 Type-C w/ DisplayPort 1.4 1 x USB 3.2 Gen 2 Type-A 1 x USB 2.0 Type-A 2 x HDMI 2.1 (TMDS) 1 x RJ45 LAN 1 x DC-in 1 x Kensington Lock | 2 x Thunderbolt 4 Type-C w/ DisplayPort 1.4 1 x USB 3.2 Gen 2 Type-A 1 x USB 2.0 Type-A 2 x HDMI 2.1 (TMDS) 1 x RJ45 LAN 1 x DC-in 1 x Kensington Lock |
| Side I/O Ports | N/A | N/A |
| Power Supply | 19.5VDC, 7.69A, 150W Power Adapter (Core Ultra 9) 19VDC, 6.32A, 120W Power Adapter (Core Ultra 5/7) | 19.5VDC, 7.69A, 150W Power Adapter (Core Ultra 9) 19VDC, 6.32A, 120W Power Adapter (Core Ultra 5/7) |
| Operating Temp | 0 to 35C | 0 to 35C |
| Storage Temp | -40 to 60C | -40 to 60C |
| Humidity | 0%~92% non-condensing ³ | 0%~92% non-condensing ³ |
| Dimensions (W x D x H) | 144mm x 112mm x 41mm | 144mm x 112mm x 41mm |
| Weights | 600g | 600g |
| Accessories | AC Adapter + Power Cord ⁴ VESA Bracket and Screws Safety/Caution/Regulatory Insert Warranty Card | AC Adapter + Power Cord ⁴ VESA Bracket and Screws Safety/Caution/Regulatory Insert Warranty Card |



⁽¹⁾ Intel® Arc™ GPU requires using 2 x SO-DIMM

⁽²⁾ Intel® Ethernet Controller I226-LM included on vPro enabled systems

⁽³⁾ Humidity Info detail please check link: [Non-condensing humidity as defined by temperature vs dew point.](#)
⁽⁴⁾ Power cord included is region specific, and some SKUs do not include the power cord

ASUS NUC 14 PRO+

Connections



- 1 1x USB 3.2 Gen2x2, Type-C
- 2 2 x USB 3.2 Gen2, Type-A
- 3 1x Power Bottom
- 4 1x Kensington Lock


- 5 1x DC-in
- 6 2 x HDMI 2.1 (TMDS)
- 7 1x Thunderbolt™ 4

- 8 1x 2.5Gb Ethernet
- 9 1x Thunderbolt™ 4
- 10 1x Thunderbolt™ 4

What's in the box



NUC 14 PRO+



120 / 150 W
power supply



Inserts



Power Cord*



VESA bracket and
Screws

NOTE:

- The most up-to-date and accurate product specifications are available on www.asus.com for download.
- Product and accessory images are for illustrative purposes only. The actual appearance and specifications may vary depending on the model.
- *The bundled power adapter may vary depending on the model and the country (or region) of sale.
- Some bundled accessories may vary depending on the model. For details on these accessories, refer to their respective user manuals.
- If the device or its components fail or malfunction during normal and proper use within the warranty period, bring the warranty card to the ASUS Service Center for replacement of the defective components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Asus:](#)

[RNUC14RVSU70000UI](#) [RNUC14RVSU50000UI](#) [RNUC14RVSU90000UI](#)