

## M12-CC-SCR-PUSH-IN-5P-LCOD-M-STR



Image is for illustration purposes only. Please refer to product description.

Part number	21 12 999 1510
Specification	M12-CC-SCR-PUSH-IN-5P-LCOD-M-STR
HARTING eCatalogue	<a href="https://b2b.harting.com/21129991510">https://b2b.harting.com/21129991510</a>

### Identification

Category	Connectors
Series	Circular connectors M12
Identification	Power
Element	Cable connector
Specification	Straight

### Version

Termination method	Push-In
Gender	Male
Shielding	Unshielded
Number of contacts	5
Number of power contacts	4
Number of special contacts	1
Specification of special contacts	FE contact
Coding	L-coding
Locking type	Screw locking

### Technical characteristics

Conductor cross-section	0.5 ... 2.5 mm <sup>2</sup>
Rated current	16 A
Rated voltage	63 V
Rated impulse voltage	1.5 kV
Pollution degree	3

## Technical characteristics

Overvoltage category	III
Insulation resistance	>10 <sup>8</sup> Ω
Contact resistance	≤10 mΩ
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	24
Limiting temperature	-40 ... +125 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 mated condition
Cable diameter	6.6 ... 11.6 mm
Isolation group	I (600 ≤ CTI)

## Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 61076-2-111
PROFINET	Yes

## Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140454989
ETIM	EC002635
eCl@ss	27440116 Circular connector (for field assembly)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21129991510](#)