

GT17005

Gate Drive Transformers

ice
components



FEATURES

- 9.2 mm Creepage
- 8.0 mm Clearance
- Suitable for pick-and-place applications
- Operating frequency of 420kHz
- Designed to work with TI UCC5390SCD and SN6505B
- Eval Module: UCC5390SCDEVM-010

PACKAGING

Reel Diameter: 13"


Reel Width: 24 mm

Pieces Per Reel: 500


APPLICATIONS

- Gate Drive Transformer
- Signal Transformer Across Isolation Barrier


Mechanical Drawing



Recommended PCB Layout



Schematic



Unit: mm

Electrical Specifications

Part Number	Turns Ratio Drive:Gate	Drive Ind. ¹ (μ H, min.)	DCR (m Ω , max.)	Lkg. Ind. ⁴ (nH, max.)	E-T Prod. ⁵ (V- μ s)	Hi-Pot ⁶ (Drive:Gate)
GT17005	1:3.5	50	600:1200	500	70.6	3750 Vac

Notes:

1. Tested at 100kHz, 0.1Vrms (Terminals 1-2).
2. Electrical specifications at 25°C.
3. Operating range: -40°C to +125°C.
4. Drive terminals 1-3 (4, 5, 6 shorted).
5. E-T product rating is for (6-4) windings and is based upon flux density of 2800 Gauss at 25°C in a bipolar drive applications.
6. Tested at 60Hz, 1mA, 1 second.
7. Meets UL 94V-0.

Specifications subject to change without prior notice.

Tel.: 800-729-2099

www.icecomponents.com



(10/17) GT17005

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ICE Components:](#)

[GT17005](#)