

3 Pole Contactor 50–60 FLA

HCC Series



3 pole contactors are typically used in commercial applications. These contactors utilize three wires to control electrical current direction. Our engineers and quality specialists provide services that meet or exceed customer requirements—all products undergo in-house testing and validation. We carry extensive inventory to meet delivery schedules.

Features

- 3 Pole NO
- Silver Cadmium Oxide Contacts
- UL 508 File No. E227250
- CSA File No. 221260 (1456104)
- Multiple mounting and termination options available, contact us for more information.

We can custom engineer a solution to meet any need. Just ask.

815.626.5170 | HartlandControls.com

Specifications

Initial Dielectric Strength

Between Contacts & Coils: 2,200 VAC
Between Poles: 2,200 VAC
Between Open Contacts: 2,200 VAC

Arc Cover

Standard

Insulation System

130°C Class B

Temperature Range

-40°C to +65°C
-40°F to +150°F

Unit Weight

50–60 FLA
22.4 oz
640 g

Power Pole Terminations

Aluminum box lug

Wire Size

50–60 FLA Box Lug
14-2

Recommended Tightening Torque


Box lug: 50 in. lbs

Quick Connects

Coil terminals:
Dual: .250" QC or #6-32 screw/.250" QC

Power terminals:
Dual .250" QC

Dimensions (inches [mm])



3 Pole Contactor 50–60 FLA

HCC Series

3 Pole Contactors				
50	65	300	250	200
60	75	360	300	240

3 Pole Contactors								
50	3	–	7.5	15	–	25	–	25
60	5	–	10	25	–	30	–	30

Suitable for use on a circuit capable of delivering not more than 5k rms symmetrical amperes, 600 Volts maximum at 400% of fuse and circuit breaker.

Multiple mounting and termination options available, contact us for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[CON-3/120/30](#) [CON-3/120/30L](#) [CON-3/120/40](#) [CON-3/24/30](#) [CON-3/24/30L](#) [CON-3/24/40](#) [CON-3/240/30](#) [CON-](#)
[3/240/30L](#) [CON-3/240/40](#) [CON-3/480/40](#)