




features

- Wide-side termination (reverse-geometry) type flat chip resistor
- High reliability and performance with T.C.R. $\pm 100 \times 10^{-6}/K$, resistance tolerance $\pm 0.5\%$
- Products with lead-free terminations meet EU RoHS requirements. EU RoHS regulation is not intended for Pb-glass contained in electrode, resistor element and glass.
- AEC-Q200 Tested

dimensions and construction



Type (Inch Size Code)	Dimensions inches (mm)				
	L	W	c	d	t
1E (0204)	.020 \pm .002 (0.5 \pm 0.05)	.039 \pm .002 (1.0 \pm 0.05)	.006 \pm .002 (0.15 \pm 0.05)	.006 \pm .002 (0.15 \pm 0.05)	.014 \pm .002 (0.35 \pm 0.05)
1J (0306)	.031 \pm .004 (0.8 \pm 0.1)	.063 \pm .004 (1.6 \pm 0.1)	.006 \pm .004 (0.15 \pm 0.1)	.008 \pm .004 (0.2 \pm 0.1)	.018 \pm .004 (0.45 \pm 0.1)
2A (0508)	.049 \pm .006 (1.25 \pm 0.15)	.079 \pm .006 (2.0 \pm 0.15)	.012 \pm .008 (0.3 \pm 0.2)	.014 \pm .008 (0.35 \pm 0.2)	.022 \pm .004 (0.55 \pm 0.1)
2B (0612)	.063 \pm .006 (1.6 \pm 0.15)	.126 \pm .008 (3.2 \pm 0.2)	.012 \pm .008 (0.3 \pm 0.2)	.018 \pm .006 (0.45 \pm 0.15)	.024 \pm .004 (0.6 \pm 0.1)
2H (1020)	.098 \pm .006 (2.5 \pm 0.15)	.197 \pm .006 (5.0 \pm 0.15)	.016 \pm .008 (0.4 \pm 0.2)	.030 \pm .006 (0.75 \pm 0.15)	
3A (1225)	.122 \pm .006 (3.1 \pm 0.15)	.252 \pm .006 (6.3 \pm 0.15)	.018 \pm .008 (0.45 \pm 0.2)		

ordering information

WK73R	1J	T	TE	33L0	F
Type	Size	Termination Material	Packaging	Nominal Resistance	Resistance Tolerance
WK73R	1E: 0.33W ¹ 1J: 0.5W ¹ , 0.66W ¹ 2A: 0.75W ¹ , 1W ¹ 2B: 0.75W ¹ , 1.5W ¹ 2H: 1W ¹ , 2W ¹ 3A: 1.5W, 3W ¹	T: Sn	TP: 0204: 7" 2mm pitch punched paper TD: 0306, 0508, 0612: 7" 4mm pitch punched paper TE: 1020, 1225: 7" embossed plastic For further information on packaging, please refer to Appendix A	$\pm 1\%$: 3 significant figures + 1 multiplier "R" indicates decimal on value $<100\Omega$ $\pm 5\%$: 2 significant figures + 1 multiplier "R" indicates decimal on values $<10\Omega$ All values less than 0.1Ω ($100m\Omega$) are expressed in $m\Omega$ with "L" as decimal. Ex: 33m Ω , 1% = 33L0	D: $\pm 0.5\%$ F: $\pm 1\%$ J: $\pm 5\%$

¹ If you want to use at rated power use the derating curves based on the terminal part temperature on the next page.

applications and ratings

Part Designation	Power Rating	Rated Ambient Temp.	Rated Terminal Part Temp.	T.C.R. (X 10 ³ /K)	Resistance Range (Ω)			Maximum Working Voltage	Maximum Overload Voltage	Operating Temp. Range	
					D±0.5% E-24/E-96	F±1% E-24/E-96	J±5% E-24				
WK73R1E (0204)	0.33W ¹	70°C	125°C	±100	—	10 - 1M	10 - 1M	75V	100V	-55°C to +155°C	
WK73R1J (0306)	0.5W ¹	70°C	125°C	±100	—	10 - 1M	10 - 1M	150V	200V		
	0.66W ¹	—			—	10 - 9.76k	10 - 9.1k				
WK73R2A (0508)	0.75W ¹	70°C	125°C	±100	20.5k - 1M	20.5k - 1M	22k-1M	200V	400V		
	1.0W ¹	—	125°C	±100	10 - 20k	10 - 20k	10 - 20k				
WK73R2B (0612)	0.75W	70°C	125°C	±100	10 - 1M	10 - 1M	10 - 1M	200V	400V		
	1.5W ¹	—	125°C	±100	10 - 9.76k	10 - 9.76k	10 - 9.1k				
WK73R2H (1020)	1.0W	70°C	125°C	±100	—	10 - 430k	10 - 430k	200V	400V		
				±200	—	432k - 1M	470k - 1M				
	2W ¹	—	125°C	±100	—	10 - 430k	10 - 430k				
				±200	—	432k - 1M	470k - 1M				
WK73R3A (1225)	1.5W	70°C	125°C	±100	—	10 - 330k	10 - 330k	200V	400V		
				±200	—	332k - 1M	360k - 1M				
	3W ¹	—	125°C	±100	—	10 - 330k	10 - 330k				
				±200	—	332k - 1M	360k - 1M				


Rated voltage = $\sqrt{\text{Power rating} \times \text{resistance value or max. working voltage}}$, whichever is lower

¹ If you want to use at rated power use derating curves based on the terminal part temperature on the right side graph located below.


If any questions arise whether to use the "Rated Ambient Temperature" or the "Rated Terminal Part Temperature", please give priority to the "Rated Terminal Part Temperature." For more details refer to the "Introduction of the derating curves based on the terminal part temperature" in the beginning of the catalog.

environmental applications

Derating Curve




For resistors operated at an ambient temperature of 70°C or above, a power rating shall be derated in accordance with the above derating curve.






When the terminal part temperature of the resistor exceeds the rated terminal part temperature shown above, the power shall be derated according to the derating curve.


Please refer to "Introduction of the derating curves based on the terminal part temperature" in the beginning of the catalog before use.



Temperature Rise



WK73R 1E-1J

WK73R 2A-2B

WK73R 2H-3A


Regarding the temperature rise, the value of the temperature varies per conditions and board for use since the temperature is measured under our measuring conditions.

Simulated and Measurement Conditions


Temperature rise is simulated and measured under our conditions. So, the values will vary depending on the operating conditions and PCB used.

One-Pulse Limiting Electric Power

WK73R 1E-2A

WK73R 2B-3A


The maximum applicable voltage is equal to the max. overload voltage. Please ask us about the resistance characteristic of continuous applied pulse. The pulse endurance values are not assured values, so be sure to check the products on actual equipment when you use them.

Performance Characteristics

Parameter	Requirement $\Delta R \pm (% + 0.005\Omega)$		Test Method						
	Limit	Typical							
Resistance	Within specified tolerance	—	25°C						
T.C.R.	Within specified T.C.R.	—	+25°C/-55°C and +25°C/+125°C						
Overload (Short time)	±2%	±0.2%	Overload wattage for 5s						
			Type (Resistance Range/Ω)	1E	1J	2A	2B	2H	3A
			Overload Wattage	1.32W	3.125W	4W	3W	6W	4.688W
Resistance to Solder Heat	±1%	±0.2%	260°C ± 5°C, 10 seconds ± 1 second						
Bending Test	±1%	±0.1%	Holding point 90mm, Bending 1 time, Bending 5mm						
Rapid Change of Temperature	±2%	±1%	-55°C (30 minutes) / +125°C (30 minutes), 1000 cycles						
Moisture Resistance	±3%: 1E ±2%: All others	±1%: 1E ±0.2%: All others	40°C ± 2°C, 90%~95% RH, 1000 hours; 1.5 hr ON, 0.5 hr OFF cycle						
Endurance at 70°C	±3%: 1E ±2%: All others	±1%: 1E ±0.2%: All others	70°C ± 2°C or rated terminal part temperature ± 2°C, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle						
High Temperature Exposure	±1%	±0.2%	+155°C, 1000 hours						

Additional environmental applications can also be found at www.koaspeer.com

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

3/17/25

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KOA Speer:

[WK73R2HTTE1000F](#) [WK73R2HTTE20R0F](#) [WK73R2HTTE182J](#) [WK73R3ATTE220J](#) [WK73R3ATTE391J](#)
[WK73R3ATTE330J](#) [WK73R3ATTE301J](#) [WK73R2HTTE100J](#) [WK73R2HTTE241J](#) [WK73R2HTTE1001F](#)
[WK73R2HTTE1002F](#) [WK73R2HTTE101J](#) [WK73R2HTTE102J](#) [WK73R2HTTE103J](#) [WK73R2HTTE104J](#)
[WK73R2HTTE121J](#) [WK73R2HTTE122J](#) [WK73R2HTTE132J](#) [WK73R2HTTE151J](#) [WK73R2HTTE152J](#)
[WK73R2HTTE10R0F](#) [WK73R3ATTE471J](#) [WK73R3ATTE750J](#) [WK73R3ATTE102J](#) [WK73R3ATTE101J](#)
[WK73R3ATTE1001F](#) [WK73R2HTTE153J](#) [WK73R3ATTE1000F](#) [WK73R3ATTE100J](#) [WK73R2HTTE202J](#)
[WK73R3ATTE472J](#) [WK73R2HTTE222J](#) [WK73R3ATTE103J](#) [WK73R3ATTE911J](#) [WK73R2HTTE331J](#)
[WK73R2HTTE330J](#) [WK73R2HTTE272J](#) [WK73R2HTTE242J](#) [WK73R3ATTE10R0F](#) [WK73R3ATTE1003F](#)
[WK73R3ATTE1004F](#) [WK73R3ATTE104J](#) [WK73R3ATTE105J](#) [WK73R3ATTE1100F](#) [WK73R3ATTE1101F](#)
[WK73R3ATTE1102F](#) [WK73R3ATTE1103F](#) [WK73R3ATTE110J](#) [WK73R3ATTE111J](#) [WK73R3ATTE112J](#)
[WK73R3ATTE113J](#) [WK73R3ATTE114J](#) [WK73R3ATTE11R0F](#) [WK73R3ATTE1200F](#) [WK73R3ATTE1201F](#)
[WK73R3ATTE1202F](#) [WK73R3ATTE1203F](#) [WK73R3ATTE120J](#) [WK73R3ATTE121J](#) [WK73R3ATTE122J](#)
[WK73R3ATTE123J](#) [WK73R3ATTE124J](#) [WK73R3ATTE12R0F](#) [WK73R3ATTE1300F](#) [WK73R3ATTE1301F](#)
[WK73R3ATTE1303F](#) [WK73R3ATTE130J](#) [WK73R3ATTE131J](#) [WK73R3ATTE132J](#) [WK73R3ATTE133J](#)
[WK73R3ATTE134J](#) [WK73R3ATTE13R0F](#) [WK73R3ATTE1500F](#) [WK73R3ATTE1501F](#) [WK73R3ATTE1502F](#)
[WK73R3ATTE1503F](#) [WK73R3ATTE150J](#) [WK73R3ATTE151J](#) [WK73R3ATTE152J](#) [WK73R3ATTE153J](#)
[WK73R3ATTE154J](#) [WK73R3ATTE15R0F](#) [WK73R3ATTE1600F](#) [WK73R3ATTE1601F](#) [WK73R3ATTE1602F](#)
[WK73R3ATTE1603F](#) [WK73R3ATTE160J](#) [WK73R3ATTE161J](#) [WK73R3ATTE162J](#) [WK73R3ATTE163J](#)
[WK73R3ATTE164J](#) [WK73R3ATTE16R0F](#) [WK73R3ATTE1800F](#) [WK73R3ATTE1801F](#) [WK73R3ATTE1802F](#)
[WK73R3ATTE1803F](#) [WK73R3ATTE180J](#) [WK73R3ATTE181J](#) [WK73R3ATTE182J](#) [WK73R3ATTE183J](#)