


2.5G Base-T, SMD PoE LAN Isolation Transformer



ALANC002G

Request Samples



Check Inventory



4.6 x 3.4 x 3.5 mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- Uniform transformer windings
- Power over Ethernet (PoE, PoE+) capable.
- Meets IEEE 802.3ab and 802.3bz standards
- Compatible with 2.5G BASE-T
- Symmetric Orientation
- Operating temperature range of -40°C to +85°C
- RoHS Compliant
- 1CT:1CT Transformer

Applications

- Fast and gigabit Ethernet
- Servers, switches and routers
- IP cameras, surveillance, and phone
- Access points
- Industrial computers and robotics
- Networking and communications
- Broadcast video
- Set top box

Electrical Specifications @25°C

Part Number*	Inductance (uH Min)	Interwinding Capacitance (pF Max)	DC Resistance (Ω Max)		Rated Current (mA)	Insertion Loss (dB Max)	Return Loss (dB Min)	Hi Pot (VAC)	Turn Ratio
Test Condition	@100kHz, 0.1V	@ 100KHz, 0.1V	Pins 1-2	Pins 4-5	Pins 1-2-6 Pins 5-4-3	1 ~150 MHz	1 ~150 MHz	1 sec.	1-2 : 4-5
ALANC002G1-EADT	150	30	1.5	1.5	300	-1.5	-10	1500	1CT:1CT
ALANC002G2- EADT	150	30	1.2	1.2	600	-1.5	-10	1500	1CT:1CT

*The “T” at the end of the part numbers refers to “Tape & Reel” packaging. For other options, please refer to the Part Identification section.

ALANC002G series is RoHS/ RoHS II Compliant and Pb free.

Moisture Sensitivity Level (MSL) – Level 1.


Applicable Standards: IEEE 802.3ab and 802.3bz.

Operating Temperature: -40°C ~ +85°C.

Storage Condition: -40°C ~ +85°C (on board), 40%-60% RH.

ALANC002G1-EADT


Insertion Loss (dB)



Return Loss (dB)



DCMR (dB)




5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION A : 11/12/2024

ABRACON IS
ISO9001-2015
CERTIFIED

2.5G Base-T, SMD PoE LAN Isolation Transformer



ALANC002G

Request Samples



Check Inventory



4.6 x 3.4 x 3.5 mm
RoHS/RoHS II Compliant
MSL Level = 1

ALANC002G2-EADT


Insertion Loss (dB)

Tr1 Sdd21 Log Mag 10.00dB/ Ref -20.00dB [F4]




Return Loss (dB)

Tr2 Sdd11 Log Mag 10.00dB/ Ref -20.00dB [F4]



DCMR (dB)

Tr3 Scd21 Log Mag 10.00dB/ Ref -40.50dB [F4]



Part Identification

ALANC002G -

Power Over Ethernet

PoE: 1
PoE+: 2

Package

E: 6-pin

Schematic

A: Standard

Operating Temp.

D: -40°C ~ +85°C

Packaging

T: Tape & reel
B: Bulk




5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION A : 11/12/2024

ABRACON IS
ISO9001-2015
CERTIFIED

4.6 x 3.4 x 3.5 mm
RoHS/RoHS II Compliant
MSL Level = 1

2.5G Base-T, SMD PoE LAN Isolation Transformer



ALANC002G

Request Samples




Check Inventory




4.6 x 3.4 x 3.5 mm
RoHS/RoHS II Compliant
MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ 150°C ~ 200°C	60 ~ 180 sec.
2	Reflow	T_L 217°C	60 ~ 150 sec.
3	Peak heat	T_P 260°C	10 sec. MAX

2.5G Base-T, SMD PoE LAN Isolation Transformer



ALANC002G

Request Samples




Check Inventory



4.6 x 3.4 x 3.5 mm
RoHS/RoHS II Compliant
MSL Level = 1


Packaging

Tape and Reel: 2000 pcs/reel



A0	B0	W	E	F	P0	P1	P2	D0	T	K0
3.60	4.90	12.00	1.75	5.50 ±0.05	4.00 ±0.05	8.00	2.00	1.50 ±0.05	0.40 ±0.05	3.0

Tolerance: ±0.1 (unless otherwise noted)



Dimensions unit: mm

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf (COTS, which are designed, intended and validated for use in commercial, industrial and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION A : 11/12/2024

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[ALANC002G1-EADT](#) [ALANC002G2- EADT](#)