


Flat Wire / Hot Pressed Molded Power Inductor



AMELH1060S

[Request Samples](#)[Check Inventory](#)

11.90 x 11.00x 5.7 mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- Excellent current capacity – up to 48A
- Exceptionally low DCR – down to only 1.7mΩ
- Soft saturation
- Compact size for high-density designs
- Shielded constructions for low EMI

Applications

- Body electronics
- Lighting
- Motor control
- Solar inverters and solar power
- DC/DC converters in distributed power systems
- Battery powered device

Electrical Specifications

| Part Number | Inductance 0.1MHz/1.0V | Tolerance | DC Resistance | | Saturation Current | | Temperature Rise Current | | Self-Resonant Frequency |
|------------------|---------------------------|-----------|---------------|------|--------------------|------|--------------------------|------|-------------------------|
| | | | Typ | Max | Typ | Max | Typ | Max | |
| Units | µH | % | mΩ | | A | | A | | MHz |
| Symbol | L | M | DCR | | Isat | | Irms | | SRF |
| AMELH1060S-1R0MT | 1.0 | 20 | 1.7 | 2.0 | 48.0 | 44.0 | 40.0 | 35.0 | 25 |
| AMELH1060S-1R2MT | 1.2 | 20 | 1.9 | 2.3 | 42.0 | 37.0 | 35.0 | 30.0 | 32 |
| AMELH1060S-1R5MT | 1.5 | 20 | 2.2 | 2.6 | 40.0 | 35.0 | 32.0 | 28.0 | 30 |
| AMELH1060S-1R8MT | 1.8 | 20 | 2.5 | 2.9 | 35.0 | 31.0 | 29.0 | 25.0 | 26 |
| AMELH1060S-2R2MT | 2.2 | 20 | 3.4 | 3.9 | 33.0 | 29.0 | 27.0 | 23.0 | 25 |
| AMELH1060S-2R7MT | 2.7 | 20 | 3.7 | 4.3 | 30.0 | 27.0 | 25.0 | 22.0 | 22 |
| AMELH1060S-3R3MT | 3.3 | 20 | 4.3 | 5.0 | 27.0 | 24.0 | 23.0 | 20.0 | 18 |
| AMELH1060S-4R7MT | 4.7 | 20 | 6.5 | 7.5 | 23.0 | 20.0 | 19.0 | 16.5 | 16 |
| AMELH1060S-5R6MT | 5.6 | 20 | 7.3 | 8.4 | 20.0 | 18.0 | 17.5 | 15.5 | 13 |
| AMELH1060S-6R8MT | 6.8 | 20 | 8.8 | 10.1 | 19.0 | 17.0 | 15.5 | 13.5 | 13 |
| AMELH1060S-8R2MT | 8.2 | 20 | 10.3 | 11.9 | 17.5 | 15.5 | 14.5 | 12.5 | 12 |
| AMELH1060S-100MT | 10.0 | 20 | 12.8 | 14.8 | 15.5 | 13.5 | 13.0 | 11.0 | 10 |

Test Conditions:

Isat: DC current at which the inductance drops 30% from its nominal value.

Irms: DC current that causes the temperature rise (ΔT , approximate 40 °C) from 25°C ambient.


Operating Voltage: 40V

Operating Temperature: -40°C ~ +125°C. (including self-temperature rise)

Storage Condition: -40°C ~ +125°C (on board), -10°C ~ +40°C (with packaging) and R.H. 85% max.

AMELH1060S Series is **RoHS Compliant and Pb free**.

Flat Wire / Hot Pressed Molded Power Inductor



AMELH1060S

Request Samples



Check Inventory



11.90 x 11.00x 5.7 mm
RoHS/RoHS II Compliant
MSL Level = 1

Part Identification

AMELH1060S -



Inductance Code

See Electrical Specification
table. E.g 1R0 for 1uH


Tolerance

M = $\pm 20\%$

Packaging

T: Tape and Reel (See Packaging)
Blank: Bulk


Marking



Inductance Code
e.g. "2R2" for 2.2uH





Marking Method = Ink Marking

Flat Wire / Hot Pressed Molded Power Inductor

**AMELH1060S**[Request Samples](#)[Check Inventory](#)

11.90 x 11.00x 5.7 mm
RoHS/RoHS II Compliant
MSL Level = 1

Mechanical Specifications


**TOP VIEW****BOTTOM VIEW****FRONT VIEW****RECOMMENDED LAND PATTERN****NOTES:**

The above PCB layout reference only.

Recommending solder paste thickness at .005[0.15] and above.
Inductance code markings, black.

DIMENSIONS: INCHES[mm]

Flat Wire / Hot Pressed Molded Power Inductor



AMELH1060S

Request Samples




Check Inventory



11.90 x 11.00x 5.7 mm
RoHS/RoHS II Compliant
MSL Level = 1

Reflow Profile



| Zone | Description | Temperature | Times |
|------|-------------|-------------------------------------------|---------------|
| 1 | Preheat | $T_{SMIN} \sim T_{SMAX}$ 150°C ~ 200°C | 60 ~ 120 sec. |
| 2 | Reflow | T_L 217°C | 60 ~ 150 sec. |
| 3 | Peak heat | T_p 250°C ± 5°C | 10 sec. MAX |

Ref. Solder paste: Sn/3.0Ag/0.5Cu (Pb-free assembly)


Ramp up rate: 3°C/s Max.

Ramp down rate: 6°C/s Max.

Time from 25C to T_p : 8mins Max


Refer to standard IPC/JEDEC J-STD-020E for more information

Flat Wire / Hot Pressed Molded Power Inductor

**AMELH1060S**[Request Samples](#)[Check Inventory](#)

11.90 x 11.00x 5.7 mm
RoHS/RoHS II Compliant
MSL Level = 1

Packaging

T: Tape & Reel, 500 pcs/reel

| A | B | D | E | F | G | H | I | J | K | L |
|-------|--------|----------|----------|----------|---------|----------|----------|-----------|-----------|-----------|
| 330.0 | 24.4±2 | 13.0±0.5 | 24.0±0.3 | 16.0±0.1 | 4.0±0.1 | 1.75±0.1 | 0.35±0.1 | 11.5 Ref. | 12.4 Ref. | 6.30 Ref. |

Dimensions: mm

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf (COTS, which are designed, intended and validated for use in commercial, industrial and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



12117 Bee Caves Rd, Bldg-3, Suite 200

Bee Cave, TX 78738

Phone: 512-371-6159 Fax: 512-351-8858

For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
6/18/2025

ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AMELH1060S-4R7MT](#) [AMELH1060S-100MT](#) [AMELH1060S-1R5MT](#) [AMELH1060S-6R8MT](#) [AMELH1060S-2R2MT](#)

[AMELH1060S-3R3MT](#) [AMELH1060S-8R2MT](#) [AMELH1060S-1R8MT](#) [AMELH1060S-2R7MT](#) [AMELH1060S-1R0MT](#)

[AMELH1060S-1R2MT](#) [AMELH1060S-5R6MT](#)