


MULTILAYER FERRITE CHIP INDUCTOR

AIML-0402

RoHS
Compliant



1.0 x 0.5 x 0.5mm

FEATURES:

- Monolithic structure for higher reliability, compact size, & lightweight
- Magnetically shielded design to eliminate cross coupling
- Excellent solderability and heat resistance for reflow soldering
- Perfect shape for PCB mounting with no polarity

APPLICATIONS:

- Resonance circuit, traps and filter circuits
- RF choke for cordless phones and radio equipment
- Communications, video and audio equipment, computer and remote Control.

STANDARD SPECIFICATIONS:

Part No.	L(μ H)	Tolerance	Q (min)	Test Freq.	SRF(MHz)	DCR(Ω)	Ir(mA)
		(%)		(MHz)	(min)	(max)	(max)
AIML-0402-1R0	1.0	K, M	20	10	40	0.90	15
AIML-0402-1R2	1.2	K, M	20	10	35	1.20	15
AIML-0402-1R5	1.5	K, M	20	10	30	1.20	15
AIML-0402-1R8	1.8	K, M	20	10	30	1.45	15
AIML-0402-2R2	2.2	K, M	20	10	28	1.70	10
AIML-0402-2R7	2.7	K, M	20	10	28	2.40	10

Test Conditions and equipments

L, Q: HP4291 Impedance Analyzer

DCR: HP4263A LCR meter

SRF: HP4291 Impedance analyzer

Ir: HP4291 Impedance Analyzer, DC power HP6632 and Adapter HP16200. $\Delta L/L$ (initial) $\geq -5\%$

Unless otherwise specified

Temperature : Ordinary Temperature (5 to 35°C)


Humidity : Ordinary Humidity (25 to 85% RH)

PARAMETERS

ABRACON P/N:	AIML-0402-xxx
Operating temperature :	-55°C to + 125°C
Storage temperature:	-55°C to + 125°C

OPTIONS AND PART IDENTIFICATION:


(Left blank if standard)



MULTILAYER FERRITE CHIP INDUCTOR


AIML-0402

RoHS
Compliant



1.0 x 0.5 x 0.5mm



OUTLINE DRAWING:



Series	L	W	T	a1,a2
AIML-0402	1.00±0.15	0.50±0.15	0.50±0.15	0.25±0.10
	[0.039±0.006]	[0.02±0.006]	[0.02±0.006]	[0.01±0.004]

Dimension: mm [inch]

MATERIALS:




#	Part Nme	Material Name
1	Ferrite Body	Ferrite Powder
2	Inner Coils	Silver Paste
3	Pull-out Electrode (Ag)	Silver Paste
4-1	Terminal Electrode: Inside Ag	Termination Silver Composition
4-2	Electro-Plating: Ni/Sn plating	Plating Chemicals

MULTILAYER FERRITE CHIP INDUCTOR


AIML-0402

RoHS
Compliant



1.0 x 0.5 x 0.5mm

REFLOW PROFILE:




Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ 150°C ~ 200°C	60 ~ 180 sec.
2	Reflow	T_L 217°C	60 ~ 150 sec.
3	Peak heat	T_P 260°C±5°C	20 ~ 40 sec.

MULTILAYER FERRITE CHIP INDUCTOR

AIML-0402

RoHS
Compliant




1.0 x 0.5 x 0.5mm

PACKAGING:

T: 10,000pcs / reel


Sprocket Hole $\Phi 1.5 (+0.1, 0)$

Chip Cavity



Codes	A	B	P	T(max)
AIML-0402	0.65 ± 0.10	1.15 ± 0.10	2.0 ± 0.05	0.80

Dimensions: mm



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[AIML-0402-1R0K-T](#) [AIML-0402-1R2K-T](#) [AIML-0402-1R5K-T](#) [AIML-0402-1R8K-T](#) [AIML-0402-2R2K-T](#) [AIML-0402-2R7K-T](#)