

# Ultra Field Stop IGBT, 1200 V, 60 A

## FGY60T120SQDN

### General Description

This Insulated Gate Bipolar Transistor (IGBT) features a robust and cost effective Ultra Field Stop Trench construction, and provides superior performance in demanding switching applications, offering both low on-state voltage and minimal switching loss. The IGBT is well suited for UPS and solar applications. Incorporated into the device is a soft and fast co-packaged free wheeling diode with a low forward voltage.

### Features

- Extremely Efficient Trench with Field Stop Technology
- Maximum Junction Temperature  $T_J = 175^\circ\text{C}$
- Low Saturation Voltage:  $V_{CE(\text{sat})} = 1.7 \text{ V (Typ.)} @ I_C = 60 \text{ A}$
- 100% of the Parts Tested for  $I_{LM}$  (Note 1)
- Soft Fast Reverse Recovery Diode
- Optimized for High Speed Switching
- RoHS Compliant

### Applications

- Solar Inverter, UPS

### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

| Symbol       | Description   | Value       | Unit             |
|--------------|---|-------------|------------------|
| $V_{CES}$    | Collector to Emitter Voltage  | 1200        | V                |
| $V_{GES}$    | Gate to Emitter Voltage   | $\pm 25$    | V                |
|              | Transient Gate to Emitter Voltage                                       | $\pm 30$    | V                |
| $I_C$        | Collector Current @ ( $T_C = 25^\circ\text{C}$ )                        | 120         | A                |
|              | Collector Current @ ( $T_C = 100^\circ\text{C}$ )                       | 60          | A                |
| $I_{LM}$ (1) | Pulsed Collector Current @ ( $T_C = 25^\circ\text{C}$ )                 | 240         | A                |
| $I_{CM}$ (2) | Pulsed Collector Current  | 240         | A                |
| $I_F$        | Diode Forward Current @ ( $T_C = 25^\circ\text{C}$ )                    | 120         | A                |
|              | Diode Forward Current @ ( $T_C = 100^\circ\text{C}$ )                   | 60          | A                |
| $I_{FM}$     | Pulsed Diode Max. Forward Current                                       | 240         | A                |
| $P_D$        | Maximum Power Dissipation @ ( $T_C = 25^\circ\text{C}$ )                | 517         | W                |
|              | @ ( $T_C = 100^\circ\text{C}$ )   | 259         | W                |
| $T_J$        | Operating Junction Temperature  | -55 to +175 | $^\circ\text{C}$ |
| $T_{stg}$    | Storage Temperature Range   | -55 to +175 | $^\circ\text{C}$ |
| $T_L$        | Maximum Lead Temp. For soldering Purposes, 1/8" from case for 5 seconds | 300         | $^\circ\text{C}$ |



Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1.  $V_{CC} = 800 \text{ V}$ ,  $V_{GE} = 15 \text{ V}$ ,  $I_C = 240 \text{ A}$ ,  $R_G = 68 \Omega$ , Inductive Load
2. Repetitive rating: Pulse width limited by max. Junction temperature




ON Semiconductor®

[www.onsemi.com](http://www.onsemi.com)



Power TO247  
(TO-247H03)

### MARKING DIAGRAM



&Y = ON Semiconductor Logo  
&3 = Data Code (Year & Week)  
&K = Lot  
FGY60T120SQDN = Specific Device Code

### ORDERING INFORMATION

See detailed ordering and shipping information on page 3 of this data sheet.

# FGY60T120SQDN

## THERMAL CHARACTERISTICS

| Symbol                  | Parameter                                     | FGY60T120SQDN | Unit |
|-------------------------|---|---------------|------|
| $R_{\theta JC}$ (IGBT)  | Thermal Resistance, Junction to Case, Max.    | 0.29          | °C/W |
| $R_{\theta JC}$ (Diode) | Thermal Resistance, Junction to Case, Max.    | 0.42          |      |
| $R_{\theta JA}$         | Thermal Resistance, Junction to Ambient, Max. | 40            | °C/W |

## ELECTRICAL CHARACTERISTICS ( $T_C = 25^\circ\text{C}$ unless otherwise noted)

| Symbol | Parameter | Test Condition | Min. | Typ. | Max. | Unit |
|--------|-----------|----------------|------|------|------|------|
|--------|-----------|----------------|------|------|------|------|

### OFF CHARACTERISTICS

|            |  |   |      |   |           |               |
|------------|--|---|------|---|-----------|---------------|
| $BV_{CES}$ | Collector to Emitter Breakdown Voltage | $V_{GE} = 0\text{V}$ , $I_C = 500\text{ }\mu\text{A}$ | 1200 | – | –         | V             |
| $I_{CES}$  | Collector Cut-Off Current              | $V_{CE} = V_{CES}$ , $V_{GE} = 0\text{ V}$            | –    | – | 400       | $\mu\text{A}$ |
| $I_{GES}$  | G-E Leakage Current                    | $V_{GE} = V_{GES}$ , $V_{CE} = 0\text{ V}$            | –    | – | $\pm 200$ | nA            |

### ON CHARACTERISTICS

|                      |   |  |     |     |      |   |
|----------------------|---|--|-----|-----|------|---|
| $V_{GE(\text{th})}$  | G-E Threshold Voltage                   | $I_C = 400\text{ }\mu\text{A}$ , $V_{CE} = V_{GE}$                       | 4.5 | 5.5 | 6.5  | V |
| $V_{CE(\text{sat})}$ | Collector to Emitter Saturation Voltage | $I_C = 60\text{ A}$ , $V_{GE} = 15\text{ V}$                             | –   | 1.7 | 1.95 | V |
|                      |   | $I_C = 60\text{ A}$ , $V_{GE} = 15\text{ V}$ , $T_C = 175^\circ\text{C}$ | –   | 2.3 | –    | V |

### DYNAMIC CHARACTERISTICS

|           |                              |  |   |      |   |    |
|-----------|------------------------------|--|---|------|---|----|
| $C_{ies}$ | Input Capacitance            | $V_{CE} = 20\text{ V}$ , $V_{GE} = 0\text{ V}$ ,<br>$f = 1\text{ MHz}$ | – | 7147 | – | pF |
| $C_{oes}$ | Output Capacitance           |  | – | 203  | – | pF |
| $C_{res}$ | Reverse Transfer Capacitance |  | – | 114  | – | pF |

### SWITCHING CHARACTERISTICS

|              |                          |   |   |       |   |    |
|--------------|--------------------------|---|---|-------|---|----|
| $t_{d(on)}$  | Turn-On Delay Time       | $V_{CC} = 600\text{ V}$ , $I_C = 60\text{ A}$ , $R_G = 10\text{ }\Omega$ ,<br>$V_{GE} = 15\text{ V}$ ,<br>Inductive Load, $T_C = 25^\circ\text{C}$  | – | 52    | – | ns |
| $t_r$        | Rise Time                |   | – | 84    | – | ns |
| $t_{d(off)}$ | Turn-Off Delay Time      |   | – | 296   | – | ns |
| $t_f$        | Fall Time                |   | – | 56    | – | ns |
| $E_{on}$     | Turn-On Switching Loss   |   | – | 5.15  | – | mJ |
| $E_{off}$    | Turn-Off Switching Loss  |   | – | 1.82  | – | mJ |
| $E_{ts}$     | Total Switching Loss     |   | – | 6.97  | – | mJ |
| $t_{d(on)}$  | Turn-On Delay Time       | $V_{CC} = 600\text{ V}$ , $I_C = 60\text{ A}$ , $R_G = 10\text{ }\Omega$ ,<br>$V_{GE} = 15\text{ V}$ ,<br>Inductive Load, $T_C = 175^\circ\text{C}$ | – | 40    | – | ns |
| $t_r$        | Rise Time                |   | – | 72    | – | ns |
| $t_{d(off)}$ | Turn-Off Delay Time      |   | – | 324   | – | ns |
| $t_f$        | Fall Time                |   | – | 144   | – | ns |
| $E_{on}$     | Turn-On Switching Loss   |   | – | 7.18  | – | mJ |
| $E_{off}$    | Turn-Off Switching Loss  |   | – | 3.1   | – | mJ |
| $E_{ts}$     | Total Switching Loss     |   | – | 10.28 | – | mJ |
| $Q_g$        | Total Gate Charge        | $V_{CE} = 600\text{ V}$ , $I_C = 60\text{ A}$ , $V_{GE} = 15\text{ V}$  | – | 311   | – | nC |
| $Q_{ge}$     | Gate to Emitter Charge   |   | – | 57    | – | nC |
| $Q_{gc}$     | Gate to Collector Charge |   | – | 153   | – | nC |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# FGY60T120SQDN

## ELECTRICAL CHARACTERISTICS OF THE DIODE ( $T_C = 25^\circ\text{C}$ unless otherwise noted)

| Symbol    | Parameter                      | Test Condition       |                           | Min. | Typ. | Max. | Unit |
|-----------|--------------------------------|----------------------|---------------------------|------|------|------|------|
| $V_{FM}$  | Diode Forward Voltage          | $I_F = 60 \text{ A}$ | $T_C = 25^\circ\text{C}$  | –    | 3.4  | 4    | V    |
|           |                                |                      | $T_C = 175^\circ\text{C}$ | –    | 3.2  | –    |      |
| $t_{rr}$  | Diode Reverse Recovery Time    | $I_F = 60 \text{ A}$ | $T_C = 25^\circ\text{C}$  | –    | 91   | –    | ns   |
|           |                                |                      | $T_C = 175^\circ\text{C}$ | –    | 309  | –    |      |
| $Q_{rr}$  | Diode Reverse Recovery Charge  | $I_F = 60 \text{ A}$ | $T_C = 25^\circ\text{C}$  | –    | 860  | –    | nC   |
|           |                                |                      | $T_C = 175^\circ\text{C}$ | –    | 4902 | –    |      |
| $I_{rrm}$ | Diode Reverse Recovery Current | $I_F = 60 \text{ A}$ | $T_C = 25^\circ\text{C}$  | –    | 19   | –    | A    |
|           |                                |                      | $T_C = 175^\circ\text{C}$ | –    | 32   | –    |      |

## PACKAGE MARKING AND ORDERING INFORMATION

| Part Number   | Top Marking   | Package                 | Quantity |
|---------------|---------------|-------------------------|----------|
| FGY60T120SQDN | FGY60T120SQDN | TO-247-3LD<br>(Pb-Free) | 30/Tube  |

## TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. Typical Output Characteristics




Figure 2. Typical Output Characteristics




Figure 3. Typical Saturation Voltage Characteristics




Figure 4. Saturation Voltage vs. Case Temperature at Variant Current Level




Figure 5. Saturation Voltage vs.  $V_{GE}$




Figure 6. Saturation Voltage vs.  $V_{GE}$

## TYPICAL PERFORMANCE CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Gate charge Characteristics




Figure 9. Turn-on Characteristics vs. Gate Resistance




Figure 10. Turn-off Characteristics vs. Gate Resistance




Figure 11. Turn-on Characteristics vs. Collector Current




Figure 12. Turn-off Characteristics vs. Collector Current

## TYPICAL PERFORMANCE CHARACTERISTICS




Figure 13. Switching Loss vs. Gate Resistance




Figure 14. Switching Loss vs. Collector Current




Figure 15. Load Current vs. Frequency




Figure 16. SOA Characteristics




Figure 17. Forward Characteristics




Figure 18. Reverse Recovery Time vs.  $di_F/dt$

## TYPICAL PERFORMANCE CHARACTERISTICS




Figure 19. Reverse Recovery Charge vs.  $di_F/dt$ Figure 20. Reverse Recovery Current vs.  $di_F/dt$ 

Figure 21. Transient Thermal Impedance if IGBT





Figure 22. Transient Thermal Impedance if Diode




TO-247-3LD  
CASE 340CD  
ISSUE A

DATE 18 SEP 2018

NOTES:

- A. THIS PACKAGE DOES NOT CONFORM TO ANY STANDARDS.
- B. ALL DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.
- D. DIMENSION AND TOLERANCE AS PER ASME Y14.5-2009.



GENERIC  
MARKING DIAGRAM\*



XXXX = Specific Device Code

A = Assembly Location

Y = Year

WW = Work Week

G = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

| DIM | MILLIMETERS |       |       |
|-----|-------------|-------|-------|
|     | MIN         | NOM   | MAX   |
| A   | 4.58        | 4.70  | 4.82  |
| A1  | 2.20        | 2.40  | 2.60  |
| A2  | 1.80        | 2.00  | 2.20  |
| D   | 20.32       | 20.57 | 20.82 |
| E   | 15.37       | 15.62 | 15.87 |
| E2  | 4.12        | 4.32  | 4.52  |
| e   | ~           | 5.45  | ~     |
| L   | 19.90       | 20.00 | 20.10 |
| L1  | 3.69        | 3.81  | 3.93  |
| Q   | 5.34        | 5.46  | 5.58  |
| b   | 1.10        | 1.20  | 1.30  |
| b2  | 2.10        | 2.24  | 2.39  |
| b4  | 2.87        | 3.04  | 3.20  |
| c   | 0.51        | 0.61  | 0.71  |
| D1  | 16.63       | 16.83 | 17.03 |
| D2  | 0.51        | 0.93  | 1.35  |
| E1  | 13.40       | 13.60 | 13.80 |

|                  |             |   |
|------------------|-------------|---|
| DOCUMENT NUMBER: | 98AON13857G | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | TO-247-3LD  | PAGE 1 OF 1   |

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

**onsemi, ONSEMI, and other names, marks, and brands** are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Email Requests to: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**onsemi** Website: [www.onsemi.com](http://www.onsemi.com)

### TECHNICAL SUPPORT

#### North American Technical Support:

Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

#### Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi](#):

[FGY60T120SQDN](#)