

NetKey® Flush Mount Modular Patch Panels

specifications

Flush mount modular patch panels shall consist of a metal panels with molded rear snap-in faceplates. Patch Panels shall accept all NetKey Modules for UTP, fiber or A/V applications and shall mount to standard 19" racks. Patch panels shall be available in 24-port and 48-port standard density. Flush mount patch panels shall be easy to identify with pre-numbered ports. Angled patch panels shall be designed at an optimum angle to help route the cable.



technical information

Mounting options:	Mounts to standard 19" rack
Material:	Stamping is CRS and faceplate is ABS
Packaging:	Packaged with appropriate pre-installed snap in faceplates and a set of mounting screws (#12-24)

key features and benefits

Modular:	Accepts all NetKey Modules to mix and match media types in the same panel
Angled design:	Minimize the need for horizontal cable managers by enabling patch cords to be routed directly into vertical cable managers which leads to increase closet density
Port and panel identification:	Pre-numbered ports with write on areas
Optional strain relief bars:	To help support and manage cables
Optional filler panels:	Flat and angled design fill unused rack openings to provide a clean and consistent look when used with any version of Panduit patch panels
Optional extender bracket:	Allows 19" patch panels to be mounted on a 23" rack

applications

NetKey Flush Mount Modular Patch Panels are ideal for multi-media applications. They accept all NetKey Modules. Flat and angled designs in various port densities are available, including pre-numbered port identification. Angled patch panels are available for applications in which rack space is limited. The design allows cable to flow to each side of the rack, minimizing the need for horizontal cable managers and increasing the density of the rack space. Flush mount patch panels can mount on a standard 19" rack or a 23" rack when using the extender brackets PEB1 or PEB2.

Flat Style

24-port, 1 RU:	NKPP24FMY
48-port, 2 RU:	NKPP48FMY
48-port, 2 RU: (vertical numbering)	NKPP48FMVNSBL

Angled Style

24-port, 1 RU:	NKPPA24FMY
48-port, 2 RU:	NKPPA48FMY

Patch Panel Accessories

Transitional cover:	CPATCBL
Angled filler panel 1 RU:	CPAF1BLY
Angled filler panel 2 RU:	CPAF2BLY
Flat filler panel 1 RU:	DPFP1
Flat filler panel 2 RU:	DPFP2


Extender Brackets

1 RU:	PEB1
2 RU:	PEB2


NetKey® Flush Mount Modular Patch Panels

modular patch panel dimensions


NKPP24FMY




NKPP48FMY



NKPPA24FMY



NKPPA48FMY



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

© 2023 Panduit Corp.
ALL RIGHTS RESERVED.
CODS4-WW-ENG
4/2023

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit](#):

[NKPP48FMVNSBL](#)