



- Interchangeable Plugs for Worldwide Use
- Class II Configuration
- Efficiency Level VI
- <210mW No Load Power Consumption
- Short Circuit Protection
- Overload Protection
- No Load Operation

Electrical Specifications

Input

Input Voltage	90-264VAC
Input Frequency	47-63 Hz
Input Current	1.5A Max.
Inrush Current	<40A peak @ 264VAC, cold start at 25°C
No Load Power Consumption	< 210mW, meets DOE level VI requirements

Output

Output Power	65W max, see table for details
Output Voltage	see table
Turn On Time	<3S @100-240VAC input & full output load
Rise Time	20mS max. @ full load
Fall Time	20mS max. @ full load
Hold-up time	10mS min @ full load 115VAC input 20mS min @ full load 230VAC input
Line Regulation	± 1% of rated output voltage at fixed load
Load Regulation	± 5% of rated voltage from 0 to full load
Transient Response	Maximum voltage excursion of 5% for 25% load change with 0.25A/uS slew rate. Recovery time: 200uS
Efficiency	Meets DOE level VI requirements

Protection

Short Circuit Protection	Hiccup mode. Auto recovery.
Overcurrent Protection	150-200% of rated current. Auto-restart when fault removed.
Ingress Protection	IP22 Compliant

Environmental & Operating

Operating Temperature	0°C to +60°C (Derate output power linearly from 100% at 40°C to 50% at 60°C)
Storage Temperature	-20°C to +80°C
Humidity	10% - 90% non-condensing
Operating Altitude	<2000m
MTBF	>100,000 hours per MIL-HDBK-217F at full load and 25°C ambient

Compliance

Safety Approvals

USA	UL60950-1
Canada	cUL60950-1
Europe	CB Report, CE Report RCM (Australia)

EMC:

Harmonic Currents	FCC Class B Radiated & Conducted
Voltage Flicker	CISPR22 Class B Radiated & Conducted
Electrostatic Discharge	EN55022 Class B Radiated & Conducted
Radiated Immunity	IEC 61000-3-2
EFT/Burst	IEC 61000-3-3
Surge Immunity	IEC 61000-4-2: ±8 KV air, ±4 KV contact
Conducted Immunity	IEC 61000-4-3: 3V/m
Magnetic Field	IEC 61000-4-4: ±1 KV
Dips / Interruptions	IEC 61000-4-5: ±1 KV differential mode
	IEC 61000-4-6: 3Vrms
	IEC 61000-4-8: 1A/m
	IEC 61000-4-11: 30% reduction for 500 ms, and >95% reduction for 10 ms


General

Dimensions	4.62"(117.3mm) x 1.98"(50.3mm) x 1.40"(35.5mm)
AC Input Output Plug	Interchangeable Plugs for Worldwide Use Barrel Type: 5.5mm x 2.1mm x 10mm Center positive (others available)
Weight	0.60 pounds

Model No.	Output voltage	Current	Total Power	Output Regulation	Ripple & Noise (Vp-p) ¹	Efficiency Level
PSAW65I-12-B1	12VDC	5A	60W	±5%	200mV	VI
PSAW65I-13-B1	15VDC	4.33A	65W	±5%	200mV	VI
PSAW65I-13-1-B1	18VDC	3.61A	65W	±5%	200mV	VI
PSAW65I-13-2-B1	19VDC	3.42A	65W	±5%	200mV	VI
PSAW65I-14-B1	24VDC	2.70A	65W	±5%	240mV	VI
PSAW65I-17-B1	36VDC	1.80A	65W	±5%	360mV	VI
PSAW65I-18-B1	48VDC	1.35A	65W	±5%	480mV	VI

1. Ripple and noise is measured at output within 20MHz bandwidth, at rated line voltage and full load, with a 10 μ F tantalum capacitor in parallel with a 0.1 μ F ceramic capacitor across the output.

Mechanical Outline



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TT Electronics:](#)

[PSAWXXI UK PLUG](#) [PSAW65I-12-B1](#) [PSAW65I-18-B1](#) [PSAW65I-14-B1](#) [PSAWXXI AUS PLUG](#) [PSAWXXI EU PLUG](#) [PSAWXXI CHINA PLUG](#)