




STYLE U




STYLE Z



STYLE F




STYLE D





DRAWN	K.SHEPPARD	DATE 29/11/2011		 3RD ANGLE PROJECTION NOT TO SCALE	 POLAMCO LTD WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PAGE 1	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES
SALES APPR	A.POLSON	11/11/2011					
DESIGN APPR							
QUAL APPR							
ISSUE 6	REV 3	DCR		THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	ASSY USED ON: MIL-DTL-83513		MATERIAL ALUMINIUM ALLOY
					TITLE: BANDING BACKSHELL		
					PART NUMBER: RBTMM SERIES		
WEIGHT		GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°		NCAGE CODE U5792			
DRAWING NO: P22259							

HARDWARE OPTION EK



HARDWARE OPTION F



EXAMPLE PART NUMBER: RBTMM-U-21-06-1-C-SL	
RBTMM =	POLAMCO SERIES
U =	ANGLE: U - TOP ENTRY Z - SIDE ENTRY F - 45° ENTRY D - DUAL ENTRY
21 =	SHELL SIZE (TABLE 1)
06 =	ENTRY SIZE (TABLE 2)
1 =	MATERIAL (ALUMINIUM ALLOY)
C =	PLATING (TABLE 3)
SL =	SCREW REF. SL - SLOTTED HEAD JACKSCREW SK - SOCKET HEAD JACKSCREW EK - EXTENDED JACKSCREW F - FEMALE JACKPOST FSK - FLOATING JACKSCREW

TABLE 1 SHELL SIZE	A	B	C	D	J MAX	K	M MAX	N	MAX ENTRY STYLES U, F & D	MAX ENTRY STYLE Z
09	19,68	14,35	9,0	9,0	16,2	11,05	25,4	16,5	08	10
15	23,50	18,16	9,0	12,0	17,1	11,20	26,2	17,8	08	12
21	27,30	21,97	9,0	15,0	18,0	11,63	26,7	18,7	08	13
25	29,84	24,51	9,0	16,5	19,0	12,27	27,7	20,3	08	14
31	33,66	28,32	9,0	18,0	19,2	12,09	28,7	21,8	09	15
37	37,46	32,13	9,0	19,0	19,7	12,14	31,2	23,5	09	16
51	36,20	30,86	10,0	19,8	21,8	13,91	31,8	24,8	10	17
69	44,00	38,48	10,0	19,8	21,8	13,91	31,8	24,8	10	17
100	54,86	45,72	11,4	21,3	25,8	17,45	33,5	26,7	12	18

TABLE 2 ENTRY SIZE	G MIN	H
04	3,18	6,4
05	3,97	7,2
06	4,77	8,0
07	5,56	8,8
08	6,35	9,6
09	7,14	10,4
10	7,94	11,2
11	8,73	12,0
12	9,52	12,8
13	10,31	13,5
14	11,10	14,3
15	11,89	15,1
16	12,70	15,9
17	13,47	16,7
18	14,26	17,5

STYLE Z ONLY

TABLE 3 CODE	PLATING
B	CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
C	ELECTROLESS NICKEL
U	UNPLATED
Y	YELLOW CHROMATE OVER CADMIUM
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL

LIST NOT EXHAUSTIVE - FOR COMPREHENSIVE LIST AND SPECS SEE WEBSITE

DRAWN	K.SHEPPARD	DATE 29/11/2011			3RD ANGLE PROJECTION NOT TO SCALE		POLAMCO LTD	WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PAGE 2	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES
SALES APPR	A.POLSON	11/11/2011								
DESIGN APPR				THIS DRAWING IS COPYRIGHTANDTHE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	ASSY USED ON: MIL-DTL-83513					MATERIAL ALUMINIUM ALLOY
QUAL APPR					TITLE:					
ISSUE 6	REV 3	DCR			BANDING BACKSHELL					
WEIGHT		GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°			PART NUMBER:					DRAWING NO: P22259
					RBTMM SERIES					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[RBMM-U-31-09-1-C-FSK](#) [RBMM-U-37-09-1-C-FSK](#) [RBMM-Z-31-09-1-C-FSK](#) [RBMM-U-25-08-1-C-FSK](#)
[RBMM-U-51-10-1-C-FSK](#) [RBMM-Z-09-08-1-C-FSK](#) [RBMM-U-21-08-1-C-FSK](#) [RBMM-Z-21-08-1-C-FSK](#) [RBMM-](#)
[Z-15-08-1-C-FSK](#) [RBMM-Z-25-08-1-C-FSK](#) [RBMM-Z-51-10-1-C-FSK](#) [RBMM-U-09-08-1-C-FSK](#) [RBMM-U-15-08-](#)
[1-C-FSK](#) [RBMM-Z-37-09-1-C-FSK](#)