

Molded Divider, High Voltage or High Precision, Surface Mount



FEATURES

- High voltage up to 1500 V utilizing thick film technology
- Precision to $\pm 0.5\%$ with low TCR tracking to 25 ppm/ $^{\circ}\text{C}$ utilizing thick film technology
- Sulfur resistant
- Automotive compliant terminations
- AEC-Q200 qualified
- Wide range of resistance value and ratios
- 12.5 mm creepage distance. Rated 1250 V per IEC 60664-1
- PATENT(S): www.vishay.com/patents
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	CASE SIZE	POWER RATING $P_{70^{\circ}\text{C}}$ W	MAXIMUM WORKING VOLTAGE ⁽¹⁾ V	RESISTANCE RANGE R_1 Ω	TOLERANCE ⁽³⁾ R_1 $\pm \%$	RATIO RANGE $(R_1 + R_2) / R_2$	RATIO TOL. $\pm \%$	TEMPERATURE COEFFICIENT ⁽⁴⁾ (-55 $^{\circ}\text{C}$ to +125 $^{\circ}\text{C}$) $\pm \text{ppm}/^{\circ}\text{C}$	TCR TRACKING $\pm \text{ppm}/^{\circ}\text{C}$
CDMM	4527	1.5	1500	500K to 50M ⁽²⁾	0.5, 1, 2, 5, 10	100:1 to 700:1	0.5, 1, 2, 5	100	25 - 50

Notes

⁽¹⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less

⁽²⁾ Resistance value is calibrated at 100 V_{DC}

⁽³⁾ Contact factory for tighter tolerances

⁽⁴⁾ Reference only: Not for all values specified. Consult factory for your value

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: CDMM20M0F2500fef (preferred part number format)

C	D	M	M	2	0	M	0	F	2	5	0	0	F	E	F	
GLOBAL MODEL	RESISTANCE VALUE (R_1)	TOLERANCE	RATIO ($R_1 + R_2$) / R_2	RATIO TOLE	SOLDER TERMINATION	PACKAGING	SPECIAL									
(see Standard Electrical Specifications Global Model column for options)	K = k Ω M = M Ω 525K = 525 k Ω 1M50 = 1.5 M Ω	D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$ K = $\pm 10\%$	3 digit significant figure, followed by a multiplier 2500 = 250:1 3000 = 300:1 1001 = 1000:1	D = $\pm 0.5\%$ F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$	E = Sn100	B = bulk F = T/R (1200 pcs) 1 = T/R (1000 pcs) 5 = T/R (500 pcs) T = T/R (250 pcs min.)	Blank = standard (dash number) (up to 2 digits) from 1 to 99 as applicable									

Notes

- Contact factory for other ratios
- For additional information on packaging, refer to the Surface Mount Resistor Packaging document (www.vishay.com/doc?31543)

PATENT(S): www.vishay.com/patents


This Vishay product is protected by one or more United States and international patents.

VOLTAGE AND TEMPERATURE COEFFICIENTS OF RESISTANCE CHART (TYPICAL)


GLOBAL MODEL	RESISTANCE Ω	RATIO (TYPICAL)	VCR ppm/V	TCR (-55 °C to +125 °C) ppm/°C
CDMM	500K	200:1	10	100
	15M	250:1	10	100
	50M	300:1	10	150

Note

- Contact factory for other ratios

DERATING CURVE

ENVIRONMENTAL SPECIFICATIONS


Operating temperature	-55 °C to +155 °C
-----------------------	-------------------

TYPICAL DC ELECTRICAL CIRCUIT

MECHANICAL SPECIFICATIONS

Resistive element	Ruthenium oxide (thick film)
Encapsulation	Molded thermoplastic
Substrate	Alumina
Termination	Solder-coated bronze

DIMENSIONS in inches (millimeters)

L	H	W	W ₁	A	B	C	E	a ₁	a ₂	b	I
0.455 ± 0.020 (11.56 ± 0.508)	0.167 ± 0.010 (4.24 ± 0.254)	0.275 ± 0.005 (6.98 ± 0.127)	0.216 ± 0.005 (5.49 ± 0.127)	0.100 ± 0.010 (2.54 ± 0.254)	0.100 ± 0.010 (2.54 ± 0.254)	0.083 ± 0.005 (2.11 ± 0.127)	0.050 ± 0.005 (1.27 ± 0.127)	0.225 (5.72)	0.87 (2.21)	0.145 (3.68)	0.255 (6.48)



PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Thermal shock	-55 °C to +150 °C, 1000 cycles, 15 min at each extreme	± 0.5 % ΔR
Short time overload	2.5 x rated power for 5 s	± 0.5 % ΔR
Low temperature storage	-55 °C for 24 h	± 0.5 % ΔR
High temperature exposure	1000 h at 155 °C	± 0.5 % ΔR
Biased humidity	+85 °C, 85 % RH, 10 % rated power ⁽¹⁾ , 1000 h	± 0.5 % ΔR
Mechanical shock	100 g's for 11 ms, 5 pulses	± 0.5 % ΔR
Vibration	Frequency varied 10 Hz to 500 Hz in 1 min, 3 directions, 9 h	± 0.5 % ΔR
Load life	1000 h at rated power, +70 °C, 1.5 h "ON", 0.5h "OFF"	± 1.0 % ΔR
Resistance to solder heat	+260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± 0.5 % ΔR


Note

⁽¹⁾ Applied voltage is based on the critical resistance value, not to exceed 500 V

PACKAGING				
MODEL	TAPE WIDTH	DIAMETER	PIECES/REEL	CODE
CDMM	24 mm / embossed plastic	330 mm / 13"	1200	EF
			1000	E1
			500	E5
			250	ET

Note

- Embossed carrier tape per EIA-481



The above image shows the orientation of the parts in the reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay](#):

[CDMM20M0F2500DET](#) [CDMM500KF1000FET](#) [CDMM50M0F5000FET](#)