


# Thick Film Planar Resistors, Through-Hole, High Voltage



## APPLICATIONS

Applications include power supplies, transformers and any application requiring operation within an environment where high voltages are used.

## FEATURES

- 30 000 V capability
- Very low voltage coefficient to less than 1 ppm/V
- Outstanding stability under adverse conditions
- Stable cermet resistive element bonded to a high-purity alumina substrate
- Tough epoxy-based coating and high voltage stability
- Dividers available, see Vishay Techno's TD datasheet ([www.vishay.com/doc?68042](http://www.vishay.com/doc?68042))
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS\***  
Available  
**HALOGEN  
FREE**

## Note

\* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details.

| STANDARD ELECTRICAL SPECIFICATIONS |                                                |                                             |                                      |                  |                                     |
|------------------------------------|------------------------------------------------|---------------------------------------------|--------------------------------------|------------------|-------------------------------------|
| GLOBAL MODEL / SIZE                | POWER RATING<br><i>P</i> <sub>25 °C</sub><br>W | MAXIMUM WORKING VOLTAGE <sup>(1)</sup><br>V | RESISTANCE RANGE <sup>(2)</sup><br>Ω | TOLERANCE<br>± % | TEMPERATURE COEFFICIENT<br>± ppm/°C |
| TR03C                              | 0.25                                           | 0.8K                                        | 300 to 3M                            | 1, 2, 5, 10, 20  | 100                                 |
|                                    |                                                |                                             | 300 to 25M                           | 1, 2, 5, 10, 20  | 200, 300                            |
| TR03X                              |                                                | 2.5K                                        | 25M to 250M                          | 1, 2, 5, 10, 20  | 200, 300                            |
|                                    |                                                |                                             | 260M to 2G                           | 5, 10, 20        | 200, 300                            |
|                                    |                                                |                                             | 2.1G to 10G                          | 5, 10, 20        | 500                                 |
| TR05D                              | 0.5                                            | 4K                                          | 500 to 25M                           | 1, 2, 5, 10, 20  | 100                                 |
|                                    |                                                |                                             | 3K to 200M                           | 1, 2, 5, 10, 20  | 200, 300                            |
| TR05X                              |                                                | 5K                                          | 30M to 1G                            | 1, 2, 5, 10, 20  | 200, 300                            |
|                                    |                                                |                                             | 1.1G to 20G                          | 5, 10, 20        | 200, 300                            |
|                                    |                                                |                                             | 21G to 100G                          | 5, 10, 20        | 500                                 |
| TR10F                              | 1                                              | 6.5K                                        | 1K to 16M                            | 1, 2, 5, 10, 20  | 100                                 |
|                                    |                                                |                                             | 2K to 120M                           | 1, 2, 5, 10, 20  | 200, 300                            |
| TR10X                              |                                                | 10K                                         | 20M to 1G                            | 1, 2, 5, 10, 20  | 200, 300                            |
|                                    |                                                |                                             | 1.1G to 15G                          | 5, 10, 20        | 200, 300                            |
|                                    |                                                |                                             | 16G to 1T                            | 5, 10, 20        | 500                                 |
| TR15G                              | 1.5                                            | 12.5K                                       | 1.5K to 45M                          | 1, 2, 5, 10, 20  | 100                                 |
|                                    |                                                |                                             | 5K to 340M                           | 1, 2, 5, 10, 20  | 200, 300                            |
| TR15X                              |                                                | 15K                                         | 60M to 1G                            | 1, 2, 5, 10, 20  | 200, 300                            |
|                                    |                                                |                                             | 1.1G to 35G                          | 5, 10, 20        | 200, 300                            |
|                                    |                                                |                                             | 36G to 1.5T                          | 5, 10, 20        | 500                                 |
| TR20H                              | 2                                              | 17.5K                                       | 2K to 64M                            | 1, 2, 5, 10, 20  | 100                                 |
|                                    |                                                |                                             | 8K to 480M                           | 1, 2, 5, 10, 20  | 200, 300                            |
| TR20X                              |                                                | 20K                                         | 80M to 1G                            | 1, 2, 5, 10, 20  | 200, 300                            |
|                                    |                                                |                                             | 1.1G to 50G                          | 5, 10, 20        | 200, 300                            |
|                                    |                                                |                                             | 51G to 2T                            | 5, 10, 20        | 500                                 |
| TR30J                              | 3                                              | 25K                                         | 3K to 82M                            | 1, 2, 5, 10, 20  | 100                                 |
|                                    |                                                |                                             | 8.5K to 620M                         | 1, 2, 5, 10, 20  | 200, 300                            |
| TR30X                              |                                                | 30K                                         | 80M to 1G                            | 1, 2, 5, 10, 20  | 200, 300                            |
|                                    |                                                |                                             | 1.1G to 60G                          | 5, 10, 20        | 200, 300                            |
|                                    |                                                |                                             | 61G to 3T                            | 5, 10, 20        | 500                                 |

## Notes

- Custom sizes available
  - Voltage coefficient: typically less than 1 ppm/V (tested per MIL-STD-202)
- (1) Continuous working voltage shall be  $\sqrt{P \times R}$  or maximum working voltage, whichever is less.
- (2) All resistance values are calibrated at 100 V<sub>DC</sub>. Calibration at other voltages available upon request.

## GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: TR20H1K00FKEB (preferred part number format)

| T                  | R                                                                                                                                                                                                                                                                                                                                                                                                                                  | 2 | 0 | H                                                                                                                                                                               | 1 | K | 0                                                                                                                                | 0 | F                                                                                    | K                                        | E | B                                  |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|---|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|---|----------------------------------------------------------------------------------------------------------------------------------|---|--------------------------------------------------------------------------------------|------------------------------------------|---|------------------------------------|
| GLOBAL MODEL<br>TR | SIZE / POWER / VOLTAGE RATING                                                                                                                                                                                                                                                                                                                                                                                                      |   |   | RESISTANCE VALUE                                                                                                                                                                |   |   | TOLERANCE                                                                                                                        |   | TCR                                                                                  | TERMINAL FINISH                          |   | PACKAGING                          |
|                    | <b>03C</b> = 0.25 W, med. voltage<br><b>03X</b> = 0.25 W, max. voltage<br><b>05D</b> = 0.5 W, med. voltage<br><b>05X</b> = 0.5 W, max. voltage<br><b>10F</b> = 1 W, med. voltage<br><b>10X</b> = 1 W, max. voltage<br><b>15G</b> = 1.5 W, med. voltage<br><b>15X</b> = 1.5 W, max. voltage<br><b>20H</b> = 2 W, med. voltage<br><b>20X</b> = 2 W, max. voltage<br><b>30J</b> = 3 W, med. voltage<br><b>30X</b> = 3 W, max. voltage |   |   | R = $\Omega$<br>K = k $\Omega$<br>M = M $\Omega$<br>G = G $\Omega$<br>T = T $\Omega$<br><b>400R</b> = 400 $\Omega$<br><b>10M0</b> = 10 M $\Omega$<br><b>1T00</b> = 1 T $\Omega$ |   |   | <b>F</b> = $\pm 1.0\%$<br><b>G</b> = $\pm 2.0\%$<br><b>J</b> = $\pm 5.0\%$<br><b>K</b> = $\pm 10.0\%$<br><b>M</b> = $\pm 20.0\%$ |   | <b>K</b> = 100 ppm<br><b>N</b> = 200 ppm<br><b>M</b> = 300 ppm<br><b>P</b> = 500 ppm | <b>E</b> = Sn100<br><b>R</b> = Sn60/Pb40 |   | <b>B</b> = bag<br><b>S</b> = strip |

Historical Part Numbering: TR20H1001FKE3 (will continue to be accepted)

| TR               | 20H                 | 1001             | F         | K   | e3              |
|------------------|---------------------|------------------|-----------|-----|-----------------|
| HISTORICAL MODEL | SIZE / POWER RATING | RESISTANCE VALUE | TOLERANCE | TCR | TERMINAL FINISH |

### Note

- For additional information on packaging, refer to the Through Hole Resistor Packaging document ([www.vishay.com/doc?31544](http://www.vishay.com/doc?31544)).

## MECHANICAL SPECIFICATIONS

**Resistive Element:** thick film

**Substrate:** 96 % pure alumina

**Encapsulation:** epoxy base, conformal coating

**Terminals:** solder plated copper leads

**Terminal Strength:** 4.5 pounds pull-test


**Power:** derated from ambient temperature +25 °C

## ENVIRONMENTAL SPECIFICATIONS

**Temperature Range:** -55 °C to +125 °C (for higher temperature range, consult factory)

**Load Life:** less than 0.15 %, 1000 h


## DIMENSIONS in inches (millimeters)



| MODEL | A<br>(LENGTH)                           | B<br>(HEIGHT)                           | C<br>(LEAD SPACING)                     | D<br>(LEAD DIA.)                       |
|-------|-----------------------------------------|-----------------------------------------|-----------------------------------------|----------------------------------------|
| TR03  | 0.300 $\pm$ 0.030<br>(7.62 $\pm$ 0.76)  | 0.210 $\pm$ 0.021<br>(5.33 $\pm$ 0.53)  | 0.200 $\pm$ 0.020<br>(5.08 $\pm$ 0.51)  | 0.025 $\pm$ 0.002<br>(0.64 $\pm$ 0.05) |
| TR05  | 0.500 $\pm$ 0.050<br>(12.70 $\pm$ 1.27) | 0.300 $\pm$ 0.030<br>(7.62 $\pm$ 0.76)  | 0.400 $\pm$ 0.040<br>(10.16 $\pm$ 1.02) | 0.025 $\pm$ 0.002<br>(0.64 $\pm$ 0.05) |
| TR10  | 1.00 $\pm$ 0.100<br>(25.40 $\pm$ 2.54)  | 0.350 $\pm$ 0.035<br>(8.89 $\pm$ 0.89)  | 0.900 $\pm$ 0.090<br>(22.86 $\pm$ 2.29) | 0.032 $\pm$ 0.002<br>(0.81 $\pm$ 0.05) |
| TR15  | 1.50 $\pm$ 0.150<br>(38.10 $\pm$ 3.81)  | 0.350 $\pm$ 0.035<br>(8.89 $\pm$ 0.89)  | 1.40 $\pm$ 0.140<br>(35.56 $\pm$ 3.56)  | 0.032 $\pm$ 0.002<br>(0.81 $\pm$ 0.05) |
| TR20  | 2.00 $\pm$ 0.200<br>(50.80 $\pm$ 5.08)  | 0.350 $\pm$ 0.035<br>(8.89 $\pm$ 0.89)  | 1.90 $\pm$ 0.190<br>(48.26 $\pm$ 4.83)  | 0.032 $\pm$ 0.002<br>(0.81 $\pm$ 0.05) |
| TR30  | 3.00 $\pm$ 0.300<br>(76.20 $\pm$ 7.62)  | 0.400 $\pm$ 0.040<br>(10.16 $\pm$ 1.02) | 2.90 $\pm$ 0.290<br>(73.66 $\pm$ 7.37)  | 0.032 $\pm$ 0.002<br>(0.81 $\pm$ 0.05) |



## DERATING





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[TR05C5008FKW](#) [TR03C5008FKW](#) [TR20H1706F](#) [TR10F5005FKW](#) [TR10F1006FK](#) [TR10F2505KKW](#)  
[TR20H100MFNRS](#) [TR10F1005J](#) [TR10F1006J](#) [TR15G1007J](#) [TR10F50M0GNRS](#) [TR10F10M0JKRB](#)  
[TR10F200MFKRS](#) [TR20H10M0FNRS](#) [TR20H50M0FKES](#) [TR10X1G00FNEB](#) [TR10F100MJNES](#) [TR03X1G10KNRB](#)  
[TR15X1G00JNEB](#) [TR10F100MFNES](#) [TR15G20M0FKES](#) [TR15G500MFNES](#) [TR20H100MFNES](#) [TR10X1G00JNES](#)  
[TR10X5G00JNES](#) [TR20X500MFNES](#) [TR15G50M0FNES](#) [TR15X1G00JNES](#) [TR20H10M0FKES](#) [TR20H1M50FKES](#)  
[TR20H20M0FKES](#) [TR20X2G00JNES](#) [TR15G10M0FKES](#) [TR15G200MFNES](#) [TR15G250MFNES](#) [TR15G300MFNES](#)  
[TR15G330KFKES](#) [TR15G4M00FKES](#) [TR10F5M00FKES](#) [TR10F80M0FNES](#) [TR10X200MJNES](#) [TR10X2G00JNES](#)  
[TR10X500MFNES](#) [TR15G100MFNES](#) [TR10F20K0FKES](#) [TR10F2K50FKES](#) [TR10F2M00FKES](#) [TR10F390KFKES](#)  
[TR10F40M0FNES](#) [TR10F50M0FNES](#) [TR05D10M0FKES](#) [TR05D1M50FKES](#) [TR05D200KFKES](#) [TR05D22M0FKES](#)  
[TR10F10M0FKES](#) [TR10F200MFKES](#) [TR05D50M0FKES](#) [TR10F500MFKEB](#) [TR15X47G0JPRS](#) [TR15G30M0GNEB](#)  
[TR10F1G00FKRS](#) [TR10X22M0KNEB](#) [TR10X500MGNEB](#) [TR10X100GKMEB](#) [TR20X1G00GNEB](#) [TR30J400MMNES](#)  
[TR10X10G0KMEB](#) [TR05X100MFNES](#) [TR15X4G70JNRS](#) [TR05D30M0GNEB](#) [TR10X300MFNES](#) [TR05D1M50FNEB](#)  
[TR10F57M6FKEB](#) [TR05D325KFNEB](#) [TR10X2G20GKRS](#) [TR05D49M9FKES](#) [TR03C20M0FKRS](#) [TR20H200MFKEB](#)  
[TR05D100MFKEB](#) [TR15G60M0GNEB](#) [TR10F200MKKRB](#) [TR10F300MFKRB](#) [TR05D470MKKES](#) [TR10F8M06FKEB](#)  
[TR10F1G00KKEB](#) [TR10F10M0JKEB](#) [TR10F60M0JNRS](#) [TR10F200MKKRS](#) [TR30J1M00JMEB](#) [TR15G150MJNES](#)  
[TR20H5M00FKEB](#) [TR20H10M0FKEB](#) [TR05D1M00FKES](#) [TR05D1G00JNEB](#) [TR30J400MFKES](#) [TR10F1G00FKEB](#)  
[TR05D20M0FNRB](#) [TR05D100MJKES](#) [TR05D500MFNES](#) [TR05D68M0FKRB](#)