

Features

Regulated Converter

- 1 inch² footprint for the tiniest 3 watt module
- Standby mode optimized (Ecodesign Lot 6)
- No load power consumption <150mW
- Operating temperature range: -40°C to +80°C
- Household IEC/EN60335
- EMC compliance without external components

RECOM
AC/DC Converter

RAC03-K

Description

The RAC03-K series are the smallest 3 watt solution on the market. In a compact 1in² footprint, these modules deliver an output power of 3 watts from -40°C to 60°C and 2 watts up to 80°C. Despite such a high power density and small footprint, the RAC03-K series is a complete solution supporting Ecodesign Lot 6 standby mode operation for worldwide applications in automation, industry 4.0, IoT, household, and home automation. With an input voltage range from 85 to 264VAC and international safety certifications for industrial, domestic, ITE, and household applications, these are some of the most versatile power modules on the market. Due to their reinforced class II installation rating and their significantly wide margin to class B emissions compliance without external components, these are the easiest to use modular power solutions in the industry.



3 Watt Single Output



UL/IEC/EN62368-1 certified
CAN/CSA C22.2 No. 62368-1-14 certified
IEC/EN60335-1 certified
EN55032/EN55024 compliant
EN55014-1 /-2 compliant
IEC/EN61204-3 compliant
FCC 47 Part 15
CB Report

Model Numbering



Ordering Examples

RAC03-05SK = 5Vout Single THT
RAC03-12SK = 12Vout Single THT

Specifications (measured @ $T_a = 25^\circ\text{C}$, nom. Vin, full load and after warm-up unless otherwise stated)


BASIC CHARACTERISTICS					
Parameter	Condition		Min.	Typ.	Max.
Internal Input Filter			Pi type		
Input Voltage Range ^(2,3)	nom. Vin = 230VAC		85VAC 120VDC	230VAC	264VAC 370VDC
Input Current	115VAC 230VAC				80mA 40mA
Inrush Current	cold start at $+25^\circ\text{C}$	115VAC 230VAC			10A 20A
No load Power Consumption	230VAC			100mW	150mW
ErP Standby Mode Conformity (Output Load Capability)	Input Power = 0.5W 1W				0.3W 0.7W
Input Frequency Range	AC Input		47Hz		63Hz
Minimum Load			0%		
Power Factor	115VAC 230VAC		0.5 0.4		
Start-up Time				20ms	
Rise Time				15ms	
Hold-up Time	115VAC 230VAC			15ms 80ms	
Internal Operating Frequency	100% load at nominal Vin				130kHz
Output Ripple and Noise ⁽⁴⁾	20MHz BW	3.3Vout, 5Vout all others			60mVp-p 1% of Vout nom.

Notes:


- Note2: The products were submitted for safety files at AC-Input operation
- Note3: Refer to **"Line Derating"**
- Note4: Measured with a $0.1\mu\text{F}$ MLCC & $10\mu\text{F}$ E-cap in parallel across output. (low ESR)

Efficiency vs. Load

RAC03-05SK




RAC03-12SK



continued on next page


Specifications (measured @ $T_a = 25^\circ\text{C}$, nom. V_{in} , full load and after warm-up unless otherwise stated)



REGULATIONS

Parameter	Condition	Value
Output Accuracy		$\pm 3.0\%$ typ.
Line Regulation	low line to high line, full load	$\pm 2.5\%$ typ.
Load Regulation	10% to 100% load	2.5% typ.
Transient Response	25% load step change recovery time	4.0% max. 500 μs typ.

Deviation vs. Load



Specifications (measured @ $T_a = 25^\circ\text{C}$, nom. V_{in} , full load and after warm-up unless otherwise stated)

PROTECTIONS			
Parameter	Type	Value	
Input Fuse ⁽⁵⁾	internal	fusible resistor	
Short Circuit Protection (SCP)	below 100mΩ	Hiccup Mode, auto recovery	
Over Voltage Category (OVC)		OVCII	
Over Current Protection (OCP)		Hiccup Mode, auto recovery	
Class of Equipment		Class II	
Isolation Voltage (safety certified) ⁽⁶⁾	I/P to O/P	1 minute	3kVAC
Isolation Resistance		Viso= 500VDC	1GΩ min.
Isolation Capacitance	I/P to O/P	100kHz, 0.1V	100pF max.
Insulation Grade			reinforced
Leakage Current			0.25mA max.


Notes:

Note5: Refer to local safety regulations if input over-current protection is also required. Recommended fuse: slow blow type

Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage


ENVIRONMENTAL			
Parameter	Condition	Value	
Operating Temperature Range	@ natural convection 0.1m/s	full load refer to " <i>Derating Graph</i> "	-25°C to +60°C -40°C to +80°C
Maximum Case Temperature	230VAC		+95°C
Temperature Coefficient			±0.05%/K
Operating Altitude	according to 62368-1 (60335-1)		5000m (6000m)
Operating Humidity			20% to 90% RH max.
Pollution Degree			PD2
Vibration	according to MIL-STD-202G		10-500kHz, 2G 10min./1cycle, period 60 min. each along x, y, z
MTBF	according to MIL-HDBK-217F, G.B.	+25°C	>450 x 10 ³ hours
Design Lifetime	230VAC/60Hz and full load	+25°C	>40 x 10 ³ hours

Derating Graph
(@ Chamber and natural convection 0.1m/s)



Ambient Temperature [°C]	Output Load [%]
-40	67
-30	75
-25	100
0	100
20	100
40	100
60	100
70	85
80	67

Line Derating



Input Voltage [VAC]	Output Load [%]
85	67
100	100
264	100


Specifications (measured @ $T_a = 25^\circ\text{C}$, nom. V_{in} , full load and after warm-up unless otherwise stated)

SAFETY AND CERTIFICATIONS (DESIGNED TO MEET)		
Certificate Type	Report Number	Standard
Audio/video, information and communication technology equipment - Safety requirements	E224736	UL62368-1:2014, 2nd Edition CAN/CSA C22.2 No. 62368-1-14, 2nd Edition
Audio/video, information and communication technology equipment - Safety requirements (CB Scheme)	E491408-A6013	IEC62368-1:2014, 2nd Edition
Audio/video, information and communication technology equipment - Safety requirements		EN62368-1:2014 + A11:2017
Household and similar electrical appliances - Safety - Part 1: General requirements (LVD)	LCS190408025CS	IEC60335-1:2010 + C1:2016, 5th Edition EN60335-1:2012 + A13:2017
Measurement methods for electromagnetic fields of household appliances and similar apparatus with regard to human exposure		EN62233:2008
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V (CB Scheme)	50237373 001	IEC61558-1:2005 2nd Edition + A1:2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V		EN61558-1:2005 + A1:2009
Safety of transformers, reactors, power supply units and similar products for supply voltages up to 1100 V Part 2-16: Particular requirements and tests for switch mode power supply units and transformers for switch mode power supply units (CB Scheme)		IEC61558-2-16:2009 1st Edition + A1:2013
Safety of transformers, reactors, power supply units and similar products for supply voltages up to 1100 V Part 2-16: Particular requirements and tests for switch mode power supply units and transformers for switch mode power supply units		EN61558-2-16:2009 + A1:2013
RoHS2		RoHS-2011/65/EU + AM-2015/863
EMC Compliance	Condition	Standard / Criterion
Low voltage power supplies, d.c. output - Part 3: Electromagnetic compatibility	LCS190408054BE	IEC/EN61204-3:2008, Class B
Electromagnetic compatibility of multimedia equipment - Emission requirements ⁽⁷⁾		EN55032:2015, Class B
Information technology equipment - Immunity characteristics - Limits and methods of measurement		EN55024:2010 + A1:2015
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 1: Emission ⁽⁷⁾		EN55014-1:2006 + A2:2011
Electromagnetic compatibility - Requirements for household appliances, electric tools and similar apparatus - Part 2: Immunity		EN55014-2:2015
ESD Electrostatic discharge immunity test	Air: $\pm 2, 4, 8\text{kV}$ Contact: $\pm 2, 4\text{kV}$	EN61000-4-2:2009, Criteria B
Radiated, radio-frequency, electromagnetic field immunity	10V/m (80-1000MHz) 3V/M (1.4-2GHz) 1V/m (2-2.7GHz)	EN61000-4-3:2006 + A1:2009, Criteria A
Fast Transient and Burst Immunity	AC & DC Port: $\pm 2\text{kV}$	EN61000-4-4:2012, Criteria B
Surge Immunity	AC Port: $\pm 1\text{kV}$ DC Port: $\pm 0.5\text{kV}$	EN61000-4-5:2014 + A1:2017, Criteria B
Immunity to conducted disturbances, induced by radio-frequency fields	AC & DC Port: 10V	EN61000-4-6:2014, Criteria A
Power Magnetic Field Immunity	50Hz, 30A/m	EN61000-4-8:2010, Criteria A
Voltage Dips	100% and 60% 30% and 20%	EN61000-4-11:2004 + A1:2017, Criteria B EN61000-4-11:2004 + A1:2017, Criteria C
Voltage Interruptions	>95%	EN61000-4-11:2004 + A1:2017, Criteria C
Limits of Voltage Fluctuations & Flicker		EN61000-3-3:2013
Limitations on the amount of electromagnetic interference allowed from digital and electronic devices		FCC 47 Part 15 Subpart B
Notes: Note7: If output is connected to GND, please contact RECOM tech support for further information		

Specifications (measured @ $T_a = 25^\circ\text{C}$, nom. V_{in} , full load and after warm-up unless otherwise stated)

DIMENSION AND PHYSICAL CHARACTERISTICS		
Parameter	Type	Value
Material	case/baseplate potting PCB	black plastic, (UL94V-0) silicone, (UL94V-0) FR4, (UL94V-0)
Dimension (LxWxH)		28.5 x 23.5 x 17.9mm
Weight		20g typ.

Dimension Drawing (mm)



Front View: Shows a rectangular case with an embossed logo. Dimensions: 28.5mm width, 23.5mm height, and a central circular hole.

Bottom View: Shows the case with pins. Dimensions: 27.9mm width, 17.9mm height, and a central circular hole. Pin 1 is at the bottom-left, Pin 2 is at the top-left, Pin 3 is at the top-right, and Pin 4 is at the bottom-right. Tolerances: 0.60^{+0.10/-0.05} for the central hole, and 5.0^{+1.0} for the bottom edge.


Top View: Shows the case with pins. Dimensions: 22.9mm width and 2.54mm height. Pin 1 is at the top-left, Pin 2 is at the top-right, Pin 3 is at the bottom-right, and Pin 4 is at the bottom-left.

Pinning information

Pin #	Single
1	VAC in (L)
2	-Vout
3	+Vout
4	VAC in (N)

NC= no connection
Tolerance: xx.x= $\pm 0.5\text{mm}$
xx.xx= $\pm 0.3\text{mm}$

Recommended Footprint Details



Top View: Shows a grid footprint with pins 1, 2, 3, and 4. Pin 1 is at the bottom-left, Pin 2 is at the top-right, Pin 3 is at the top-left, and Pin 4 is at the bottom-right. Dimensions: 2.54mm for the central gap and 2.54mm for the height.

Bottom View: Shows a grid footprint with pins 1, 2, 3, and 4. Pin 1 is at the bottom-left, Pin 2 is at the top-left, Pin 3 is at the top-right, and Pin 4 is at the bottom-right. Dimensions: 9 x 2.54= 22.86mm width, 7 x 2.54= 17.78mm height, 11.39mm bottom width, and 8.89mm side widths.

PACKAGING INFORMATION		
Parameter	Type	Value
Packaging Dimension (LxWxH)	tube	486.8 x 30.5 x 27.6mm
Packaging Quantity		18pcs
Storage Temperature Range		-40°C to +85°C
Storage Humidity	non condensing	20% to 90% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RECOM:

[RAC03-05SK](#) [RAC03-3.3SK](#) [RAC03-12SK](#) [RAC03-18SK](#) [RAC03-15SK](#) [RAC03-24SK](#)