

LOW PROFILE BLADE AND BEAM

(0.50 mm) .0197" PITCH • LTH/LSH SERIES

14
Gbps



LTH
Mates:
LSH

LTH - **NO. OF POSITIONS PER ROW** - **01** - **PLATING OPTION** - **D** - **A** - **OTHER OPTION**

LSH
Mates:
LTH

-010, -020,
-030, -040, -050

-G
= 10 μ "
(0.25 μ m)
Gold

-K
= (5.50 mm)
.217" DIA
Polyimide
film Pick &
Place Pad

SPECIFICATIONS

Insulator Material:

Liquid Crystal
Polymer

Terminal Material:

Phosphor Bronze

Contact Material:

BeCu

Plating:

Au over 50 μ " (1.27 μ m) Ni

Current Rating:

2.6 A per pin


(2 pins powered)

Voltage Rating:

188 VAC/266 VDC

Operating Temp Range:

-55 °C to +125 °C



-TR
= Tape & Reel

-FR
= Full Reel
Tape & Reel
(must order max.
quantity per reel;
contact Samtec for
quantity breaks)

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max

Board Stacking:


For applications requiring more
than two connectors per board,
contact ipg@samtec.com

LSH - **NO. OF POSITIONS PER ROW** - **01** - **PLATING OPTION** - **D** - **A** - **OTHER OPTION**

MATED HEIGHT

LEAD STYLE	MATED HEIGHT*
-01	(2.31 mm) .091"

*Processing conditions
will affect mated height.



-K
= (7.50 mm)
.295" DIA
Polyimide
film Pick &
Place Pad

-TR
= Tape & Reel

-FR
= Full Reel
Tape & Reel
(must order max.
quantity per reel;
contact Samtec for
quantity breaks)

Note:

Some lengths, styles and
options are non-standard,
non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec](#):

[LSH-010-01-G-D-A-K-TR](#) [LSH-020-01-G-D-A-K-TR](#) [LSH-010-01-G-D-A](#) [LSH-030-01-H-D-A](#) [LSH-030-01-H-D-A-K](#)
[LSH-050-01-G-D-A-TR](#) [LSH-010-01-H-D-A-K-TR](#) [LSH-030-01-H-D-A-TR](#) [LSH-010-01-H-D-A-TR](#) [LSH-040-01-G-D](#)
[LSH-020-01-H-D-A-K-TR](#) [LSH-030-01-G-D-A-TR](#) [LSH-030-01-G-D-A-K](#) [LSH-040-01-G-D-A-TR](#) [LSH-040-01-H-D-A-K](#)
[TR](#) [LSH-020-01-G-D-A-K](#) [LSH-020-01-G-D-A-TR](#) [LSH-020-01-H-D-A-FR](#) [LSH-010-01-G-D-A-FR](#) [LSH-050-01-G-D-A](#)
[K-FR](#) [LSH-010-01-G-D-A-K-FR](#) [LSH-050-01-H-D-A-TR](#) [LSH-050-01-G-D-A-FR](#) [LSH-050-01-H-D-A-FR](#)