

## Evaluating the LTC2686 8-Channel, 16-Bit Voltage Output SoftSpan DAC

### FEATURES

- ▶ Fully featured evaluation board for the [LTC2686](#) multichannel voltage output DAC
- ▶ Flexible output power supply configuration
- ▶ Easy connection to external loads
- ▶ Test points to monitor DAC status signals
- ▶ [ACE](#) evaluation software compatible

### EVALUATION KIT CONTENTS

- ▶ DC2904A-B evaluation board
- ▶ Ribbon cable to connect to the Linduino [DC2026C](#) controller board

### EQUIPMENT NEEDED

- ▶ DC2026C controller board (must be purchased separately)
- ▶ PC running Windows® 7 or Windows 10
- ▶ Voltmeter
- ▶ Power supply


### SOFTWARE NEEDED

- ▶ ACE evaluation software (available for download from the [DC2904A](#) product page)

### DOCUMENTS NEEDED

- ▶ LTC2686 data sheet
- ▶ DC2904A-B design files (see the DC2904A product page)

### EVALUATION BOARD PHOTOGRAPH



001

Figure 1. DC2904A-B Evaluation Board

**TABLE OF CONTENTS**

Features.....	1	Reference.....	4
Evaluation Kit Contents.....	1	Multiplexer Output.....	4
Equipment Needed.....	1	On-Board Connectors.....	4
Software Needed.....	1	Getting Started.....	5
Documents Needed.....	1	Software Installation Procedures.....	5
General Description.....	1	Evaluation Hardware Setup.....	5
Evaluation Board Photograph.....	1	Software Operation.....	5
Evaluation Board Hardware.....	3	Main Window.....	6
Evaluation Board Overview.....	3	Troubleshooting.....	10
Power Supplies.....	3	Hardware.....	10
Analog Outputs.....	4	Ordering Information.....	11
Digital Interface.....	4		

**REVISION HISTORY****10/2021—Revision 0: Initial Version**

## EVALUATION BOARD HARDWARE

### EVALUATION BOARD OVERVIEW

The DC2904A-B requires the power connections and connection to the DC2026C controller board shown in [Figure 2](#). The ribbon cable provided in the evaluation kit connects the DC2904A-B and the DC2026C via the J1 connector. Turrets are provided to connect the DC2904A-B to the power supplies.

The DC2904A-B has other optional features to allow the user to select an external reference, provide separate supply voltages for Channel 0 to Channel 3 and Channel 4 to Channel 7, and to monitor various outputs through the on-board MUX pin. These optional features do not need to be changed for normal operation.

### POWER SUPPLIES

The DC2904A-B is powered using external supplies. The minimum requirement to power the DC2904A-B is to provide 5.0 V to 21 V on E2 (V1+) and connect E3 (GND) and E4 (V-) to ground (GND).

As an alternative, the supply connection to E4 (V-) can be in the range between -21 V and ground (GND) to accommodate applications that require a negative supply.

The default position for JP5 (V1+ = V2+) is in the CONNECT position. This position connects the V1+ and V2+ power supplies so that they are at the same voltage. By changing JP5 to the NC (not connected) position, V1+ and V2+ are decoupled on the evaluation board and can be driven with separate supplies. V1+ and V2+ have the same requirement. They must be in the range of 5 V to 21 V but do not need to be the same voltage when decoupled. However, V2+ must be less than or equal to V1+.

E10 (VCC) and E5 (IOVCC) are supplied from on-board regulators by default. If desired, these voltages can be driven with an external supply.




Figure 2. DC2904A-B Hardware Connections

## EVALUATION BOARD HARDWARE

### ANALOG OUTPUTS

The analog outputs,  $V_{OUT0}$  to  $V_{OUT7}$ , are available on the E13, E14, E15, E16, E17, E18, E19, and E20 turrets, respectively. Return paths for the ground currents are available on the E3 and E23 (GND) turrets. These turrets must be connected to load GND.

### DIGITAL INTERFACE

#### DC2026C Connections

The DC2904A-B uses the [DC2026C](#) to communicate with the [ACE](#) evaluation software through the USB port on the DC2026C. Use the provided ribbon cable to connect J1 of the DC2904A-B to J1 of the DC2026C. When this connection is made, the DC2026C powers the electrically erasable programmable read only memory (EEPROM) on the DC2904A-B. The ACE evaluation software uses the EEPROM to identify the DC2904A-B and load the proper plugin.

To ensure proper serial transfers and compatibility, the DC2026C powers the  $IOV_{CC}$  pin of the [LTC2686](#), which is nominally 5 V.

#### DC2026C Connector Pin Descriptions

[Figure 3](#) shows the pins for the [DC2026C](#) J1 connector. For descriptions of each pin, see [Table 1](#).




Figure 3. DC2026C J1 Connector Pins

Table 1. DC2026C Connector J1 Pin Descriptions

Pin No.	Mnemonic	Description
1	V+	Unregulated voltage from the DC2026C, nominally 7 V
2	VCCIO	I/O voltage set by JP3 on the DC2026C
3	GND	Ground
4	SCL/SCK	Serial clock from the DC2026C
5	MISO	Serial data from the DC2904A-B
6	CS	Chip select from the DC2026C
7	SDA/MOSI	Serial data from the DC2026C
8	GND	Ground
9	EEDA	Serial data for EEPROM
10	EEV <sub>CC</sub>	Power supply ( $V_{CC}$ ) for EEPROM
11	EESCL	Serial clock for EEPROM
12	EEGND	Ground for EEPROM
13	GND	Ground
14	NC	No connection

### REFERENCE

By default, the DC2904A-B uses the internal reference of the [LTC2686](#). To use an external reference, place the DC2904A-B JP1 (REF SEL) jumper into the EXT position and apply an external reference to E11 (REF).

### MULTIPLEXER OUTPUT

The LTC2686 has an internal multiplexer that allows monitoring of compliance voltages, output currents, and internal die temperature. The output compliance voltages and representative voltages of the output current and internal die temperature are available on the LTC2686 MUX pin and can be routed to the DC2904A-B E21 connector (MUX) using the [LTC2686-16 Memory Map](#) view in the ACE GUI (see [Figure 8](#)), and setting the appropriate bits in the analog mux control register. Refer to the LTC2686 data sheet for more details on the multiplexer functionality and register structure.

### ON-BOARD CONNECTORS

[Table 2](#) describes the on-board connectors on the DC2904A-B.

Table 2. On-Board Connectors

Connector	Function
J1	SPI/I <sup>2</sup> C interface pin header connector
JP1	Internal or external reference select
JP2	Toggle Pin 0 (TGP0)
JP3	Toggle Pin 1 (TGP1)
JP4	Toggle Pin 2 (TGP2)
JP5	Connect or disconnect V1+ and V2+
E1	V2+
E2	V1+
E3, E6, E7, E12, E23	GND
E4	V-
E5	IOVCC
E8	CLR
E9	LDAC
E10	VCC
E11	REF
E13	Channel 0 voltage output (VOUT0)
E14	Channel 1 voltage output (VOUT1)
E15	Channel 2 voltage output (VOUT2)
E16	Channel 3 voltage output (VOUT3)
E17	Channel 4 voltage output (VOUT4)
E18	Channel 5 voltage output (VOUT5)
E19	Channel 6 voltage output (VOUT6)
E20	Channel 7 voltage output (VOUT7)
E21	MUX
E22	FAULT

## GETTING STARTED

The ACE evaluation software controls and configures the on-board LTC2686 through the DC2026C.

## SOFTWARE INSTALLATION PROCEDURES

Before connecting the DC2026C to the DC2904A-B, follow these steps to set up the DC2904A-B for initial use in the ACE evaluation software:

1. Download the ACE evaluation software package from the DC2904A-B product page at [www.analog.com/DC2904A](http://www.analog.com/DC2904A) to start the ACE evaluation software installation.
2. Open the **ACEInstall\_1.21.xxxx.xxxx.exe** file and follow the instructions in the folder to complete the software installation process.

## EVALUATION HARDWARE SETUP


When the ACE evaluation software installation is complete, follow these steps to set up the DC2026C and the DC2904A-B together:

1. Connect the DC2026C to the DC2904A-B via the J1 connectors with the ribbon cable provided (see [Figure 2](#)).

2. Connect the desired power supplies to E2 (V1+), E3 (GND), and E4 (V-) on the DC2904A-B.
3. Connect the desired load to the appropriate channel on the DC2904A-B.
4. Connect the load ground to a ground (GND) turrets (either E3 or E23) on the DC2904A-B.
5. Connect the DC2026C to a PC or laptop using the USB cable.
6. Start the ACE evaluation software (see the [Software Operation](#) section).

## SOFTWARE OPERATION

To start the ACE evaluation software, from the **Start** menu, click **Analog Devices > ACE**. The software window opens (see [Figure 4](#)) until the software recognizes the DC2904A-B. When the software recognizes the DC2904A-B, the main software window in [Figure 5](#) opens.



*Figure 4. Interface Window*

## GETTING STARTED




Figure 5. ACE Evaluation Software Main Window

## MAIN WINDOW

In the main ACE evaluation software window (see Figure 5), each channel can be controlled. Various settings for the LTC2686 are available in this window, allowing the user to configure the output range, output voltage, gain adjustment, offset adjustment, toggle options, and dither options of each channel.

Refer to the [LTC2686](#) data sheet for more information on the device features associated with the different tab functions that are described in the following sections.

### Reference Configuration

The DC2904A-B uses the LTC2686 internal reference to set the full-scale range. To apply an external reference, click the box labeled **Reference Select** (see Figure 5).

### Setting the Channel Output Range

To set the output range for a specific channel on the LTC2686,

1. Select the channel from the **Channel Select** dropdown box.
2. Select the desired range for the selected channel using the **Span selection (V)** dropdown box (see Figure 5).

### Setting the Channel Voltage Value

To set the output voltage for a specific channel on the LTC2686,

1. Select the channel from the **Channel Select** dropdown box.
2. Type the desired value into the **Register A** text box (see Figure 5).

### Toggling Between A and B Output Registers

Each channel has two output registers that can be written independently.

1. Click the **Register A** or **Register B** option to select the register to write to.
2. Type the desired hexadecimal value into the **Register A** (or **Register B**) text box (see Figure 5).

### Settling Offset and Gain Values

Each channel can have an offset and gain value applied to the output. The value is applied to each channel independently.

1. Select the channel from the **Channel Select** dropdown box.
2. Type the desired hexadecimal offset or gain adjust value into the **Offset Adjust** or **Gain Adjust** text boxes (see Figure 5).

### Enabling Toggle Mode

Toggle mode can be enabled by selecting the **Enable Toggle/Dither Functionality** check box (see Figure 5). This check box enables the toggle view shown in Figure 6. The toggle signal can then be applied to the selected pin or supplied internally.

## GETTING STARTED

### Enabling Dither Mode

After enabling the toggle view shown in [Figure 6](#) as described in the [Enabling Toggle Mode](#) section, select the dither mode from the **Mode** dropdown box to bring up the dither options (see [Figure 7](#)).

The default values for the dither phase ( $\phi_0$ ) and period (N) are 0° and N = 4. The phase and period of the dither can be modified using the dropdown boxes to select from a fixed list of options.




Figure 6. Toggle View

## GETTING STARTED




Figure 7. Dither View

## GETTING STARTED

### Memory Map View

To access the **LTC2686-16 Memory Map** view, click the **Proceed to Memory Map** button from the software main window (see [Figure 5](#)).




Figure 8. LTC2686-16 Memory Map View

## TROUBLESHOOTING

### HARDWARE

A comprehensive list of frequently asked questions (FAQ) is available on the [LTC2686 FAQs](#) page in the [EngineerZone™](#) site. For

other questions, submit them to the [Precision DACs](#) section of the [EngineerZone](#) site.

## ORDERING INFORMATION

**Table 3. Evaluation Board Models**

Product	Board Model	Resolution
LTC2686-16	DC2904A-B	16 bits

### ESD Caution

**ESD (electrostatic discharge) sensitive device.** Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

### Legal Terms and Conditions

By using the evaluation board discussed herein (together with any tools, components documentation or support materials, the "Evaluation Board"), you are agreeing to be bound by the terms and conditions set forth below ("Agreement") unless you have purchased the Evaluation Board, in which case the Analog Devices Standard Terms and Conditions of Sale shall govern. Do not use the Evaluation Board until you have read and agreed to the Agreement. Your use of the Evaluation Board shall signify your acceptance of the Agreement. This Agreement is made by and between you ("Customer") and Analog Devices, Inc. ("ADI"), with its principal place of business at Subject to the terms and conditions of the Agreement, ADI hereby grants to Customer a free, limited, personal, temporary, non-exclusive, non-sublicensable, non-transferable license to use the Evaluation Board FOR EVALUATION PURPOSES ONLY. Customer understands and agrees that the Evaluation Board is provided for the sole and exclusive purpose referenced above, and agrees not to use the Evaluation Board for any other purpose. Furthermore, the license granted is expressly made subject to the following additional limitations: Customer shall not (i) rent, lease, display, sell, transfer, assign, sublicense, or distribute the Evaluation Board; and (ii) permit any Third Party to access the Evaluation Board. As used herein, the term "Third Party" includes any entity other than ADI, Customer, their employees, affiliates and in-house consultants. The Evaluation Board is NOT sold to Customer; all rights not expressly granted herein, including ownership of the Evaluation Board, are reserved by ADI. CONFIDENTIALITY. This Agreement and the Evaluation Board shall all be considered the confidential and proprietary information of ADI. Customer may not disclose or transfer any portion of the Evaluation Board to any other party for any reason. Upon discontinuation of use of the Evaluation Board or termination of this Agreement, Customer agrees to promptly return the Evaluation Board to ADI. ADDITIONAL RESTRICTIONS. Customer may not disassemble, decompile or reverse engineer chips on the Evaluation Board. Customer shall inform ADI of any occurred damages or any modifications or alterations it makes to the Evaluation Board, including but not limited to soldering or any other activity that affects the material content of the Evaluation Board. Modifications to the Evaluation Board must comply with applicable law, including but not limited to the RoHS Directive. TERMINATION. ADI may terminate this Agreement at any time upon giving written notice to Customer. Customer agrees to return to ADI the Evaluation Board at that time. LIMITATION OF LIABILITY. THE EVALUATION BOARD PROVIDED HEREUNDER IS PROVIDED "AS IS" AND ADI MAKES NO WARRANTIES OR REPRESENTATIONS OF ANY KIND WITH RESPECT TO IT. ADI SPECIFICALLY DISCLAIMS ANY REPRESENTATIONS, ENDORSEMENTS, GUARANTEES, OR WARRANTIES, EXPRESS OR IMPLIED, RELATED TO THE EVALUATION BOARD INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, TITLE, FITNESS FOR A PARTICULAR PURPOSE OR NONINFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS. IN NO EVENT WILL ADI AND ITS LICENSORS BE LIABLE FOR ANY INCIDENTAL, SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES RESULTING FROM CUSTOMER'S POSSESSION OR USE OF THE EVALUATION BOARD, INCLUDING BUT NOT LIMITED TO LOST PROFITS, DELAY COSTS, LABOR COSTS OR LOSS OF GOODWILL. ADI'S TOTAL LIABILITY FROM ANY AND ALL CAUSES SHALL BE LIMITED TO THE AMOUNT OF ONE HUNDRED US DOLLARS (\$100.00). EXPORT. Customer agrees that it will not directly or indirectly export the Evaluation Board to another country, and that it will comply with all applicable United States federal laws and regulations relating to exports. GOVERNING LAW. This Agreement shall be governed by and construed in accordance with the substantive laws of the Commonwealth of Massachusetts (excluding conflict of law rules). Any legal action regarding this Agreement will be heard in the state or federal courts having jurisdiction in Suffolk County, Massachusetts, and Customer hereby submits to the personal jurisdiction and venue of such courts. The United Nations Convention on Contracts for the International Sale of Goods shall not apply to this Agreement and is expressly disclaimed.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Analog Devices Inc.:](#)

[DC2904A-B](#)