

Specification Sheet

Part Number: 151-03789

TPE layer protects cables and prevents rotation and axial slide, for a positive hold without crushing bundles.

Clamps are stackable to minimize space.

Anti-rotation feature prevents clamps from rotating while bolting down.

Releasable latch allows access to routings for serviceability.



Dual Bundle High Voltage Clamp, Anti-Rotation, 0.67" Bundle Dia, PA66GF15%/TPE, Black, 400/carton

Article Number	151-03789
Type	HDC17X2
Color	Black (BK)
Quantity Per	carton
Product Description	A clamp system that protects high-voltage cables in dual routing configurations and can be secured using hardware.
Short Description	Dual Bundle High Voltage Clamp, Anti-Rotation, 0.67" Bundle Dia, PA66GF15%/TPE, Black, 400/carton
Global Part Name	HDC17x2-PA66GF15/TPE-BK

Length L (Imperial)	3.24
Length L (Metric)	82.3
Width W (Imperial)	1.02
Width W (Metric)	26.0
Bundle Diameter Min (Imperial)	0.65
Bundle Diameter Min (Metric)	16.5
Bundle Diameter Max (Imperial)	0.69
Bundle Diameter Max (Metric)	17.5
Bundle Diameter 1st Loop Max (Imperial)	0.69
Bundle Diameter 1st Loop Max (Metric)	17.5
Bundle Diameter 2nd Loop Max (Imperial)	0.69
Bundle Diameter 2nd Loop Max (Metric)	17.5
Height H (Imperial)	1.31
Height H (Metric)	33.2
Mounting Hole Diameter D (Imperial)	0.31 x 0.05
Mounting Hole Diameter D (Metric)	M8 x 1.25 Threaded

Stud Diameter (Metric)	M8
Mounting Hole Centers (Imperial)	1.73
Material	Thermoplastic Elastomer (TPE) Polyamide 6.6 glass fiber reinforced (PA66GF15%)
Material Shortcut	PA66GF15 TPE
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	400
Package Quantity (Metric)	400
Customs Number	3926909988

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-03789](#)